Specifications

		0										1	12
		have place today the											
5	- I water	Carried and a	marris E	free Renations									
	- (t)	Annual I Sugar									81.0	* 4.0	
	0.6	Aug 1									True II		
	Content A												
							¥						
		Constanting the state	200	Enclosed Parties		12480	2						
	in the second												
		80											
	100 10					100	M						
	and in the other												
•0								10010-00-0					
A state lyped with solid hid solid.				1.11.1.10 1.11.1				Exception and Advance Maximum Advance Maximum Advance Maximum Advance					
			Training Color						Anders Martinet, 7 and and 7 for Solder-streets,				
									In the second se				

Appliance, EcoStruxure IT Data Center Expert, basic, up to 525 devices, up to 15 surveillance cameras, remote monitoring, management

AP9465

Overview Presentation StruxureWare Data Center Expert Basic scales up to 525 devices and 15 surveillance cameras. Lead Time Usually Ships within 2 Weeks Main Number Of Rack Unit 1U Number Of Cables 1 **Communication Port Protocol** DNS HTTP HTTPS SMTP SMS SSL TCP/IP **Provided Equipment** 1 Node Surveillance License Key 25-Node license key CD with software Installation guide Server appliance User Manual General **Operating System** Windows 7 Windows 8 Windows Vista Windows XP Windows XP Professional SP1 Windows XP Professional SP2 Memory Capacity 1GB/160GB available for data storage **Physical** Color Black Height 1.73 in (4.4 cm) Width 19.02 in (48.3 cm) Depth 15.00 in (38.1 cm) Net Weight 21.05 lb(US) (9.55 kg) **Mounting Location** Front

Mounting Preference

Mounting Mode



No preference

Rack-mounted

Environmental

Ambient Air Temperature For Operation	5095 °F (1035 °C)
Operating Altitude	010000 ft
Relative Humidity	590 %
Ambient Air Temperature For Storage	-31140 °F (-3560 °C)
Storage Altitude	030000 ft (0.009144.00 m)
Storage Relative Humidity	595 %

Communications & Management

Communication Network Type RJ-45 10/100/1000 Base-T

Ordering and shipping details

Gtin

731304262367

Packing Units

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.01 in (30.5 cm)
Package 1 Width	35.00 in (88.9 cm)
Package 1 Length	24.76 in (62.9 cm)
Package 1 Weight	42.09 lb(US) (19.09 kg)

Contractual warranty

Warranty

2 years repair or replace

Sustainability

Green Premium[™] label is Schneider Electric's commitment to delivering products with best-inclass environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low- $\rm CO_2$ products.

Learn more about Green Premium >

Eu Rohs Directive

Under investigation

