MAGIC InstaScan™ PORTABLE SMART SCANNER

MODEL: PDSBT-FL20-VP

SCAN DIRECTLY TO SMART DEVICES OR COMPUTER VIA WIRELESS TECHNOLOGY

Using wireless technology, you can scan and save directly to your smart devices via free app. Portable and compact scanner to scan anytime, anywhere.

SCAN WITH NO RESTRICTION IN SIZE

Scan different sizes as large as a blueprint to as small as a business card. Built-in smart stitching technology will stitch and auto-assemble each swipe back into a complete scan



POWERFUL OCR SOFTWARE

Directly save budget reports onto Excel®, or printed articles onto Word®, for full editing and archiving. You can also easily translate text into multiple languages using its translation feature. Share your scans instantly to Email, Dropbox®, Evernote«, and more. Built-in Text-to-Speech feature speaks out scanned text to you via app



Scan Resolution	400 DPI
Scan Speed (max.)	20cm/sec
Scan Direction	360°
Image Sensor	VGA (640 x 480)
Position Sensor	Laser mouse sensor and gyro
Light Source	3x LED
Interface	microUSB
iOS Requirement	Apple iOS 8: iPhone 5, iPhone 5s, iPhone 6, iPhone 6 Plus iPad Mini 2nd Generation or later, iPad® 3 Generation or later Android™ v4.4 or v5.0 (selected models only)
Operating Systerm	Windows® 7, Windows® 8, Windows® 8.1 Mac OS® 10.8, Mac OS® 10.9, Mac OS® 10.10
System Requirement	Intel® Core™ Duo 1.4 GHz or better 2GB RAM / 1GB free disk space 128 graphics memory (dedicated or shared) or better
Power	1090 mAh Li-Polymer
Battery Life	Approx. 3.5 hours
Dimensions approx.	4” (L) x 2.1” (H) x 1.1” (W)
Weight approx.	3.5 oz.

Apple and Mac are registered trademark of APple Inc., registered in the U.S. and other countries. Android® is a trademark of Google, Inc. Use of this trademark is subject to Google permission. Dropbox is a registered trademark of Dropbox, Inc. Evernote is a registered trademark of Evernote Corporation. Excel and Word are trademarks of Microsoft Corporation. Product names, logos, brands, and other trademarks referred to herein are the property of their respective trademark holders. All trademarks remain the property of their respective holders, and are used only to directly describe the products being provided. These trademark holders are not affiliated with VuPoint Solutions Inc. They do not sponsor or endorse VuPoint Solutions Inc. products or services. All trademarks are the property of their respective owners.

[VuPoint] Solutions
sales@vupointsolutions.com | www.vupointsolutions.com
17583 Railroad Street, City of Industry, CA 91748 | Tel: 626. 839. 5175 | Fax: 626. 839. 5217

07302015 specifications subject to change without prior notice