

Jabra Evolve 40

Engineered to boost efficiency.

Professional corded headset.

Enhanced productivity.

- Enjoy music with amazing sound
- Integrated busylight to avoid interruptions
- Flexible connectivity



Specifications

Audio	Microphone concept	Noise cancelling unidirectional microphone
	Microphone frequency range	100Hz – 10kHz
	Speaker size	D28 x 3.9mm
	Speaker bandwidth - Music mode	HiFi, 20Hz – 20kHz (wideband)
	Speaker bandwidth - Conference mode	150Hz - 7 kHz (wideband)
	Speaker sensitivity	93.6dB
	Speaker impedance	32+/-4.8Ω
	Active Noise Cancellation	No
	Passive Noise Cancellation	Yes
	Certifications	Certified for Skype for Business*, Avaya, Cisco, Alcatel Lucent and Astra
Ease of use	Call control	Call control unit for easy call handling
	Discreet boom arm	Boom arm with magnet that integrates into the headset when not on calls
	Busylight	Integrated busylight that acts as a 'do not disturb' signal
Battery	Battery included	No
	AC power supply	USB or USB-C power supply by PC
Connectivity	Connection	USB 2.0/3.0, USB-A, USB-C, 3.5mm jack
	NFC	No
General	Box content	Jabra Evolve 40 headset, Neoprene pouch, Quick Start Guide, Warning & Warranty leaflets
	Packaging dimensions (L x W x H)	190 x 255 x 100mm
	Weight	Mono headset: 143g Stereo headset: 171g
	USB cord length	Control cable: 95cm Headset cable: 120cm
	Warranty	2 years
	Certifications	CE, FCC, KCC, RCM, UL
	Operating temperature	-10°C to +50°C

SKU	Description
6393-823-189	Jabra Evolve 40 MS, Mono, USB-C
6393-829-289	Jabra Evolve 40 UC, Mono, USB-C
6399-823-189	Jabra Evolve 40 MS, Stereo, USB-C
6399-829-289	Jabra Evolve 40 UC, Stereo, USB-C
6399-823-109	Jabra Evolve 40 MS Stereo, USB
6399-829-209	Jabra Evolve 40 UC Stereo, USB
6393-823-109	Jabra Evolve 40 MS Mono, USB
6393-829-209	Jabra Evolve 40 UC Mono, USB

* USB-C connection is optimized for computers. USB-C connection with a mobile phone or tablet may give reduced performance.