Product data sheet

Specifications



Uniflair InRow RD, 300mm, Air Cooled, 208-230V, 60Hz

ACRD100

Overview

Lead time	Special Order - Call for Quoted Lead Times

Main

Main Input Voltage	208 V 230 V
Number of rack unit	42U
Provided Equipment	Installation guide Operations and maintenance manual

General

Compressor Type	Scroll
Air Discharge Patterns	Horizontal
Intake Air	Rear Return
Air flow	2290 ft³/min (1080.8 l/s)
Condensate Pump Capacity	2.6 Gal/hr(US) (0.010 m3/h)

Physical

Color	Black
Height	78.4 in (199.1 cm)
Width	11.8 in (30 cm)
Depth	42.1 in (107 cm)
Net Weight	404.86 lb(US) (183.64 kg)
Mounting preference	No preference
Mounting Mode	Not rack-mountable

Input

Input power	4600 W
Minimum Circuit Amp Capacity	25 A
Input Frequency	60 Hz
Maximum Overcurrent Protection	40 A

Conformance

Price is “List Price” and may be subject to a trade discount – check with your local distributor or retailer for actual price.

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Product Certifications	cUL Listed C-tick CE UL Listed

Environmental

Acoustic level	88.3 dBA

Communications & Management

Control panel	Multi-function LCD status and control console

Ordering and shipping details

GTIN	731304264477

Packing Units

Unit Type of Package 1	PCE
Nbr. of units in pkg.	1
Package 1 Height	83.4 in (211.8 cm)
Package 1 Width	44.8 in (113.7 cm)
Package 1 Length	29.4 in (74.6 cm)
Package weight(Lbs)	489.03 lb(US) (221.82 kg)

Contractual warranty

Warranty (in months)	12

Environmental Data

Schneider Electric aims to achieve Net Zero status by 2050 through supply chain partnerships, lower impact materials, and circularity via our ongoing “Use Better, Use Longer, Use Again” campaign to extend product lifetimes and recyclability.

Environmental Data explained >

How we assess product sustainability >

Use Better

Materials and Substances

Packaging made with recycled cardboard	**No**
Packaging without single use plastic	**No**
EU RoHS Directive	**Compliant with Exemptions**
REACh Regulation	**REACh Declaration**
California proposition 65	**WARNING: This product can expose you to chemicals including: Lead and lead compounds, which is known to the State of California to cause cancer and birth defects or other reproductive harm. For more information go to www.P65Warnings.ca.gov**

Use Again

Repack and remanufacture

Take-back	**No**
WEEE Label	**The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.**

Image of product / Alternate images

Alternative

