Product data sheet

Specifications



StruxureWare Data Center Expert Basic Management Pack

AP9482

Overview

Presentation	StruxureWare Data Center Expert Basic Management Pack provides a complete, surveillance, environmental, and physical infrastructure monitoring solution. Includes: 1 NetBotz Room Monitor 355 (with 120/240V PoE Injector), 1 NetBotz Door Switch Sensor for Rooms or 3rd Party Racks - 50 ft, 1 StruxureWare Data Center Expert Basic appliance with 25-Node License, 1 StruxureWare Data Center Expert Basic Software Support Contract
Lead time	Usually Ships within 2 Weeks

Main

Number of rack unit	1U
Number of cables	2
Communication port protocol	DHCP DNS HTTP HTTPS Modbus SMTP SMS SNMP v1 SNMP v3 SSL TCP/IP
Provided equipment	1 node surveillance license key 25-node license key Documentation CD Installation guide

Physical

Colour	Black
Height	4.4 cm
Width	54.6 cm
Depth	38.1 cm
Net weight	9.55 kg
Mounting location	Front
Mounting preference	No preference
Mounting mode	Not rack-mountable

Conformance

Standards	UL 60950

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Environmental

Ambient air temperature for operation	10…35 °C
Operating altitude	0...10000 ft
Relative humidity	5…90 %
Ambient air temperature for storage	-35…60 °C
Storage altitude	0.00…9144.00 m
Storage Relative Humidity	5…95 %

Packing Units

Package 1 Weight	19.09 kg
Package 1 Height	30.5 cm
Package 1 width	62.9 cm
Package 1 Length	78.7 cm

Offer Sustainability

REACh Regulation	REACh Declaration
REACh free of SVHC	Yes
EU RoHS Directive	Pro-active compliance (Product out of EU RoHS legal scope) EU RoHS Declaration
Take-back	Take-back program available

Contractual warranty

Warranty	2 years repair or replace