

Product data sheet

Specifications



APC NetShelter Soundproof, 32U, Server Rack Enclosure, 230V, Maple

AR4032IA

⚠ Discontinued

Overview

Lead time Usually Ships within 2 Weeks

Main

Product or Component Type Rack enclosure

Main Input Voltage 230 V

Input Connection Type IEC 60320 C20

Output connection type 8 IEC 60320 C13

Number of rack unit 32U

Cable length 8.17 ft (2.49 m)

Number of cables 1

Provided equipment Casters

Physical

Height 65.94 in (1675 mm)

Width 29.53 in (750 mm)

Depth 44.50 in (1130.4 mm)

Net Weight 476.20 lb(US) (216 kg)

Color Maple

Mounting preference No preference

Mounting Mode Not rack-mountable

Mounting position Horizontal

Maximum Mounting Depth 2.72 ft (0.83 m)

Minimum Mounting Depth 2.26 ft (0.69 m)

Rack Width 19"

Permanent permissible load 3306.94 lb(US) (1500 kg) static

Input

Input Frequency 50/60 Hz

Output

PDU Type Basic

Conformance

Standards EIA-310D

Ordering and shipping details

GTIN 731304621775

Packing Units

Unit Type of Package 1 PCE

Number of Units in Package 1 1

Package 1 Height 70.35 in (178.7 cm)

Package 1 Width 32.28 in (82 cm)

Package 1 Length 47.24 in (120 cm)

Package 1 Weight 376.99 lb(US) (171 kg)

Offer Sustainability

EU RoHS Directive Not applicable, out of EU RoHS legal scope

Contractual warranty

Warranty 2 Years

Recommended replacement(s)