Product specifications

Eaton TEL-150K-6

Catalog Number: TEL-150K-6

Eaton Power-sure 700, Transformer, Metering, Three-phase, 150 kVA, +10% to −20%, 208Y/120V, Hardwired, 17698 BTU/h

General specifications

Product Name	Catalog Number
Eaton Power-Sure 700 power conditioner	TEL-150K-6
UPC	**Product Length/Depth**
743172023049	35.5 in
Product Height	**Product Width**
74 in	34.4 in
Product Weight	**Warranty**
1978 lb	1 year

Certifications

UL 1012 CSA Certified FCC Cat. A

ANSI/IEEE Std C62.41

Product specifications

Type

Transformer

Phase

Three-phase

Bypass

Bypass

Efficiency

97% typical, 95% minimum

Output

Hardwired

Model

Metering

Operating Temperature

-10° to 40°C

Topology

Line conditioner

BTU rating

17698 BTU/h

Output voltage

208Y/120V

Indicators

Reg volt (3 green on phase), over temp cond (red)

Resources

Brochures

Power-Sure 700 - Product Assist

Installation instructions

Power-Sure 700 - Instruction Manual

Specifications and datasheets

Eaton Specification Sheet - TEL-150K-6

Power-Sure 700 - Technical Data

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Eaton.com/socialmedia