VOYAGER™ XP 1470G & 1472G

Durable, Highly Accurate 2D Scanner

Accessories Guide



Honeywell

TABLE OF CONTENTS

3 Battery and battery chargers

3 Access points, communication base and charger

4 Power supplies for cabled connections and charge/ communication bases

5 Cables/stands

BATTERY AND BATTERY CHARGERS



BAT-SCN01A

Battery Pack

Battery: Lithium-ion battery for Voyager™ 1202g and 1472g wireless scanners.



MB4-BAT-SCN01XXD06[1]

4-Bay Battery Charger-Desk Mount

4-bay battery charger for use with Granit, Xenon and Voyager Lithium-ion batteries, desktop power supply, two mounting screws (100006897), and instructions (MBC-INST).



MB4-BAT-SCN01XXW06[1]

MB4-BAT-SCN01XXW06

4-bay battery charger for use with Granit, Xenon and Voyager lithium-ion batteries, wall mount power supply, two mounting screws (100006897), and instructions (MBC-INST).

ACCESS POINTS, COMMUNICATION BASE AND CHARGER



AP-100BT-07N

Bluetooth® Access Point

Access point for scanners. Class 1 Bluetooth, 100m(330'), RS232/ USB/KBW/IBM (cable sold separately).



AP-010BT-07N

Bluetooth Access Point

Access point for scanners. Class 2 Bluetooth, 10m (33'), RS232/USB/KBW/ IBM (cable sold separately).



CCB01-010BT-V1N

Voyager Charge and Communication Base

Charge & Communication, Bluetooth, Typical 10m, 1 scanner can be connected, RS232/USB/KBW/IBM host interfaces (cables sold separately).



COB01

Charge Only Base

Charge-Only Base: Only 1 scanner can be charged at a time, power supply must be purchased separately.

[1] Indicates characters designating regional configuration

POWER SUPPLIES FOR CABLED CONNECTIONS AND CHARGE/COMMUNICATION BASES



46-00525-6

Power Supply – NA Plug

Power Supply: NA plug, 1.0A @ 5.2V DC, 90-255V AC @ 50-60Hz.



46-00526

Power Supply – EU Plug

Power Supply: EU plug, 1.0A @ 5.2V DC, 90-255V AC @ 50-60Hz.



46-00528

Power Supply – AU Plug

Power Supply: AU plug, 1.0A @ 5.2V DC, 90-255V AC @ 50-60Hz.



46-00529

Power Supply – CN Plug

Power Supply: CN plug, 1.0A @ 5.2V DC, 90-255V AC @ 50-60Hz.



46-00526-6-I

Power Supply – IN Plug

Power Supply: India plug, 1.0A@55.2V DC, 90-255V AC @50-60Hz.



PS-05-1000W-G

Power Supply - Type G (UK) Plug

Power Supply: Type G (UK) plug, 1.0A@5.2V DC, 90-255V AC @ 50-60Hz.

Power supplies for cabled connections



Power supplies for charge/communication bases



CABLES

CBL-020-300-C00	CBL-020-500-C00	CBL-500-150-S00	CBL-500-300-S00	CBL-500-300-C00
Cable: RS232(5V signals), black, DB9 Female, 3m (9.8'), coiled, 5V external power with option for host power on pin 9, w/o ferrite.	Cable: RS232(5V signals), black, DB9 Female, 5m (16'), coiled, 5V external power with option for host power on pin 9, w/o ferrite.	Cable: USB, Black, Type A, 1.5m(4.9'), Straight, 5V host power, w/o ferrite.	Cable: USB, black, Type A, 3m (9.8'), Straight, 5V host power, w/o ferrite.	Cable: USB, black, Type A, 3m (9.8'), coiled, 5V host power, w/o ferrite.

CBL-500-500-C00	CBL-500-500-S00	CBL-500-400-C00-01	CBL-503-300-C00	CBL-503-300-S00
Cable: USB, black, Type A, 5m (16.4'), coiled, 5V host power, w/o ferrite.	Cable: USB, black, Type A, 5m (16.4'), straight, 5V host power, w/o ferrite.	Cable: USB, black, Type A, 4m (13.1'), coiled, 5V host power, w/o ferrite.	Cable: USB, black, 12 locking type, 3m (9.8'), coiled, 5V host power, w/o ferrite.	Cable: USB, black, 12 locking type, 3m (9.8'), straight, 5V host power, w/o ferrite.

CBL-503-500-C00	CBL-800-300-C00	CBL-720-300-C00
Cable: USB, black, 12 locking type, 5m (16.4'), coiled, 5V host power, w/o ferrite.	Cable: USB, Type C, black, 3m (9.8'), coiled, 5V host power, w/o ferrite.	Cable: KBW, black, PS2, 3m (9.8'), coiled, 5V external power with options for host power, w/o ferrite.

STANDS



STND-15F03-009-6

Voyager™ XP 1470g Stand

Stand: gray, 15cm (6´) height, flexible rod, medium oval weighted base, Voyager 1250g/1470g cup.



STND-15R00-009-6

Voyager XP 1470g Stand (Rigid)

Stand: gray, 6in, rigid, cradle, 1470g.

HOLDER



HOLDER-009-U

Voyager Holder

Holder: Desk or wall holder, for Voyager 1250g and 1470g, 30,82.

For more information
automation.honeywell.com

Honeywell Industrial Automation
9680 Old Bailes Road
Fort Mill, SC 29707
800-582-4263
www.honeywell.com

Granit, Voyager, and Xenon are trademarks or registered trademarks of Honeywell International Inc.

Bluetooth is a trademark or registered trademark of Bluetooth SIG, Inc. All other trademarks are the property of their respective owners.

Voyager XP 1470g & 1472g 2D Scanner AG_LTR | Rev C | 05/24
© 2024 Honeywell International Inc.

Honeywell