Product specifications

Eaton TDL-100K-6



Catalog Number: TDL-100K-6

Eaton Power-Sure 700 TDL power conditioner, 11833 BTU/h, Three-phase, 97% typical, 95% minimum, 208Y/120V

General specifications

Product Name	Catalog Number
Eaton Power-Sure 700 power conditioner	TDL-100K-6
UPC	**Product Length/Depth**
743172022813	29 in
Product Height	**Product Width**
44 in	45 in
Product Weight	**Warranty**
1660 lb	1 year

Certifications

CSA Certified
FCC Cat. A
ANSI/IEEE Std C62.41
UL 1012

Powering Business Worldwide

Product specifications

Type

Transformer

Phase

Three-phase

Bypass

Bypass

Efficiency

97% typical, 95% minimum

Output

Hardwired

Model

Metering

Operating Temperature

-10° to 40°C

Topology

Line conditioner

BTU rating

11833 BTU/h

Output voltage

208Y/120V

Indicators

Reg volt (3 green on phase), over temp cond (red)

Resources

Brochures

Power-Sure 700 - Product Assist

Installation instructions

Power-Sure 700 - Instruction Manual

Specifications and datasheets

Eaton Specification Sheet - TDL-100K-6

Power-Sure 700 - Technical Data

Eaton Corporation plc
Eaton House
30 Pembroke Road
Dublin 4, Ireland
Eaton.com

© 2023 Eaton. All Rights Reserved.

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Eaton.com/socialmedia