Ortronics

Clarity 6 TracJack, T568A/B, 180 degree, Lt Blue

Part No. TJ600-26



Clarity 6a, 6 & 5e TracJacks, ETL verified to TIA Category 6a, 6 & 5e component specification. Front-loading and front removable. New universal T568A/B wiring label and tapered wiring towers simplify termination. Center tuned to Clarity patch cords for optimum performance.

TracJack® modules combine the ease and reliability of a front-loading individual jack with 110
termination.

Features & Benefits

ETL Verified to Category 6A component standard: Ensures standards compliance.

Easy to follow universal wiring label: Quick and user-friendly, eliminates confusion.

Center tuned design: Transparent interface with Clarity 6A/10G cords

Easy lace IDC housing: Reduces wiring time

Standard TracJack footprint: Fits in all TracJack faceplates and housings

Icon compatible, C6A marking on jack face: Supports 606 designation requirements

Specifications

General Info

Product Line	Ortronics	Color	Light Blue
UPC Number	662875433248	Country Of Origin	Mexico
Application Sector	Commercial, Industrial	Standard	UL 1863, TIA-568.2-D, 802.3bt Type 3 and Type 4, IEEE 802.3af / 802.3at, FCC part 68 Subpart F, IEC-603-7 compliant
Warranty Type	5-Year	Type	Jack

Dimensions

Product Width US	0.73 in	Product Depth US	1.1 in
Product Height US	0.92 in		

Additional Information

RoHS Compliant	Yes	Product Environmental Profile	Yes

Technical Information

Wire Gauge	22-24 AWG	Termination Style	110
Connector Type	RJ-45	Impedance	100 Ohm
Connectivity Footprint	TracJack		