

### Overview

## HPE Smart Choice Purchase Program – Supplemental QuickSpecs

### What is the HPE Smart Choice purchase program?

The HPE Smart Choice purchase program features popular fully configured products that can be quoted in minutes and shipped quickly through HPE Authorized Partners. Products are configured and tested in an HPE factory and stocked at HPE Authorized Distributors and Partners. The products arrive in a single box, making onsite integration easier and more efficient for partners and customers. Additionally, there are aggressively priced HPE Tech Care Services available only through the HPE Smart Choice program when you purchase an HPE Smart Choice product.

---

### Country Code Key

- -005 = HPE Smart Choice for US and Canada
  - -035 = HPE Smart Choice for United Kingdom
  - -205 = HPE Smart Choice for Brazil
  - -295 = HPE Smart Choice for Japan
  - -375 = HPE Smart Choice for Asia Pacific
  - -425 = HPE Smart Choice for Europe, the Middle East and Africa (EMEA)
  - -B25 = Worldwide HPE Smart Choice for Storage
  - -D05 = HPE Smart Choice for Argentina
  - -D65 = HPE Smart Choice for India
  - -DM5 = HPE Smart Choice for LATAM
-

## ProLiant Smart Choice Services

### HPE Services

Don't forget to add HPE Services – Standard Tech Care Basic and Essential Fixed support services in unique packages specific to Smart Choice purchase server configurations.

Fixed Families	Fixed SS	Long Description
<b>Smart Choice DL320 Gen11</b>	H44YQE	HPE 3 Year Tech Care Basic DL320 Gen11 Smart Choice Service
	H44YSE	HPE 5 Year Tech Care Basic DL320 Gen11 Smart Choice Service
	H79X2E	HPE 7 Year Tech Care Basic DL320 Gen11 Smart Choice Service
	H44YRE	HPE 3 Year Tech Care Essential DL320 Gen11 Smart Choice Service
	H44YTE	HPE 5 Year Tech Care Essential DL320 Gen11 Smart Choice Service
	H79X3E	HPE 7 Year Tech Care Essential DL320 Gen11 Smart Choice Service
<b>Smart Choice DL360 G10/+</b>	H44YVE	HPE 3 Year Tech Care Basic DL360 Gen10/Gen10+ Smart Choice Service
	H44YXE	HPE 5 Year Tech Care Basic DL360 Gen10/Gen10+ Smart Choice Service
	H79X4E	HPE 7 Year Tech Care Basic DL360 Gen10/Gen10+ Smart Choice Service
	H44YWE	HPE 3 Year Tech Care Essential DL360 Gen10/Gen10+ Smart Choice Service
	H44YYE	HPE 5 Year Tech Care Essential DL360 Gen10/Gen10+ Smart Choice Service
	H79X5E	HPE 7 Year Tech Care Essential DL360 Gen10/Gen10+ Smart Choice Service
<b>Smart Choice DL360 G11</b>	H44YZE	HPE 3 Year Tech Care Basic DL360 Gen11 Smart Choice Service
	H44ZCE	HPE 5 Year Tech Care Basic DL360 Gen11 Smart Choice Service
	H79X6E	HPE 7 Year Tech Care Basic DL360 Gen11 Smart Choice Service
	H44ZBE	HPE 3 Year Tech Care Essential DL360 Gen11 Smart Choice Service
	H44ZDE	HPE 5 Year Tech Care Essential DL360 Gen11 Smart Choice Service
	H79X7E	HPE 7 Year Tech Care Essential DL360 Gen11 Smart Choice Service
<b>Smart Choice DL380 G10/+</b>	H44ZFE	HPE 3 Year Tech Care Basic DL380 Gen10/Gen10+ Smart Choice Service
	H44ZHE	HPE 5 Year Tech Care Basic DL380 Gen10/Gen10+ Smart Choice Service
	H79X8E	HPE 7 Year Tech Care Basic DL380 Gen10/Gen10+ Smart Choice Service
	H44ZGE	HPE 3 Year Tech Care Essential DL380 Gen10/Gen10+ Smart Choice Service
	H44ZJE	HPE 5 Year Tech Care Essential DL380 Gen10/Gen10+ Smart Choice Service
	H79X9E	HPE 7 Year Tech Care Essential DL380 Gen10/Gen10+ Smart Choice Service
<b>Smart Choice DL38x G11</b>	H44ZKE	HPE 3 Year Tech Care Basic DL38x Gen11 Smart Choice Service
	H44ZME	HPE 5 Year Tech Care Basic DL38x Gen11 Smart Choice Service
	H79Y0E	HPE 7 Year Tech Care Basic DL38x Gen11 Smart Choice Service
	H44ZLE	HPE 3 Year Tech Care Essential DL38x Gen11 Smart Choice Service
	H44ZNE	HPE 5 Year Tech Care Essential DL38x Gen11 Smart Choice Service
	H79Y1E	HPE 7 Year Tech Care Essential DL38x Gen11 Smart Choice Service



## ProLiant Smart Choice Services

<b>Smart Choice DL325/DL345 G11</b>	H44ZQE	HPE 3 Year Tech Care Basic DL325/DL345 Gen11 Smart Choice Service
	H44ZSE	HPE 5 Year Tech Care Basic DL325/DL345 Gen11 Smart Choice Service
	H79Y2E	HPE 7 Year Tech Care Basic DL325/DL345 Gen11 Smart Choice Service
	H44ZRE	HPE 3 Year Tech Care Essential DL325/DL345 Gen11 Smart Choice Service
	H44ZTE	HPE 5 Year Tech Care Essential DL325/DL345 Gen11 Smart Choice Service
	H79Y3E	HPE 7 Year Tech Care Essential DL325/DL345 Gen11 Smart Choice Service
<b>Smart Choice ML350 G11</b>	H44ZVE	HPE 3 Year Tech Care Basic ML350 Gen11 Smart Choice Service
	H44ZXE	HPE 5 Year Tech Care Basic ML350 Gen11 Smart Choice Service
	H79Y4E	HPE 7 Year Tech Care Basic ML350 Gen11 Smart Choice Service
	H44ZWE	HPE 3 Year Tech Care Essential ML350 Gen11 Smart Choice Service
	H44ZYE	HPE 5 Year Tech Care Essential ML350 Gen11 Smart Choice Service
	H79Y5E	HPE 7 Year Tech Care Essential ML350 Gen11 Smart Choice Service
<b>Smart Choice ML110</b>	H44ZZE	HPE 3 Year Tech Care Basic ML110 Server Smart Choice Service
	H45BBE	HPE 5 Year Tech Care Basic ML110 Server Smart Choice Service
	H79Y8E	HPE 7 Year Tech Care Basic ML110 Server Smart Choice Service
	H79Y6E	HPE 3 Year Tech Care Essential ML110 Server Smart Choice Service
	H79Y7E	HPE 5 Year Tech Care Essential ML110 Server Smart Choice Service
	H79Y9E	HPE 7 Year Tech Care Essential ML110 Server Smart Choice Service
<b>Smart Choice Low-end Servers</b>	H45BCE	HPE 3 Year Tech Care Basic Low-end Server (ML30 and DL20) Smart Choice Service
	H45BDE	HPE 5 Year Tech Care Basic Low-end Server (ML30 and DL20) Smart Choice Service
	H81T2E	HPE 7 Year Tech Care Basic Low-end Servers Smart Choice Service
	H81T0E	HPE 3 Year Tech Care Essential Low-end Server Smart Choice Service
	H81T1E	HPE 5 Year Tech Care Essential Low-end Server Smart Choice Service
	H81T3E	HPE 7 Year Tech Care Essential Low-end Server Smart Choice Service
<b>Smart Choice MicroServer</b>	H45BFE	HPE 3 Year Tech Care Basic MicroServer Smart Choice Service
	H45BGE	HPE 5 Year Tech Care Basic MicroServer Smart Choice Service
	H81T4E	HPE 3 Year Tech Care Essential MicroServer Smart Choice Service
	H81T5E	HPE 5 Year Tech Care Essential MicroServer Smart Choice Service
<b>Smart Choice DL145 Gen11</b>	H48DJE	HPE 3 Year Tech Care Basic DL145 Gen11 Smart Choice Service
	H48DLE	HPE 5 Year Tech Care Basic DL145 Gen11 Smart Choice Service
	H48DNE	HPE 7 Year Tech Care Basic DL145 Gen11 Smart Choice Service
	H48DKE	HPE 3 Year Tech Care Essential DL145 Gen11 Smart Choice Service
	H48DME	HPE 5 Year Tech Care Essential DL145 Gen11 Smart Choice Service
	H48DQE	HPE 7 Year Tech Care Essential DL145 Gen11 Smart Choice Service



## MSA Smart Choice Services

Fixed Families	Fixed SS	Long Description
<b>HPE MSA 2070 SFF FC 12x1.92 XCVR Array</b>	HZ4L9E	HPE 3 Year Tech Care Basic MSA FC 23TB Smart Choice Service
	HZ4M0E	HPE 5 Year Tech Care Basic MSA FC 23TB Smart Choice Service
	HZ4M1E	HPE 3 Year Tech Care Essential MSA FC 23TB Smart Choice Service
	HZ4M2E	HPE 5 Year Tech Care Essential MSA FC 23TB Smart Choice Service
<b>HPE MSA 2070 SFF FC 12x3.84T XCVR Array</b>	HZ4M3E	HPE 3 Year Tech Care Basic MSA FC 46TB Smart Choice Service
	HZ4M4E	HPE 5 Year Tech Care Basic MSA FC 46TB Smart Choice Service
	HZ4M5E	HPE 3 Year Tech Care Essential MSA FC 46TB Smart Choice Service
	HZ4M6E	HPE 5 Year Tech Care Essential MSA FC 46TB Smart Choice Service
<b>HPE MSA 2070 SFF iSCSI 12x1.92T Array</b>	HZ4M7E	HPE 3 Year Tech Care Basic MSA iSCSI23 Smart Choice Service
	HZ4M8E	HPE 5 Year Tech Care Basic MSA iSCSI23 Smart Choice Service
	HZ4M9E	HPE 3 Year Tech Care Essential MSA iSCSI23 Smart Choice Service
	HZ4N0E	HPE 5 Year Tech Care Essential MSA iSCSI23 Smart Choice Service
<b>HPE MSA 2070 SFF iSCSI 12x3.84T Array</b>	HZ4N1E	HPE 3 Year Tech Care Basic MSA iSCSI46 Smart Choice Service
	HZ4N2E	HPE 5 Year Tech Care Basic MSA iSCSI46 Smart Choice Service
	HZ4N3E	HPE 3 Year Tech Care Essential MSA iSCSI46 Smart Choice Service
	HZ4N4E	HPE 5 Year Tech Care Essential MSA iSCSI46 Smart Choice Service



## Storage Tape Smart Choice Services

Fixed Families	Fixed SS	Long Description
<b>HPE Stg LTO8 Rack Mnt Tp 5LTO-8 30T Crtg</b>	HZ4N5E	HPE 3 Year Tech Care Basic LTO-8 Rack Smart Choice Service
	HZ4N6E	HPE 5 Year Tech Care Basic LTO-8 Rack Smart Choice Service
	HZ4N7E	HPE 3 Year Tech Care Essential LTO-8 Rack Smart Choice Service
	HZ4N8E	HPE 5 Year Tech Care Essential LTO-8 Rack Smart Choice Service
<b>HPE Stg LTO9 Rack Mnt Tp 5LTO-9 45T Crtg</b>	HZ4N9E	HPE 3 Year Tech Care Basic LTO-9 Rack Smart Choice Service
	HZ4P0E	HPE 5 Year Tech Care Basic LTO-9 Rack Smart Choice Service
	HZ4P1E	HPE 3 Year Tech Care Essential LTO-9 Rack Smart Choice Service
	HZ4P2E	HPE 5 Year Tech Care Essential LTO-9 Rack Smart Choice Service
<b>HPE MSL Tape Autoloader, MSL LTO-8 drive &amp; Media</b>	HZ4P3E	HPE 3 Year Tech Care Basic Auto+LTO-8 Smart Choice Service
	HZ4P4E	HPE 5 Year Tech Care Basic Auto+LTO-8 Smart Choice Service
	HZ4P5E	HPE 3 Year Tech Care Essential Auto+LTO-8 Smart Choice Service
	HZ4P6E	HPE 5 Year Tech Care Essential Auto+LTO-8 Smart Choice Service
<b>HPE MSL2024 Tape Library, MSL LTO-8 drive &amp; Media</b>	HZ4P7E	HPE 3 Year Tech Care Basic 2024+LTO-8 Smart Choice Service
	HZ4P8E	HPE 5 Year Tech Care Basic 2024+LTO-8 Smart Choice Service
	HZ4P9E	HPE 3 Year Tech Care Essential 2024+LTO-8 Smart Choice Service
	HZ4Q0E	HPE 5 Year Tech Care Essential 2024+LTO-8 Smart Choice Service
<b>HPE MSL3040 Tape Library, MSL LTO-9 drive &amp; Media</b>	HZ4Q1E	HPE 3 Year Tech Care Basic 3040+LTO-9 Smart Choice Service
	HZ4Q2E	HPE 5 Year Tech Care Basic 3040+LTO-9 Smart Choice Service
	HZ4Q3E	HPE 3 Year Tech Care Essential 3040+LTO-9 Smart Choice Service
	HZ4Q4E	HPE 5 Year Tech Care Essential 3040+LTO-9 Smart Choice Service



## ProLiant Gen11 Smart Choice

HPE ProLiant DL20 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P71375-425	P71682-005	P74296-205
<b>Model Name</b>	HPE ProLiant DL20 Gen11 E-2436 2.9GHz 6c 1P 32GB-DR 4SFF VROC 2x480GB SATA SSD 800W RPS EU Server	HPE ProLiant DL20 Gen11 E-2436 2.9GHz 6-core 1P 32GB-DR MR408i-o 4SFF 2x500W RPS NA Server	HPE ProLiant DL20 Gen11 E-2436 2.9GHz 6c 1P 32GB-R 4SFF 2x480GB SSD 500W PS BR Server
<b>Chassis</b>	HPE ProLiant DL20 Gen11 4SFF Hot Plug Configure-to-order Server		
<b>Processor</b>	E-2436 (6 core, 2.9 GHz, 65W)		
<b>Number of Processors</b>	One		
<b>Memory</b>	32 GB (1x32 GB UDIMM, 4800 MT/s)	32 GB (1x32 GB UDIMM, 4800 MT/s)	32 GB (2x16 GB UDIMM, 4800 MT/s)
<b>Network Controller</b>	HPE embedded 1GB 4-port BCM5719 Network Adapter		
<b>Storage Controller</b>	Embedded Intel VROC SATA software RAID <b>Notes: SATA only</b>	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller	Embedded Intel VROC SATA software RAID <b>Notes: SATA only</b>
<b>Included Drives</b>	2x 480GB SATA SSD	2x 960GB SATA SSD	2x 480GB SATA SSD
<b>Internal Storage</b>	4 SFF HDD Bays		
<b>Optical Drive</b>	Optional: DVD-ROM, DVD-RW		
<b>Expansion Slots</b>	1x PCIe 5.0 CEM slot, 1 Internal OCP Storage Controller slot, 1 External OCP 3.0 Network Controller slot		
<b>Power Supply</b>	1x HPE 800W Flex Slot Titanium Hot Plug Low Halogen Power Supply Kit	2x HPE 500W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	1x HPE 500W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit
<b>Fans</b>	3x high performance non-hot plug and non-redundant fans		
<b>Management</b>	iLO Management (standard), Intelligent Provisioning (standard) iLO Advanced (optional)		
<b>Rail Kit</b>	HPE Easy Install Rail 12 Kit		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	1U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		



## ProLiant Gen11 Smart Choice

HPE ProLiant DL20 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P75333-D65	P78087-425	P78107-295
<b>Model Name</b>	HPE ProLiant DL20 Gen11 E-2436 2.9GHz 6c 1P 32GB-DR 4SFF 960GB SSD 500W PS IN Server	HPE ProLiant DL20 Gen11 E-2434 3.4GHz 4c 1P 32GB-U 4SFF 2x480GB SATA SSD 800W PS EU Server	HPE ProLiant DL20 Gen11 E-2414 2.6GHz 4c 1P 16GB-U 2LFF 2x2TB HDD 2x500W PS JP Server
<b>Chassis</b>	HPE ProLiant DL20 Gen11 4SFF Hot Plug Configure-to-order Server	HPE ProLiant DL20 Gen11 4SFF Hot Plug Configure-to-order Server	HPE ProLiant DL20 Gen11 2LFF Hot Plug Configure-to-order Server
<b>Processor</b>	E-2436 (6 core, 2.9 GHz, 65W)		
<b>Number of Processors</b>	One		
<b>Memory</b>	32 GB (1x32 GB UDIMM, 4800 MT/s)	32 GB (1x32 GB UDIMM, 4800 MT/s)	16 GB (1x16 GB UDIMM, 4800 MT/s)
<b>Network Controller</b>	HPE embedded 1GB 4-port BCM5719 Network Adapter		
<b>Storage Controller</b>	Embedded Intel VROC SATA software RAID <b>Notes: SATA only</b>		
<b>Included Drives</b>	960GB SATA SSD	2x 480GB SATA SSD	2x 2TB SATA HDD
<b>Internal Storage</b>	4 SFF HDD Bays	4 SFF HDD Bays	2 LFF HDD Bays
<b>Optical Drive</b>	Optional: DVD-ROM, DVD-RW		
<b>Expansion Slots</b>	1x PCIe 5.0 CEM slot, 1 Internal OCP Storage Controller slot, 1 External OCP 3.0 Network Controller slot		
<b>Power Supply</b>	1x HPE 500W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	1x HPE 800W Flex Slot Titanium Hot Plug Low Halogen Power Supply Kit	2x HPE 500W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit
<b>Fans</b>	3x high performance non-hot plug and non-redundant fans		
<b>Management</b>	iLO Management (standard), Intelligent Provisioning (standard) iLO Advanced (optional)		
<b>Rail Kit</b>	HPE Easy Install Rail 12 Kit		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	1U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		



## ProLiant Gen11 Smart Choice

HPE ProLiant DL20 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P78108-295	P78109-295	P78179-425
<b>Model Name</b>	HPE ProLiant DL20 Gen11 E-2434 3.4GHz 4c 1P 32GB-U 4SFF MR408i-o 2x600GB HDD 2x500W PS JP Server	HPE ProLiant DL20 Gen11 E-2436 2.9GHz 6c 1P 32GB-U 4SFF MR408i-o 4x1.2TB HDD 2x500W PS JP Server	HPE ProLiant DL20 Gen11 E-2434 3.4GHz 4c 1P 32GB-U 2LFF 2x2TB HDD 290W PS EU Server
<b>Chassis</b>	HPE ProLiant DL20 Gen11 4SFF Hot Plug Configure-to-order Server	HPE ProLiant DL20 Gen11 4SFF Hot Plug Configure-to-order Server	HPE ProLiant DL20 Gen11 2LFF Hot Plug Configure-to-order Server
<b>Number of Processors</b>	One		
<b>Memory</b>	32 GB (1x32 GB UDIMM, 4800 MT/s)		
<b>Network Controller</b>	HPE embedded 1GB 4-port BCM5719 Network Adapter		
<b>Storage Controller</b>	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller	Embedded Intel VROC SATA software RAID <b>Notes: SATA only</b>
<b>Included Drives</b>	2x 600GB SAS HDD	4x 1.2TB SAS HDD	2x 2TB SATA HDD
<b>Internal Storage</b>	4 SFF HDD Bays	4 SFF HDD Bays	2 LFF HDD Bays
<b>Optical Drive</b>	1x SATA 9.5mm DVD-ROM Optical Drive	1x SATA 9.5mm DVD-ROM Optical Drive	Optional: DVD-ROM, DVD-RW
<b>Expansion Slots</b>	1x PCIe 5.0 CEM slot, 1 Internal OCP Storage Controller slot, 1 External OCP 3.0 Network Controller slot		
<b>Power Supply</b>	2x HPE 500W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	2x HPE 500W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	1x HPE ProLiant DL20 Gen10 Plus 290W FIO Power Supply Kit
<b>Fans</b>	3x high performance non-hot plug and non-redundant fans		
<b>Management</b>	iLO Management (standard), Intelligent Provisioning (standard) iLO Advanced (optional)		
<b>Rail Kit</b>	HPE Easy Install Rail 12 Kit		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	1U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		





## ProLiant Gen11 Smart Choice

HPE ProLiant DL145 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P79788-005	P79810-005	P79811-DM5
<b>Model Name</b>	HPE ProLiant DL145 Gen11 8024P 2.4GHz 8c 1P 1x32GB-R 2SFF NS204i-u NC BCM5719 2x700W PS NA Server	HPE ProLiant DL145 Gen11 8124P 2.45GHz 16c 1P 2x32GB-R 2SFF NS204i-u MR216i-p 2x700W PS NA Server	HPE ProLiant DL145 Gen11 8024P 2.4GHz 8c 1P 1x32GB-R 2SFF NS204i-u NC BCM5719 2x700W PS LA Server
<b>Chassis</b>	HPE ProLiant DL145 Gen11 Configure-to-order Server		
<b>Processor</b>	8024P (8 core, 2.4 GHz, 90W)	8124P (16 core, 2.45 GHz, 125W)	8024P (8 core, 2.4 GHz, 90W)
<b>Number of Processors</b>	One		
<b>Memory</b>	32 GB (1x32 GB, 4800 MT/s)	64 GB (2x32 GB, 4800 MT/s)	32 GB (1x32 GB, 4800 MT/s)
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE		
<b>Storage Controller</b>	HPE NS204i-u Gen11 NVMe Hot Plug Boot Optimized Storage Device	HPE MR216i-p Gen11 x16 Lanes without Cache PCI SPDM Plug-in Storage Controller HPE NS204i-u Gen11 NVMe Hot Plug Boot Optimized Storage Device	HPE NS204i-u Gen11 NVMe Hot Plug Boot Optimized Storage Device
<b>Included Drives</b>	None ship standard, 2 SFF supported		
<b>Expansion Slots</b>	4 x PCIe Gen5 (2 FHFL, 1 FHHL, 1OCP 3.0)		
<b>Power Supply</b>	2x HPE ProLiant DL110 700W Flex Slot Platinum Hot Plug Low Halogen AC Power Supply Kit		
<b>Fans</b>	4x Standard Fans		
<b>Management</b>	HPE iLO Standard with Intelligent Provisioning (embedded), HPE OneView Standard (requires download), HPE iLO Advanced, HPE iLO Advanced Premium Security Edition, and HPE OneView Advanced (require licenses), HPE Compute Ops Management (subscription included)		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	2U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		



## ProLiant Gen11 Smart Choice

HPE ProLiant DL145 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P79813-DM5	P79814-425	P79815-425
<b>Model Name</b>	HPE ProLiant DL145 Gen11 8124P 2.45GHz 16c 1P 2x32GB-R 2SFF NS204i-u MR216i-p 2x700W PS LA Server	HPE ProLiant DL145 Gen11 8024P 2.4GHz 8c 1P 1x32GB-R 2SFF NS204i-u NC BCM5719 2x1000W PS EMEA Server	HPE ProLiant DL145 Gen11 8124P 2.45GHz 16c 1P 2x32GB-R 2SFF NS204i-u 2x1000W PS EMEA Server
<b>Chassis</b>	HPE ProLiant DL145 Gen11 Configure-to-order Server		
<b>Processor</b>	8124P (16 core, 2.45 GHz, 125W)	8024P (8 core, 2.4 GHz, 90W)	8124P (16 core, 2.45 GHz, 125W)
<b>Number of Processors</b>	One		
<b>Memory</b>	64 GB (2x32 GB, 4800 MT/s)	32 GB (1x32 GB, 4800 MT/s)	64 GB (2x32 GB, 4800 MT/s)
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE		
<b>Storage Controller</b>	HPE MR216i-p Gen11 x16 Lanes without Cache PCI SPDM Plug-in Storage Controller HPE NS204i-u Gen11 NVMe Hot Plug Boot Optimized Storage Device	HPE NS204i-u Gen11 NVMe Hot Plug Boot Optimized Storage Device	HPE NS204i-u Gen11 NVMe Hot Plug Boot Optimized Storage Device
<b>Included Drives</b>	None ship standard, 2 SFF supported		
<b>Expansion Slots</b>	4 x PCIe Gen5 (2 FHFL, 1 FHHL, 1OCP 3.0)		
<b>Power Supply</b>	2x HPE ProLiant DL110 700W Flex Slot Platinum Hot Plug Low Halogen AC Power Supply Kit	2x HPE ProLiant DL110 900W-1000W Titanium Hot Plug AC Power Supply Kit	2x HPE ProLiant DL110 900W-1000W Titanium Hot Plug AC Power Supply Kit
<b>Fans</b>	4x Standard Fans		
<b>Management</b>	HPE iLO Standard with Intelligent Provisioning (embedded), HPE OneView Standard (requires download), HPE iLO Advanced, HPE iLO Advanced Premium Security Edition, and HPE OneView Advanced (require licenses), HPE Compute Ops Management (subscription included)		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	2U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		



## ProLiant Gen11 Smart Choice

HPE ProLiant DL320 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P69302-005	P77243-425	P78088-425
<b>Model Name</b>	HPE ProLiant DL320 Gen11 5416S 2.0GHz 16-core 1P 64GB-R 8SFF 800W PS AMS Server	HPE ProLiant DL320 Gen11 4514Y 2.0GHz 16c 64GB-R 8SFF MR408i- o 2x480GB SATA SSD 2x1000W PS EU Server	HPE ProLiant DL320 Gen11 6530 2.1GHz 32c 1P 128GB-R 10SFF MR416i-o 3x2.4TB HDD 2x1000W PS EU Server
<b>Chassis</b>	HPE ProLiant DL320 Gen11 8SFF Configure-to-order Server		
<b>Processor</b>	5416S (16 core, 2.0 GHz, 150W)	4514Y (16 core, 2.0 GHz, 150W)	6530 (32 core, 2.1 GHz, 270W)
<b>Number of Processors</b>	One with standard heatsink	One with standard heatsink	One with performance heatsink
<b>Memory</b>	64 GB (2x32 GB, 4800 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>	64 GB (2x32 GB, 5600 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>	128 GB (2x64 GB, 5600 MT/s) <b>Notes: Runs at 4800 MT/s due to processor limitation.</b>
<b>Accelerators</b>	Optional	Optional	2x NVIDIA L4 24GB PCIe Accelerator
<b>Network Controller</b>	Broadcom BCM5720 Ethernet 1Gb 2-port BASE-T Adapter		
<b>Storage Controller</b>	HPE NS204i-u Gen11 NVMe Hot Plug Boot Optimized Storage Device	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller <b>Notes: Smart Storage battery included</b>	HPE MR416i-o Gen11 x16 Lanes 8GB Cache OCP SPDM Storage Controller
<b>Included Drives</b>	None ship standard, 8 SFF supported	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD	3x HPE 2.4TB SAS 12G Mission Critical 10K SFF BC 3-year Warranty 512e HDD 2x HPE 1.92TB SATA 6G Mixed Use SFF BC Multi Vendor SSD
<b>Optical Drive</b>	None included (Optical Drive options available)	None included, optional HPE 9.5mm SATA DVD-RW Optical Drive or HPE Mobile USB DVD-RW Drive	None included, optional HPE 9.5mm SATA DVD-RW Optical Drive or HPE Mobile USB DVD-RW Drive
<b>Expansion Slots</b>	1 x16 FHHL PCIe Gen5; 1 OCP 3.0 Slot as default. 1 x16 FHHL PCIe Gen5 optional.		
<b>Power Supply</b>	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit
<b>Fans</b>	7x High Performance Fans	7x Standard Fans	7x High Performance Fans
<b>Management</b>	HPE iLO 6		
<b>Rail Kit</b>	HPE Easy Install Rail 1 Kit		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	1U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		

## ProLiant Gen11 Smart Choice

HPE ProLiant DL320 Gen11 - Smart Choice Models		
<b>SKU Number</b>	P78092-425	P78093-005
<b>Model Name</b>	HPE ProLiant DL320 Gen11 5416S 2.0GHz 16c 1P 64GB-R 10SFF MR416i-o 3x2.4TB HDD 2x1000W PS EU Server	HPE ProLiant DL320 Gen11 5416S 2.0GHz 16c 1P 64GB-R 10SFF MR416i-o 3x2.4TB HDD 2x1000W PS NA Server
<b>Chassis</b>	HPE ProLiant DL320 Gen11 8SFF Configure-to-order Server	
<b>Processor</b>	5416S (16 core, 2.0 GHz, 150W)	
<b>Number of Processors</b>	One with standard heatsink	
<b>Memory</b>	64 GB (2x32 GB, 4800 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>	
<b>Accelerators</b>	1x NVIDIA L4 24GB PCIe Accelerator	
<b>Network Controller</b>	Broadcom BCM5720 Ethernet 1Gb 2-port BASE-T Adapter	
<b>Storage Controller</b>	HPE MR416i-o Gen11 x16 Lanes 8GB Cache OCP SPDM Storage Controller	
<b>Included Drives</b>	3x HPE 2.4TB SAS 12G Mission Critical 10K SFF BC 3-year Warranty 512e HDD 2x HPE 1.92TB SATA 6G Mixed Use SFF BC Multi Vendor SSD	
<b>Optical Drive</b>	None included, optional HPE 9.5mm SATA DVD-RW Optical Drive or HPE Mobile USB DVD-RW Drive	
<b>Expansion Slots</b>	1 x16 FHHL PCIe Gen5; 1 OCP 3.0 Slot as default. 1 x16 FHHL PCIe Gen5 optional.	
<b>Power Supply</b>	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit	
<b>Fans</b>	7x High Performance Fans	
<b>Management</b>	HPE iLO 6	
<b>Rail Kit</b>	HPE Easy Install Rail 1 Kit	
<b>Security</b>	TPM (Trusted Platform Module)	
<b>Form Factor</b>	1U Rack	
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.	



## ProLiant Gen11 Smart Choice

HPE ProLiant DL320 Gen11 - Smart Choice Models		
<b>SKU Number</b>	P78100-005	P78110-295
<b>Model Name</b>	HPE ProLiant DL320 Gen11 6530 2.1GHz 32c 1P 128GB-R 10SFF MR416i-o 3x2.4TB HDD 2x1000W PS NA Server	HPE ProLiant DL320 Gen11 3408U 1.8GHz 8c 1P 16GB-R 4LFF MR408i-o 4x8TB HDD 2x500W PS JP Server
<b>Chassis</b>	HPE ProLiant DL320 Gen11 8SFF Configure-to-order Server	HPE ProLiant DL320 Gen11 4LFF Configure-to-order Server
<b>Processor</b>	6530 (32 core, 2.1 GHz, 270W)	
<b>Number of Processors</b>	One with performance heatsink	One with standard heatsink
<b>Memory</b>	128 GB (2x64 GB, 5600 MT/s) <b>Notes: Runs at 4800 MT/s due to processor limitation.</b>	16 GB (1x16 GB, 4800 MT/s) <b>Notes: Runs at 4000 MT/s due to processor limitation.</b>
<b>Accelerators</b>	2x NVIDIA L4 24GB PCIe Accelerator	Optional
<b>Network Controller</b>	Broadcom BCM5720 Ethernet 1Gb 2-port BASE-T Adapter	
<b>Storage Controller</b>	HPE MR416i-o Gen11 x16 Lanes 8GB Cache OCP SPDM Storage Controller	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller <b>Notes: Smart Storage battery included</b>
<b>Included Drives</b>	3x HPE 2.4TB SAS 12G Mission Critical 10K SFF BC 3-year Warranty 512e HDD 2x HPE 1.92TB SATA 6G Mixed Use SFF BC Multi Vendor SSD	4x HPE 8TB SATA 6G Business Critical 7.2K LFF LP 1-year Warranty 512e Multi Vendor HDD
<b>Optical Drive</b>	None included, optional HPE 9.5mm SATA DVD-RW Optical Drive or HPE Mobile USB DVD-RW Drive	
<b>Expansion Slots</b>	1 x16 FHHL PCIe Gen5; 1 OCP 3.0 Slot as default. 1 x16 FHHL PCIe Gen5 optional.	
<b>Power Supply</b>	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit	2x HPE 500W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit
<b>Fans</b>	7x High Performance Fans	
<b>Management</b>	HPE iLO 6	
<b>Rail Kit</b>	HPE Easy Install Rail 1 Kit	HPE ProLiant DL3XX Gen11 Easy Install Rail 2 Kit
<b>Security</b>	TPM (Trusted Platform Module)	
<b>Form Factor</b>	1U Rack	
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.	



## ProLiant Gen11 Smart Choice

HPE ProLiant DL325 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P72990-005	P75342-DM5	P77239-425
<b>Model Name</b>	HPE ProLiant DL325 Gen11 9354P 3.25GHz 32c 1P 256GB-R 8SFF MR408i-o 800W PS Server	HPE ProLiant DL325 Gen11 9124 3.0GHz 16c 1P 32GB-R 8SFF MR408i-o 2x480GB SATA 2x800W RPS LA Server	HPE ProLiant DL325 Gen11 9224 2.5GHz 24c 64GB-R 8SFF MR408i-o 2x480GB SATA SSD 2x1000W RPS EU Server
<b>Chassis</b>	HPE ProLiant DL325 Gen11 8SFF Configure-to-order Server		
<b>Backplane</b>		8 SFF	
<b>Processor</b>	9354P (32 core, 3.25 GHz, 280W)	9124 (16 core, 3.0 GHz, 200W)	9224 (24 core, 2.5 GHz, 200W)
<b>Number of Processors</b>	One with performance heatsink	One with standard heatsink	One with standard heatsink
<b>Memory</b>	256 GB (4x64 GB, 4800 MT/s)	32 GB (1x32 GB, 4800 MT/s)	64 GB (2x32 GB, 4800 MT/s)
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Broadcom BCM57414 Ethernet 10/25Gb 2-port SFP28 OCP3 Adapter for HPE	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE	Broadcom BCM57416 Ethernet 10Gb 2-port BASE-T OCP3 Adapter for HPE
<b>Storage Controller</b>	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller		
<b>Included Drives</b>	2x HPE 1.92TB NVMe Gen4 Mainstream Performance Read Intensive SFF BC U.3 Static V2 Multi Vendor SSD	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD
<b>Internal Storage</b>	8 SFF Chassis (upgradeable to 10 SFF front)		
<b>Optical Drive</b>	Optional, None ship standard		
<b>Expansion Slots</b>	1 PCIe x16 Primary Riser		
<b>Power Supply</b>	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit
<b>Fans</b>	7x Performance Fans	7x Standard Fans	7x Standard Fans
<b>Management</b>	Default: HPE iLO Standard with Intelligent Provisioning, HPE OneView Standard (requires download)		
<b>Rail Kit</b>	HPE ProLiant DL3XX Gen11 Easy Install Rail 2 Kit		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Energy Star</b>	4.0 certified		
<b>Form Factor</b>	1U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		

## ProLiant Gen11 Smart Choice

HPE ProLiant DL325 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P77246-005	P77252-425	P79763-375
<b>Model Name</b>	HPE ProLiant DL325 Gen11 9124 3.0GHz 16c 64GB-R 8SFF MR408i-o 2x480GB SATA SSD 2x500W RPS NA Server	HPE ProLiant DL325 Gen11 9124 3.0GHz 16c 64GB-R 8SFF MR408i-o 2x480GB SATA SSD 2x1000W RPS EU Server	HPE ProLiant DL325 Gen11 9224 2.5GHz 24c 1P 4x32GB-R 8SFF NS204i-u MR408i-o 2x800W PS AP Server
<b>Chassis</b>	HPE ProLiant DL325 Gen11 8SFF Configure-to-order Server		
<b>Processor</b>	9124 (16 core, 3.0 GHz, 200W)	9124 (16 core, 3.0 GHz, 200W)	9224 (24 core, 2.5 GHz, 200W)
<b>Number of Processors</b>	One with standard heatsink		
<b>Memory</b>	64 GB (2x32 GB, 4800 MT/s)	64 GB (2x32 GB, 4800 MT/s)	128 GB (4x32 GB, 4800 MT/s)
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Broadcom BCM57416 Ethernet 10Gb 2-port BASE-T OCP3 Adapter for HPE	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE	Broadcom BCM57416 Ethernet 10Gb 2-port BASE-T OCP3 Adapter for HPE
<b>Storage Controller</b>	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller	HPE NS204i-u Gen11 NVMe Hot Plug Boot Optimized Storage Device HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller
<b>Included Drives</b>	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD	None ship standard, 8 SFF supported
<b>Optical Drive</b>	Optional, None ship standard		
<b>Expansion Slots</b>	1 PCIe x16 Primary Riser		
<b>Power Supply</b>	2x HPE 500W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit
<b>Fans</b>	7x Standard Fans	7x Standard Fans	7x Performance Fans
<b>Management</b>	Default: HPE iLO Standard with Intelligent Provisioning, HPE OneView Standard (requires download)		
<b>Rail Kit</b>	HPE ProLiant DL3XX Gen11 Easy Install Rail 2 Kit	HPE ProLiant DL3XX Gen11 Easy Install Rail 2 Kit	
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	1U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		



## ProLiant Gen11 Smart Choice

HPE ProLiant DL345 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P75332-005	P77238-425	P77248-425
<b>Model Name</b>	HPE ProLiant DL345 Gen11 9354P 3.25GHz 32c 1P 256GB-R 8SFF MR416i-p 2x1.92TB SSD 2x800W PS NA Server	HPE ProLiant DL345 Gen11 9124 3.0GHz 16c 64GB-R 8SFF MR416i-p 2x480GB SATA SSD 2x1000W RPS EU Server	HPE ProLiant DL345 Gen11 9124 3.0GHz 16c 64GB-R 8LFF MR416i-p 2x960GB SATA SSD 2x1000W RPS EU Server
<b>Chassis</b>	HPE ProLiant DL345 Gen11 8SFF Configure-to-order Server	HPE ProLiant DL345 Gen11 8SFF Configure-to-order Server	HPE ProLiant DL345 Gen11 8LFF Configure-to-order Server
<b>Backplane</b>	2x 8SFF		
<b>Processor</b>	9354P (32 core, 3.25 GHz, 280W)	9124 (16 core, 3.0 GHz, 200W)	9124 (16 core, 3.0 GHz, 200W)
<b>Number of Processors</b>	One with performance heatsink	One with standard heatsink	One with standard heatsink
<b>Memory</b>	256 GB (4x64 GB, 4800 MT/s)	64 GB (2x32 GB, 4800 MT/s)	64 GB (2x32 GB, 4800 MT/s)
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	1x Broadcom BCM57414 Ethernet 10/25Gb 2-port SFP28 OCP3 Adapter for HPE 1x Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE
<b>Storage Controller</b>	HPE MR416i-p Gen11 x16 Lanes 8GB Cache PCI SPDM Plug-in Storage Controller		
<b>Included Drives</b>	2x HPE 1.92TB NVMe Gen4 Mainstream Performance Read Intensive SFF BC U.3 Static V2 Multi Vendor SSD	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD	2x HPE 960GB SATA 6G Read Intensive LFF LPC Multi Vendor SSD
<b>Expansion Slots</b>	2 PCIe x16 Riser (Primary slot 3 and Secondary slot 6)		
<b>Power Supply</b>	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit
<b>Fans</b>	6x Standard Fans		
<b>Management</b>	Default: HPE iLO Standard with Intelligent Provisioning, HPE OneView Standard (requires download)		
<b>Rail Kit</b>	HPE ProLiant DL3XX Gen11 Easy Install Rail 2 Kit		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	2U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		





## ProLiant Gen11 Smart Choice

HPE ProLiant DL360 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P71673-425	P71676-005	P71678-005
<b>Model Name</b>	HPE ProLiant DL360 Gen11 4510 2.4GHz 12c 1P 64GB-R 8SFF MR408i-o 2x960GB SSD 2x1000W PS EMEA Server	HPE ProLiant DL360 Gen11 4509Y 2.6GHz 8-core 1P 64GB-R MR408i- o NC 8SFF 1000W RPS AMS Server	HPE ProLiant DL360 Gen11 6526Y 2.8GHz 16-core 1P 128GB-R NS204i-u NC 8SFF 1000W RPS AMS Server
<b>Chassis</b>	HPE ProLiant DL360 Gen11 8SFF NC Configure-to-order Server		
<b>Processor</b>	4510 (12 core, 2.4 GHz, 150W)	4509Y (8 core, 2.6 GHz, 125W)	6526Y (16 core, 2.8 GHz, 195W)
<b>Number of Processors</b>	One with standard heatsink	One with standard heatsink	One with high performance heatsink
<b>Memory</b>	64 GB (2x32 GB, 5600 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>	64 GB (2x32 GB, 5600 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>	128 GB (4x32 GB, 5600 MT/s) <b>Notes: Runs at 5200 MT/s due to processor limitation.</b>
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE <b>Notes: No embedded networking</b>		
<b>Storage Controller</b>	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller	HPE NS204i-u Gen11 NVMe Hot Plug Boot Optimized Storage Device <b>Notes: Internal, without hot-plug capability.</b>
<b>Included Drives</b>	2x HPE 960GB SATA 6G Read Intensive SFF BC Multi Vendor SSD	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD	None ship standard, 8 SFF supported
<b>Optical Drive</b>	Optional - HPE 9.5mm SATA DVD-RW Optical Drive, HPE Mobile USB DVD-RW Drive.		
<b>Power Supply</b>	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit		
<b>Fans</b>	5x Standard Fans	5x Standard Fans	7x High Performance Fans
<b>Management</b>	HPE iLO 6		
<b>Rail Kit</b>	HPE ProLiant DL3XX Gen11 Easy Install Rail 3 Kit <b>Notes: Server does not support shelf mounted rail kits ("L" brackets).</b>		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	1U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		



## ProLiant Gen11 Smart Choice

HPE ProLiant DL360 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P71686-005	P72985-005	P72987-005
<b>Model Name</b>	HPE ProLiant DL360 Gen11 4510 2.4GHz 12-core 1P 64GB-R MR408i-o NC 8SFF 1000W RPS AMS Server	HPE ProLiant DL360 Gen11 4514Y 2.0GHz 16c 128GB-R 8SFF MR408i-o 2x1.2TB HDD NC 2x1000W RPS NA Server	HPE ProLiant DL360 Gen11 4510 2.4GHz 12c 64GB-R 8SFF MR408i- o 2x1.2TB HDD NC 2x1000W RPS NA Server
<b>Chassis</b>	HPE ProLiant DL360 Gen11 8SFF NC Configure-to-order Server		
<b>Processor</b>	4510 (12 core, 2.4 GHz, 150W)	4514Y (16 core, 2.0 GHz, 150W)	4510 (12 core, 2.4 GHz, 150W)
<b>Number of Processors</b>	One with standard heatsink		
<b>Memory</b>	64 GB (2x32 GB, 5600 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>	128 GB (4x32 GB, 5600 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>	64 GB (2x32 GB, 5600 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE <b>Notes: No embedded networking</b>		
<b>Storage Controller</b>	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller		
<b>Included Drives</b>	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD	2x HPE 1.2TB SAS 12G Mission Critical 10K SFF BC 3-year Warranty HDD	2x HPE 1.2TB SAS 12G Mission Critical 10K SFF BC 3-year Warranty HDD
<b>Optical Drive</b>	Optional - HPE 9.5mm SATA DVD-RW Optical Drive, HPE Mobile USB DVD-RW Drive.		
<b>Power Supply</b>	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit		
<b>Fans</b>	5x Standard Fans		
<b>Management</b>	HPE iLO 6		
<b>Rail Kit</b>	HPE ProLiant DL3XX Gen11 Easy Install Rail 3 Kit <b>Notes: Server does not support shelf mounted rail kits ("L" brackets).</b>		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	1U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		



## ProLiant Gen11 Smart Choice

HPE ProLiant DL360 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P72992-005	P72993-005	P72994-005
<b>Model Name</b>	HPE ProLiant DL360 Gen11 4514Y 2.0GHz 16c 128GB-R 8SFF MR408i-o 2x960GB SSD NC 2x1000W RPS NA Server	HPE ProLiant DL360 Gen11 4516Y+ 2.2GHz 24c 1P 128GB-R 8SFF NS204i-u NC 2x1000W RPS NA Server	HPE ProLiant DL360 Gen11 6530 2.1GHz 32c 1P 128GB-R 8SFF NS204i-u NC 2x1000W RPS NA Server
<b>Chassis</b>	HPE ProLiant DL360 Gen11 8SFF NC Configure-to-order Server		
<b>Processor</b>	4514Y (16 core, 2.0 GHz, 150W)	4516Y+ (24 core, 2.2 GHz, 185W)	6530 (32 core, 2.1 GHz, 270W)
<b>Number of Processors</b>	One with standard heatsink	One with high performance heatsink	One with high performance heatsink
<b>Memory</b>	128 GB (4x32 GB, 5600 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>	128 GB (2x64 GB, 5600 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>	128 GB (2x64 GB, 5600 MT/s) <b>Notes: Runs at 4800 MT/s due to processor limitation.</b>
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE <b>Notes: No embedded networking</b>		
<b>Storage Controller</b>	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller	HPE NS204i-u Gen11 NVMe Hot Plug Boot Optimized Storage Device <b>Notes: Internal, without hot-plug capability.</b>	HPE NS204i-u Gen11 NVMe Hot Plug Boot Optimized Storage Device <b>Notes: Internal, without hot-plug capability.</b>
<b>Included Drives</b>	2x HPE 960GB SATA 6G Mixed Use SFF BC Multi Vendor SSD	None ship standard, 8 SFF supported	None ship standard, 8 SFF supported
<b>Optical Drive</b>	Optional - HPE 9.5mm SATA DVD-RW Optical Drive, HPE Mobile USB DVD-RW Drive.		
<b>Power Supply</b>	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit		
<b>Fans</b>	5x Standard Fans	7x High Performance Fans	7x High Performance Fans
<b>Management</b>	HPE iLO 6		
<b>Rail Kit</b>	HPE ProLiant DL3XX Gen11 Easy Install Rail 3 Kit <b>Notes: Server does not support shelf mounted rail kits ("L" brackets).</b>		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	1U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		



## ProLiant Gen11 Smart Choice

HPE ProLiant DL360 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P74291-205	P74292-205	P74651-D65
<b>Model Name</b>	HPE ProLiant DL360 Gen11 4410Y 2.0GHz 12c 1P 32GB-R 8SFF MR408i-o 2x1.2TB HDD 2x800W RPS BR Server	HPE ProLiant DL360 Gen11 4410Y 2.0GHz 12c 2P 64GB-R 8SFF MR408i-o 2x480GB SSD 2x800W RPS BR Server	HPE ProLiant DL360 Gen11 4510 2.4GHz 12c 1P 64GB-R 8SFF MR408i-o 2x960GB SSD 2x1000W RPS IN Server
<b>Chassis</b>	HPE ProLiant DL360 Gen11 8SFF NC Configure-to-order Server		
<b>Processor</b>	4410Y (12 core, 2.0 GHz, 150W)	4410Y (12 core, 2.0 GHz, 150W)	4510 (12 core, 2.4 GHz, 150W)
<b>Number of Processors</b>	One with standard heatsink	Two with standard heatsink	One with standard heatsink
<b>Memory</b>	32 GB (1x32 GB, 4800 MT/s) <b>Notes: Runs at 4000 MT/s due to processor limitation.</b>	64 GB (2x32 GB, 4800 MT/s) <b>Notes: Runs at 4000 MT/s due to processor limitation.</b>	64 GB (1x64 GB, 5600 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE <b>Notes: No embedded networking</b>		
<b>Storage Controller</b>	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller		
<b>Included Drives</b>	2x HPE 1.2TB SAS 12G Mission Critical 10K SFF BC 3-year Warranty HDD	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD	2x HPE 960GB SATA 6G Read Intensive SFF BC Multi Vendor SSD
<b>Optical Drive</b>	Optional - HPE 9.5mm SATA DVD-RW Optical Drive, HPE Mobile USB DVD-RW Drive.		
<b>Power Supply</b>	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit
<b>Fans</b>	5x Standard Fans	7x Standard Fans	5x Standard Fans
<b>Management</b>	HPE iLO 6		
<b>Rail Kit</b>	HPE ProLiant DL3XX Gen11 Easy Install Rail 3 Kit <b>Notes: Server does not support shelf mounted rail kits ("L" brackets).</b>		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	1U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		



## ProLiant Gen11 Smart Choice

HPE ProLiant DL360 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P74653-D65	P75343-DM5	P77236-425
<b>Model Name</b>	HPE ProLiant DL360 Gen11 4514Y 2.0GHz 16c 1P 128GB-R 8SFF MR408i-o 2x960GB SSD NC 1000W PS IN Server	HPE ProLiant DL360 Gen11 4410Y 2.0GHz 12c 1P 64GB-R 8SFF MR408i-o 2x960GB SSD 2x1000W RPS LA Server	HPE ProLiant DL360 Gen11 4514Y 2.0GHz 16c 1P 128GB-R 8SFF NS204i-u NC BCM57416 2x1000W PS EU Server
<b>Chassis</b>	HPE ProLiant DL360 Gen11 8SFF NC Configure-to-order Server		
<b>Processor</b>	4514Y (16 core, 2.0 GHz, 150W)	4410Y (12 core, 2.0 GHz, 150W)	4514Y (16 core, 2.0 GHz, 150W)
<b>Number of Processors</b>	One with high performance heatsink	One with standard heatsink	One with high performance heatsink
<b>Memory</b>	128 GB (2x64 GB, 5600 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>	64 GB (2x32 GB, 4800 MT/s) <b>Notes: Runs at 4000 MT/s due to processor limitation.</b>	128 GB (4x32 GB, 5600 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE <b>Notes: No embedded networking</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE <b>Notes: No embedded networking</b>	Broadcom BCM57416 Ethernet 10Gb 2-port BASE-T Adapter for HPE <b>Notes: No embedded networking</b>
<b>Storage Controller</b>	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller	HPE NS204i-u Gen11 NVMe Hot Plug Boot Optimized Storage Device <b>Notes: Internal, without hot-plug capability.</b>
<b>Included Drives</b>	2x HPE 960GB SATA 6G Read Intensive SFF BC Multi Vendor SSD	2x HPE 960GB SATA 6G Mixed Use SFF BC Multi Vendor SSD	None ship standard, 8 SFF supported
<b>Optical Drive</b>	Optional - HPE 9.5mm SATA DVD-RW Optical Drive, HPE Mobile USB DVD-RW Drive.		
<b>Power Supply</b>	1x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit
<b>Fans</b>	7x High Performance Fans	5x Standard Fans	7x High Performance Fans
<b>Management</b>	HPE iLO 6		
<b>Rail Kit</b>	HPE ProLiant DL3XX Gen11 Easy Install Rail 3 Kit <b>Notes: Server does not support shelf mounted rail kits ("L" brackets).</b>		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	1U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		



## ProLiant Gen11 Smart Choice

HPE ProLiant DL360 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P77237-425	P77247-425	P79764-375
<b>Model Name</b>	HPE ProLiant DL360 Gen11 4514Y 2.0GHz 16c 64GB-R 8SFF MR408i-o 2x480GB SATA SSD 2x1000W PS EU Server	HPE ProLiant DL360 Gen11 4510 2.4GHz 12c 1P 64GB-R 8SFF MR408i-o 2x2.4TB HDD 2x1000W PS EU Server	HPE ProLiant DL360 Gen11 4514Y 2.0GHz 16c 2P 4x16GB-R 8SFF MR408i-o 2x600GB HDD 2x800W PS AP Server
<b>Chassis</b>	HPE ProLiant DL360 Gen11 8SFF NC Configure-to-order Server		
<b>Processor</b>	4514Y (16 core, 2.0 GHz, 150W)	4510 (12 core, 2.4 GHz, 150W)	4514Y (16 core, 2.0 GHz, 150W)
<b>Number of Processors</b>	One with standard heatsink	One with standard heatsink	Two with standard heatsink
<b>Memory</b>	64 GB (2x32 GB, 5600 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>	64 GB (2x32 GB, 5600 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>	64 GB (4x16 GB, 5600 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Broadcom BCM57416 Ethernet 10Gb 2-port BASE-T Adapter for HPE <b>Notes: No embedded networking</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE <b>Notes: No embedded networking</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE <b>Notes: No embedded networking</b>
<b>Storage Controller</b>	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller		
<b>Included Drives</b>	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD	2x HPE 2.4TB SAS 12G Mission Critical 10K SFF BC 3-year Warranty 512e HDD	2x HPE 600GB SAS 12G Mission Critical 10K SFF BC 3-year Warranty Multi Vendor HDD
<b>Optical Drive</b>	Optional - HPE 9.5mm SATA DVD-RW Optical Drive, HPE Mobile USB DVD-RW Drive.		
<b>Power Supply</b>	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit
<b>Fans</b>	5x Standard Fans	5x Standard Fans	7x Standard Fans
<b>Management</b>	HPE iLO 6		
<b>Rail Kit</b>	HPE ProLiant DL3XX Gen11 Easy Install Rail 3 Kit <b>Notes: Server does not support shelf mounted rail kits ("L" brackets).</b>		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	1U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		



## ProLiant Gen11 Smart Choice

HPE ProLiant DL365 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P77249-005	P78090-425	P78091-425
<b>Model Name</b>	HPE ProLiant DL365 Gen11 9354 3.25GHz 32c 2P 384GB-R 8SFF NS204i-u NC BCM57414 2x1000W PS NA Server	HPE ProLiant DL365 Gen11 9124 3.0GHz 16c 64GB-R 8SFF MR408i-o 2x480GB SATA SSD 2x1000W PS EU Server	HPE ProLiant DL365 Gen11 9224 2.5GHz 24c 64GB-R 8SFF MR408i-o 2x480GB SATA SSD 2x1000W PS EU Server
<b>Chassis</b>	HPE ProLiant DL365 Gen11 8SFF Configure-to-order Server		
<b>Processor</b>	9354 (32 core, 3.25 GHz, 280W)	9124 (16 core, 3.0 GHz, 200W)	9224 (24 core, 2.5 GHz, 200W)
<b>Number of Processors</b>	Two with performance heatsink	One with standard heatsink	One with standard heatsink
<b>Memory</b>	384 GB (24x16 GB, 4800 MT/s)	64 GB (2x32 GB, 4800 MT/s)	64 GB (2x32 GB, 4800 MT/s)
<b>Network Controller</b>	1x Broadcom BCM57414 Ethernet 10/25Gb 2-port SFP28 OCP3 Adapter for HPE 1x Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE	Broadcom BCM57416 Ethernet 10Gb 2-port BASE-T OCP3 Adapter for HPE	Broadcom BCM57416 Ethernet 10Gb 2-port BASE-T OCP3 Adapter for HPE
<b>Storage Controller</b>	HPE NS204i-u Gen11 NVMe Hot Plug Boot Optimized Storage Device	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller
<b>Included Drives</b>	None ship standard, 8 SFF supported	2x 480GB SATA SSD	2x 480GB SATA SSD
<b>Optical Drive</b>	Optional: 9.5mm SATA DVD-ROM/RW Optical Drive		
<b>Power Supply</b>	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit		
<b>Fans</b>	7x Performance Fans	7x Standard Fans	7x Standard Fans
<b>Rail Kit</b>	HPE ProLiant DL3XX Gen11 Easy Install Rail 2 Kit		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	1U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		



## ProLiant Gen11 Smart Choice

HPE ProLiant DL380 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P71674-425	P71675-425	P71679-005
<b>Model Name</b>	HPE ProLiant DL380 Gen11 4510 2.4GHz 12c 1P 64GB-R 8SFF MR408i-o 2x960GB SSD 2x1000W PS EMEA Server	HPE ProLiant DL380 Gen11 4510 2.4GHz 12c 64GB-R 12LFF MR416i-p 2x8TB SATA HDD 2x1000W PS EMEA Server	HPE ProLiant DL380 Gen11 4510 12-core 1P 64GB-R MR408i-o NC BCM5719 8SFF 2x1000W RPS NA Server
<b>Chassis</b>	HPE ProLiant DL380 Gen11 8SFF NC Configure-to-order Server	HPE ProLiant DL380 Gen11 12LFF NC Configure-to-order Server	HPE ProLiant DL380 Gen11 8SFF NC Configure-to-order Server
<b>Processor</b>	4510 (12 core, 2.4 GHz, 150W)		
<b>Number of Processors</b>	One		
<b>Memory</b>	64 GB (2x32 GB, 5600 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>		
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE		
<b>Storage Controller</b>	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller	HPE MR416i-p Gen11 x16 Lanes 8GB Cache PCI SPDM Plug-in Storage Controller	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller
<b>Included Drives</b>	2x HPE 960GB SATA 6G Read Intensive SFF BC Multi Vendor SSD	2x HPE 8TB SATA 6G Business Critical 7.2K LFF LP 1-year Warranty 512e Multi Vendor HDD	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD
<b>Optical Drive</b>	Optional DVD-ROM Optional via Universal Media Bay External support only		
<b>Expansion Slots</b>	3-slots (x8, x16, x8) as standard; upgradeable to 8-slots in a 2 processor configuration		
<b>Power Supply</b>	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit		
<b>Fans</b>	4x Standard Fans	4x Standard Fan	4x Standard Fans
<b>Management</b>	HPE iLO 6		
<b>Rail Kit</b>	HPE ProLiant DL3XX Gen11 Easy Install Rail 3 Kit		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	2U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		





## ProLiant Gen11 Smart Choice

HPE ProLiant DL380 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P71680-005	P71681-005	P72981-005
<b>Model Name</b>	HPE ProLiant DL380 Gen11 4509Y 8-core 1P 64GB-R MR408i-o NC BCM5719 8SFF 2x1000W RPS NA Server	HPE ProLiant DL380 Gen11 6526Y 16-core 1P 128GB-R NS204i-u NC BCM5719 8SFF 2x1000W RPS NA Server	HPE ProLiant DL380 Gen11 4510 2.4GHz 12c 1P 64GB-R 12LFF MR416i-o 2x8TB HDD 2x1000W PS NA Server
<b>Chassis</b>	HPE ProLiant DL380 Gen11 8SFF NC Configure-to-order Server	HPE ProLiant DL380 Gen11 8SFF NC Configure-to-order Server	HPE ProLiant DL380 Gen11 12LFF NC Configure-to-order Server
<b>Processor</b>	4509Y (8 core, 2.6 GHz, 125W)	6526Y (16 core, 2.8 GHz, 195W)	4510 (12 core, 2.4 GHz, 150W)
<b>Number of Processors</b>	One	One with high performance heatsink	One
<b>Memory</b>	64 GB (2x32 GB, 5600 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>	128 GB (4x32 GB, 5600 MT/s) <b>Notes: Runs at 5200 MT/s due to processor limitation.</b>	64 GB (2x32 GB, 5600 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE		
<b>Storage Controller</b>	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller	HPE NS204i-u Gen11 NVMe Hot Plug Boot Optimized Storage Device	HPE MR416i-o Gen11 x16 Lanes 8GB Cache OCP SPDM Storage Controller
<b>Included Drives</b>	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD	None ship standard, 8 SFF supported	2x HPE 8TB SATA 6G Business Critical 7.2K LFF LP 1-year Warranty 512e Multi Vendor HDD
<b>Optical Drive</b>	Optional DVD-ROM Optional via Universal Media Bay External support only		
<b>Expansion Slots</b>	3-slots (x8, x16, x8) as standard; upgradeable to 8-slots in a 2 processor configuration		
<b>Power Supply</b>	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit		
<b>Fans</b>	4x Standard Fans	6x High Performance Fan	4x Standard Fans
<b>Management</b>	HPE iLO 6		
<b>Rail Kit</b>	HPE ProLiant DL3XX Gen11 Easy Install Rail 3 Kit		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	2U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		



## ProLiant Gen11 Smart Choice

HPE ProLiant DL380 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P72982-005	P72983-005	P72984-005
<b>Model Name</b>	HPE ProLiant DL380 Gen11 4514Y 2.0GHz 16c 1P 128GB-R 8SFF MR408i-o 2x480GB SSD 2x1000W PS NA Server	HPE ProLiant DL380 Gen11 4510 2.4GHz 12c 1P 64GB-R 8SFF MR408i-o 2x2.4TB HDD 2x1000W PS NA Server	HPE ProLiant DL380 Gen11 4514Y 2.0GHz 16c 1P 128GB-R 8SFF MR408i-o 2x2.4TB HDD 2x1000W PS NA Server
<b>Chassis</b>	HPE ProLiant DL380 Gen11 8SFF NC Configure-to-order Server		
<b>Processor</b>	4514Y (16 core, 2.0 GHz, 150W)	4510 (12 core, 2.4 GHz, 150W)	4514Y (16 core, 2.0 GHz, 150W)
<b>Number of Processors</b>	One		
<b>Memory</b>	128 GB (4x32 GB, 5600 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>	64 GB (2x32 GB, 5600 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>	128 GB (4x32 GB, 5600 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE		
<b>Storage Controller</b>	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller		
<b>Included Drives</b>	2x HPE 480GB SATA 6G Mixed Use SFF BC Multi Vendor SSD	2x HPE 2.4TB SAS 12G Mission Critical 10K SFF BC 3-year Warranty 512e HDD	2x HPE 2.4TB SAS 12G Mission Critical 10K SFF BC 3-year Warranty 512e HDD
<b>Optical Drive</b>	Optional DVD-ROM Optional via Universal Media Bay External support only		
<b>Expansion Slots</b>	3-slots (x8, x16, x8) as standard; upgradeable to 8-slots in a 2 processor configuration		
<b>Power Supply</b>	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit		
<b>Fans</b>	4x Standard Fans		
<b>Management</b>	HPE iLO 6		
<b>Rail Kit</b>	HPE ProLiant DL3XX Gen11 Easy Install Rail 3 Kit		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	2U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		



## ProLiant Gen11 Smart Choice

HPE ProLiant DL380 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P74293-205	P74294-205	P74295-205
<b>Model Name</b>	HPE ProLiant DL380 Gen11 4410Y 2.0GHz 12c 1P 32GB-DR 8SFF MR408i-o 2x1.2TB HDD 2x800W RPS BR Server	HPE ProLiant DL380 Gen11 4416+ 2.0GHz 20c 1P 32GB-DR 8SFF MR408i-o 2x480GB SSD 2x800W RPS BR Server	HPE ProLiant DL380 Gen11 4410Y 2.0GHz 12c 1P 32GB-DR 12LFF MR416i-o 2x4TB HDD 2x800W RPS BR Server
<b>Chassis</b>	HPE ProLiant DL380 Gen11 8SFF NC Configure-to-order Server	HPE ProLiant DL380 Gen11 8SFF NC Configure-to-order Server	HPE ProLiant DL380 Gen11 12LFF NC Configure-to-order Server
<b>Processor</b>	4410Y (12 core, 2.0 GHz, 150W)	4416+ (20 core, 2.0 GHz, 165W)	4410Y (12 core, 2.0 GHz, 150W)
<b>Number of Processors</b>	One	One with high performance heatsink	One
<b>Memory</b>	32 GB (1x32 GB, 4800 MT/s) <b>Notes: Runs at 4000 MT/s due to processor limitation.</b>		
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE		
<b>Storage Controller</b>	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller	HPE MR416i-o Gen11 x16 Lanes 8GB Cache OCP SPDM Storage Controller
<b>Included Drives</b>	2x HPE 1.2TB SAS 12G Mission Critical 10K SFF BC 3-year Warranty HDD	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD	2x HPE 4TB SATA 6G Business Critical 7.2K LFF LP 1-year Warranty Multi Vendor HDD
<b>Optical Drive</b>	Optional DVD-ROM Optional via Universal Media Bay External support only		
<b>Expansion Slots</b>	3-slots (x8, x16, x8) as standard; upgradeable to 8-slots in a 2 processor configuration		
<b>Power Supply</b>	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit		
<b>Fans</b>	4x Standard Fan		
<b>Management</b>	HPE iLO 6		
<b>Rail Kit</b>	HPE ProLiant DL3XX Gen11 Easy Install Rail 3 Kit		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	2U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		



## ProLiant Gen11 Smart Choice

HPE ProLiant DL380 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P74648-D65	P74649-D65	P75344-DM5
<b>Model Name</b>	HPE ProLiant DL380 Gen11 4510 2.4GHz 12c 1P 64GB-R 8SFF MR416i-o 2x960GB SSD 2x1000W RPS IN Server	HPE ProLiant DL380 Gen11 4514Y 2.0GHz 16c 1P 64GB-R 8SFF MR416i-o 2x960GB SSD 2x1000W RPS IN Server	HPE ProLiant DL380 Gen11 4410Y 2.0GHz 12c 1P 32GB-R 12LFF MR416i-o 2x4TB HDD 2x1000W RPS LA Server
<b>Chassis</b>	HPE ProLiant DL380 Gen11 8SFF NC Configure-to-order Server	HPE ProLiant DL380 Gen11 8SFF NC Configure-to-order Server	HPE ProLiant DL380 Gen11 12LFF NC Configure-to-order Server
<b>Processor</b>	4510 (12 core, 2.4 GHz, 150W)	4514Y (16 core, 2.0 GHz, 150W)	4410Y (12 core, 2.0 GHz, 150W)
<b>Number of Processors</b>	One		
<b>Memory</b>	64 GB (1x64 GB, 5600 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>	64 GB (1x64 GB, 5600 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>	32 GB (1x32 GB, 4800 MT/s) <b>Notes: Runs at 4000 MT/s due to processor limitation.</b>
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE		
<b>Storage Controller</b>	HPE MR416i-o Gen11 x16 Lanes 8GB Cache OCP SPDM Storage Controller		
<b>Included Drives</b>	2x HPE 960GB SATA 6G Read Intensive SFF BC Multi Vendor SSD	2x HPE 960GB SATA 6G Read Intensive SFF BC Multi Vendor SSD	2x HPE 4TB SATA 6G Business Critical 7.2K LFF LP 1-year Warranty Multi Vendor HDD
<b>Optical Drive</b>	Optional DVD-ROM Optional via Universal Media Bay External support only		
<b>Expansion Slots</b>	3-slots (x8, x16, x8) as standard; upgradeable to 8-slots in a 2 processor configuration		
<b>Power Supply</b>	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit		
<b>Fans</b>	4x Standard Fans		
<b>Management</b>	HPE iLO 6		
<b>Rail Kit</b>	HPE ProLiant DL3XX Gen11 Easy Install Rail 3 Kit		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	2U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		



## ProLiant Gen11 Smart Choice

HPE ProLiant DL380 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P75345-DM5	P77235-425	P77241-425
<b>Model Name</b>	HPE ProLiant DL380 Gen11 5418Y 2.0GHz 24c 1P 64GB-R 8SFF NS204i-u 2x1000W RPS LA Server	HPE ProLiant DL380 Gen11 4514Y 2.0GHz 16c 1P 64GB-R 8SFF MR416i-o 2x2.4TB HDD 2x1000W PS EU Server	HPE ProLiant DL380 Gen11 6526Y 2.8GHz 16c 1P 128GB-R 8SFF NS204i-u NC BCM57416 2x1000W PS EU Server
<b>Chassis</b>	HPE ProLiant DL380 Gen11 8SFF NC Configure-to-order Server		
<b>Processor</b>	5418Y (24 core, 2.0 GHz, 185W)	4514Y (16 core, 2.0 GHz, 150W)	6526Y (16 core, 2.80 GHz, 195W)
<b>Number of Processors</b>	One with high performance heatsink	One	One with high performance heatsink
<b>Memory</b>	64 GB (2x32 GB, 4800 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>	64 GB (2x32 GB, 5600 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>	128 GB (4x32 GB, 5600 MT/s) <b>Notes: Runs at 5200 MT/s due to processor limitation.</b>
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Broadcom BCM57416 Ethernet 10Gb 2-port BASE-T Adapter for HPE		
<b>Storage Controller</b>	HPE NS204i-u Gen11 NVMe Hot Plug Boot Optimized Storage Device	HPE MR416i-o Gen11 x16 Lanes 8GB Cache OCP SPDM Storage Controller	HPE NS204i-u Gen11 NVMe Hot Plug Boot Optimized Storage Device
<b>Included Drives</b>	None ship standard, 8 SFF supported	2x HPE 2.4TB SAS 12G Mission Critical 10K SFF BC 3-year Warranty 512e HDD	None ship standard, 8 SFF supported
<b>Optical Drive</b>	Optional DVD-ROM Optional via Universal Media Bay External support only		
<b>Expansion Slots</b>	3-slots (x8, x16, x8) as standard; upgradeable to 8-slots in a 2 processor configuration		
<b>Power Supply</b>	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit		
<b>Fans</b>	6x High Performance Fan	4x Standard Fans	6x High Performance Fan
<b>Management</b>	HPE iLO 6		
<b>Rail Kit</b>	HPE ProLiant DL3XX Gen11 Easy Install Rail 3 Kit		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	2U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		



## ProLiant Gen11 Smart Choice

HPE ProLiant DL380 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P77242-425	P79768-375	P79769-375
<b>Model Name</b>	HPE ProLiant DL380 Gen11 4514Y 2.0GHz 16c 1P 128GB-R 8SFF NS204i-u NC BCM57416 2x1000W PS EU Server	HPE ProLiant DL380 Gen11 4509Y 2.6GHz 8c 2P 4x16GB-R 8SFF MR408i-o 5x600GB HDD 2x800W PS AP Server	HPE ProLiant DL380 Gen11 4514Y 2.0GHz 16c 2P 4x16GB-R 8SFF MR408i-o 5x600GB HDD 2x800W PS AP Server
<b>Chassis</b>	HPE ProLiant DL380 Gen11 8SFF NC Configure-to-order Server		
<b>Processor</b>	4514Y (16 core, 2.0 GHz, 150W)		4514Y (16 core, 2.0 GHz, 150W)
<b>Number of Processors</b>	One	Two	Two
<b>Memory</b>	128 GB (4x32 GB, 5600 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>	64 GB (4x16 GB, 5600 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>	64 GB (4x16 GB, 5600 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Broadcom BCM57416 Ethernet 10Gb 2-port BASE-T Adapter for HPE	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE
<b>Storage Controller</b>	HPE NS204i-u Gen11 NVMe Hot Plug Boot Optimized Storage Device	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller
<b>Included Drives</b>	None ship standard, 8 SFF supported	5x HPE 600GB SAS 12G Mission Critical 10K SFF BC 3-year Warranty Multi Vendor HDD	5x HPE 600GB SAS 12G Mission Critical 10K SFF BC 3-year Warranty Multi Vendor HDD
<b>Optical Drive</b>	Optional DVD-ROM Optional via Universal Media Bay External support only		
<b>Expansion Slots</b>	3-slots (x8, x16, x8) as standard; upgradeable to 8-slots in a 2 processor configuration		
<b>Power Supply</b>	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit
<b>Fans</b>	6x High Performance Fan	4x Standard Fan	4x Standard Fan
<b>Management</b>	HPE iLO 6		
<b>Rail Kit</b>	HPE ProLiant DL3XX Gen11 Easy Install Rail 3 Kit		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	2U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		



## ProLiant Gen11 Smart Choice

HPE ProLiant DL380 Gen11 - Smart Choice Models		
<b>SKU Number</b>	P79770-375	P79771-375
<b>Model Name</b>	HPE ProLiant DL380 Gen11 5515+ 3.2GHz 8c 2P 8x16GB-R 8SFF MR408i-o 5x600GB HDD 2x800W PS AP Server	HPE ProLiant DL380 Gen11 6526Y 2.8GHz 16c 2P 8x16GB-R 8SFF MR408i-o 5x600GB HDD 2x800W PS AP Server
<b>Chassis</b>	HPE ProLiant DL380 Gen11 8SFF NC Configure-to-order Server	
<b>Number of Processors</b>	Two with high performance heatsink	
<b>Memory</b>	128 GB (8x16 GB, 5600 MT/s) <b>Notes: Runs at 4800 MT/s due to processor limitation.</b>	128 GB (8x16 GB, 5600 MT/s) <b>Notes: Runs at 5200 MT/s due to processor limitation.</b>
<b>Accelerators</b>	Optional	
<b>Network Controller</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE	
<b>Storage Controller</b>	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller	
<b>Included Drives</b>	5x HPE 600GB SAS 12G Mission Critical 10K SFF BC 3-year Warranty Multi Vendor HDD	
<b>Optical Drive</b>	Optional DVD-ROM Optional via Universal Media Bay External support only	
<b>Expansion Slots</b>	3-slots (x8, x16, x8) as standard; upgradeable to 8-slots in a 2 processor configuration	
<b>Power Supply</b>	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	
<b>Fans</b>	4x Standard Fan	
<b>Management</b>	HPE iLO 6	
<b>Rail Kit</b>	HPE ProLiant DL3XX Gen11 Easy Install Rail 3 Kit	
<b>Security</b>	TPM (Trusted Platform Module)	
<b>Form Factor</b>	2U Rack	
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.	



## ProLiant Gen11 Smart Choice

HPE ProLiant DL385 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P75340-D65	P75346-DM5	P77244-425
<b>Model Name</b>	HPE ProLiant DL385 Gen11 9124 3.0GHz 16c 1P 64GB-R 8SFF MR408i-o 2x480GB SATA 2x800W RPS IN Server	HPE ProLiant DL385 Gen11 9124 3.0GHz 16c 1P 64GB-R 8SFF MR408i-o 2x960GB SSD 2x800W RPS LA Server	HPE ProLiant DL385 Gen11 9124 3.0GHz 16c 1P 64GB-R 8LFF NS204i-u NC BCM57416 2x1000W PS EU Server
<b>Chassis</b>	HPE ProLiant DL385 Gen11 8SFF Configure-to-order Server	HPE ProLiant DL385 Gen11 8SFF Configure-to-order Server	HPE ProLiant DL385 Gen11 8LFF Configure-to-order Server
<b>Processor</b>	9124 (16 core, 3.0 GHz, 200W)		
<b>Number of Processors</b>	One with standard heatsink		
<b>Memory</b>	64 GB (2x32 GB, 4800 MT/s)		
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Broadcom BCM57416 Ethernet 10Gb 2-port BASE-T OCP3 Adapter for HPE		
<b>Storage Controller</b>	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller	HPE NS204i-u Gen11 NVMe Hot Plug Boot Optimized Storage Device
<b>Included Drives</b>	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD	2x HPE 960GB SATA 6G Mixed Use SFF BC Multi Vendor SSD	None ship standard, 8 LFF supported
<b>Power Supply</b>	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit
<b>Fans</b>	6x Standard Fans	6x Standard Fans	6x Performance Fans
<b>Rail Kit</b>	HPE ProLiant DL3XX Gen11 Easy Install Rail 2 Kit		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	2U Rack		





## ProLiant Gen11 Smart Choice

HPE ProLiant DL385 Gen11 - Smart Choice Models		
<b>SKU Number</b>	P77245-425	P77251-005
<b>Model Name</b>	HPE ProLiant DL385 Gen11 9124 3.0GHz 16c 64GB-R 8SFF MR408i-o 2x480GB SATA SSD 2x1000W PS EU Server	HPE ProLiant DL385 Gen11 9354 3.25GHz 32c 2P 384GB-R 8SFF NS204i-u NC BCM57414 2x1000W PS NA Server
<b>Chassis</b>	HPE ProLiant DL385 Gen11 8SFF Configure-to-order Server	
<b>Processor</b>	9124 (16 core, 3.0 GHz, 200W)	9354 (32 core, 3.25 GHz, 280W)
<b>Number of Processors</b>	One with standard heatsink	Two with performance heatsink
<b>Memory</b>	64 GB (2x32 GB, 4800 MT/s)	384 GB (24x16 GB, 4800 MT/s)
<b>Accelerators</b>	Optional	
<b>Network Controller</b>	Broadcom BCM57416 Ethernet 10Gb 2-port BASE-T OCP3 Adapter for HPE	1x Broadcom BCM57414 Ethernet 10/25Gb 2-port SFP28 OCP3 Adapter for HPE 1x Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE
<b>Storage Controller</b>	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller	HPE NS204i-u Gen11 NVMe Hot Plug Boot Optimized Storage Device
<b>Included Drives</b>	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD	None ship standard, 8 SFF supported
<b>Power Supply</b>	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit	
<b>Fans</b>	6x Standard Fans	6x Performance Fans
<b>Rail Kit</b>	HPE ProLiant DL3XX Gen11 Easy Install Rail 2 Kit	
<b>Security</b>	TPM (Trusted Platform Module)	
<b>Form Factor</b>	2U Rack	



## ProLiant Gen11 Smart Choice

HPE ProLiant MicroServer Gen11 - Smart Choice Models			
<b>SKU Number</b>	P74439-005 P74439-425	P74440-005	P74441-DM5
<b>Model Name</b>	<p><b>P74439-005:</b> HPE ProLiant MicroServer Gen11 G7400 2c 16GB-U 4LFF-NHP 1TB HDD 180W Ext PS NA Cmp Module Server</p> <p><b>P74439-425:</b> HPE ProLiant MicroServer Gen11 G7400 2c 16GB-U 4LFF-NHP 1TB HDD 180W Ext PS EMEA Cmp Module Server</p>	HPE ProLiant MicroServer Gen11 E-2434 4c 32GB-U 4LFF-NHP 4TB HDD 180W External PS NA Cmp Mod Server	HPE ProLiant MicroServer Gen11 E-2434 4c 16GB-U 4LFF-NHP 2x1TB HDD 180W External PS LA Cmp Mod Svr
<b>Chassis</b>	HPE ProLiant MicroServer Gen11 4LFF Non-hot Plug Configure-to-order Server		
<b>Processor</b>	Intel® Pentium® Gold G7400	Intel® Xeon® E-2434	Intel® Xeon® E-2434
<b>Number of Processors</b>	One		
<b>Memory</b>	16 GB (1x16 GB UDIMM, 4800 MT/s)	32 GB (1x32 GB UDIMM, 4800 MT/s)	16 GB (1x16 GB UDIMM, 4800 MT/s)
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	4x1Gbe embedded <b>Notes:</b> Embedded 1Gb 4-port		
<b>Storage Controller</b>	Embedded Intel® VROC SATA for HPE ProLiant Gen11		
<b>Included Drives</b>	HPE 1TB SATA 6G Business Critical 7.2K LFF RW 1-year Warranty Multi Vendor HDD	HPE 4TB SATA 6G Business Critical 7.2K LFF RW 1-year Warranty Multi Vendor HDD	2x HPE 1TB SATA 6G Business Critical 7.2K LFF RW 1-year Warranty Multi Vendor HDD
<b>Optical Drive</b>	Optional ODD Bay Kit, none included		
<b>Expansion Slots</b>	(1) PCIe 5.0 slots, (1) PCIe 4.0 slots <b>Notes:</b> By adding the dedicated iLO-M.2-serial port kit this adds one M.2 slot and one serial port.		
<b>Power Supply</b>	1x 180W External Power Adapter, Non-Redundant Power Supply		
<b>Fans</b>	1 non-redundant system fan shipped standard		
<b>Management</b>	HPE iLO 6		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	Ultra Micro Tower		
<b>Warranty</b>	Server warranty includes 1-year parts, 1-year labor, 1-year onsite support with next business day response.		



## ProLiant Gen11 Smart Choice

HPE ProLiant MicroServer Gen11 - Smart Choice Models			
<b>SKU Number</b>	P75207-425	P75215-D65	P78521-005
<b>Model Name</b>	HPE ProLiant MicroServer Gen11 E-2434 4c 32GB-U 4LFF-NHP 2x4TB HDD 180W External PS EMEA Cmp Mod Svr	HPE ProLiant MicroServer Gen11 E-2434 4c 32GB-U 4LFF-NHP 1TB HDD 180W External PS IN Cmp Module Svr	HPE ProLiant MicroServer Gen11 E-2414 2.6GHz 4c 1P 1x16GB-U 4LFF-NHP 180W External PS NA Server
<b>Chassis</b>	HPE ProLiant MicroServer Gen11 4LFF Non-hot Plug Configure-to-order Server		
<b>Processor</b>	Intel® Xeon® E-2434	Intel® Xeon® E-2434	Intel® Xeon® E-2414
<b>Number of Processors</b>	One		
<b>Memory</b>	32 GB (1x32 GB UDIMM, 4800 MT/s)	32 GB (1x32 GB UDIMM, 4800 MT/s)	16 GB (1x16 GB UDIMM, 4800 MT/s)
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	4x1Gbe embedded <b>Notes:</b> Embedded 1Gb 4-port		
<b>Storage Controller</b>	Embedded Intel® VROC SATA for HPE ProLiant Gen11		
<b>Included Drives</b>	2x HPE 4TB SATA 6G Business Critical 7.2K LFF RW 1-year Warranty Multi Vendor HDD	HPE 1TB SATA 6G Business Critical 7.2K LFF RW 1-year Warranty Multi Vendor HDD	None ship standard, 4 LFF-NHP supported
<b>Optical Drive</b>	Optional ODD Bay Kit, none included		
<b>Expansion Slots</b>	(1) PCIe 5.0 slots, (1) PCIe 4.0 slots <b>Notes:</b> By adding the dedicated iLO-M.2-serial port kit this adds one M.2 slot and one serial port.		
<b>Power Supply</b>	1x 180W External Power Adapter, Non-Redundant Power Supply		
<b>Fans</b>	1 non-redundant system fan shipped standard		
<b>Management</b>	HPE iLO 6		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	Ultra Micro Tower		
<b>Warranty</b>	Server warranty includes 1-year parts, 1-year labor, 1-year onsite support with next business day response.		



## ProLiant Gen11 Smart Choice

HPE ProLiant MicroServer Gen11 - Smart Choice Models			
<b>SKU Number</b>	P78522-295	P78523-295	P79744-375
<b>Model Name</b>	HPE ProLiant MicroServer Gen11 E-2414 2.6GHz 4c 1x16GB-U 2x1TB SATA HDD 180W External PS JP Server	HPE ProLiant MicroServer Gen11 E-2414 2.6GHz 4c 1P 1x16GB-U 2x4TB HDD 180W External PS JP Server	HPE ProLiant MicroServer Gen11 E-2414 2.6GHz 4c 1P 1x16GB-U 4LFF-NHP 2x4TB HDD 180W Ext PS AP Server
<b>Chassis</b>	HPE ProLiant MicroServer Gen11 4LFF Non-hot Plug Configure-to-order Server		
<b>Processor</b>	Intel® Xeon® E-2414	Intel® Xeon® E-2414	
<b>Number of Processors</b>	One		
<b>Memory</b>	16 GB (1x16 GB UDIMM, 4800 MT/s)		
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	4x1Gbe embedded <b>Notes:</b> Embedded 1Gb 4-port		
<b>Storage Controller</b>	Embedded Intel® VROC SATA for HPE ProLiant Gen11		
<b>Included Drives</b>	2x HPE 1TB SATA 6G Business Critical 7.2K LFF RW 1-year Warranty Multi Vendor HDD	2x HPE 4TB SATA 6G Business Critical 7.2K LFF RW 1-year Warranty Multi Vendor HDD	2x HPE 4TB SATA 6G Business Critical 7.2K LFF RW 1-year Warranty Multi Vendor HDD
<b>Optical Drive</b>	Optional ODD Bay Kit, none included		
<b>Expansion Slots</b>	(1) PCIe 5.0 slots, (1) PCIe 4.0 slots <b>Notes:</b> By adding the dedicated iLO-M.2-serial port kit this adds one M.2 slot and one serial port.		
<b>Power Supply</b>	1x 180W External Power Adapter, Non-Redundant Power Supply		
<b>Fans</b>	1 non-redundant system fan shipped standard		
<b>Management</b>	HPE iLO 6		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	Ultra Micro Tower		
<b>Warranty</b>	Server warranty includes 1-year parts, 1-year labor, 1-year onsite support with next business day response.		



## ProLiant Gen11 Smart Choice

HPE ProLiant MicroServer Gen11 - Smart Choice Models	
<b>SKU Number</b>	P79785-D05
<b>Model Name</b>	HPE ProLiant MicroServer Gen11 E-2434 4c 1x16GB-U 4LFF-NHP 2x1TB HDD 180W External PS AR Server
<b>Chassis</b>	HPE ProLiant MicroServer Gen11 4LFF Non-hot Plug Configure-to-order Server
<b>Number of Processors</b>	One
<b>Memory</b>	16 GB (1x16 GB UDIMM, 4800 MT/s)
<b>Accelerators</b>	Optional
<b>Network Controller</b>	4x1Gbe embedded <b>Notes:</b> Embedded 1Gb 4-port
<b>Storage Controller</b>	Embedded Intel® VROC SATA for HPE ProLiant Gen11
<b>Included Drives</b>	2x HPE 1TB SATA 6G Business Critical 7.2K LFF RW 1-year Warranty Multi Vendor HDD
<b>Optical Drive</b>	Optional ODD Bay Kit, none included
<b>Expansion Slots</b>	(1) PCIe 5.0 slots, (1) PCIe 4.0 slots <b>Notes:</b> By adding the dedicated iLO-M.2-serial port kit this adds one M.2 slot and one serial port.
<b>Power Supply</b>	1x 180W External Power Adapter, Non-Redundant Power Supply
<b>Fans</b>	1 non-redundant system fan shipped standard
<b>Management</b>	HPE iLO 6
<b>Security</b>	TPM (Trusted Platform Module)
<b>Form Factor</b>	Ultra Micro Tower
<b>Warranty</b>	Server warranty includes 1-year parts, 1-year labor, 1-year onsite support with next business day response.



## ProLiant Gen11 Smart Choice

HPE ProLiant ML30 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P71385-425	P71387-425	P71388-035
<b>Model Name</b>	HPE ProLiant ML30 Gen11 E-2414 2.6GHz 4c 1P 32GB-DR 4LFF-NHP VROC 2x1TB SATA HDD 350W PS EU Server	HPE ProLiant ML30 Gen11 E-2434 3.4GHz 4c 1P 32GB-DR 8SFF VROC 2x480GB SATA SSD 800W RPS EU Server	HPE ProLiant ML30 Gen11 E-2434 3.4GHz 4c 1P 32GB-DR 8SFF VROC 2x480GB SATA SSD 800W RPS UK/IE Server
<b>Chassis</b>	HPE ProLiant ML30 Gen11 4LFF Non-hot Plug Configure-to-order Server	HPE ProLiant ML30 Gen11 8SFF Hot Plug Configure-to-order Server	HPE ProLiant ML30 Gen11 8SFF Hot Plug Configure-to-order Server
<b>Processor</b>	E-2414 (4 core, 2.6 GHz, 55W)	E-2434 (4 core, 3.4 GHz, 55W)	E-2434 (4 core, 3.4 GHz, 55W)
<b>Number of Processors</b>	One		
<b>Memory</b>	32 GB (1x32 GB UDIMM, 4800 MT/s)		
<b>Network Controller</b>	Embedded 1Gb 4-Port Ethernet Adapter		
<b>Storage Controller</b>	Embedded Intel VROC SATA software RAID <b>Notes:</b> – SATA Only – NHP models do not support internal Smart Array controllers		
<b>Included Drives</b>	2x HPE 1TB SATA 6G Business Critical 7.2K LFF RW 1-year Warranty Multi Vendor HDD	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD
<b>Optical Drive Bay</b>	Optional Slimline ODD Bay Kit (P65102-B21) consumes 1 media bay <b>Notes: Up to 1 optical drive bay</b>		
<b>Optical Drive</b>	None ship standard; ODD Optional		
<b>Power Supply</b>	1x HPE ProLiant ML30 Gen10 Plus 350W Platinum ATX FIO Power Supply	1x HPE 800W Flex Slot Titanium Hot Plug Low Halogen Power Supply Kit <b>Notes:</b> – Add a second 800W Flex Slot Power Supply to get 1+1 power redundancy feature. – 800W power supply only in EMEA for EU Lot 9 Compliance.	1x HPE 800W Flex Slot Titanium Hot Plug Low Halogen Power Supply Kit <b>Notes:</b> – Add a second 800W Flex Slot Power Supply to get 1+1 power redundancy feature. – 800W power supply only in EMEA for EU Lot 9 Compliance.
<b>Fans</b>	1x Non-hot plug non-redundant system fan		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	4U Tower		
<b>Warranty</b>	Server Warranty includes 3-Year Parts, 1-Year Labor, 1-Year Onsite support with next business day response <b>Notes: APAC, Japan, and PRC Server Warranty includes 3-Year parts, 3-Year Labor, 3-Year Onsite support with next business day response</b>		

## ProLiant Gen11 Smart Choice

HPE ProLiant ML30 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P71389-035	P72995-005	P72996-005
<b>Model Name</b>	HPE ProLiant ML30 Gen11 E-2414 2.6GHz 4c 1P 32GB-DR 4LFF-NHP VROC 2x1TB SATA HDD 350W PS UK Server	HPE ProLiant ML30 Gen11 E-2434 3.4GHz 4-core 1P 32GB-R 8SFF 2x960GB SSD 2x500W RPS NA Server	HPE ProLiant ML30 Gen11 E-2434 3.4GHz 4-core 1P 32GB-R 4LFF 2x2TB HDD 500W RPS NA Server
<b>Chassis</b>	HPE ProLiant ML30 Gen11 4LFF Non-hot Plug Configure-to-order Server	HPE ProLiant ML30 Gen11 8SFF Hot Plug Configure-to-order Server	HPE ProLiant ML30 Gen11 4LFF Hot Plug Configure-to-order Server
<b>Processor</b>	E-2414 (4 core, 2.6 GHz, 55W)	E-2434 (4 core, 3.4 GHz, 55W)	E-2434 (4 core, 3.4 GHz, 55W)
<b>Number of Processors</b>	One		
<b>Memory</b>	32 GB (1x32 GB UDIMM, 4800 MT/s)		
<b>Network Controller</b>	Embedded 1Gb 4-Port Ethernet Adapter		
<b>Storage Controller</b>	Embedded Intel VROC SATA software RAID <b>Notes:</b> – SATA Only – NHP models do not support internal Smart Array controllers	HPE MR216i-p Gen11 x16 Lanes without Cache PCI SPDM Plug-in Storage Controller	HPE MR216i-p Gen11 x16 Lanes without Cache PCI SPDM Plug-in Storage Controller
<b>Included Drives</b>	2x HPE 1TB SATA 6G Business Critical 7.2K LFF RW 1-year Warranty Multi Vendor HDD	2x HPE 960GB SATA 6G Read Intensive SFF BC Multi Vendor SSD	2x HPE 2TB SATA 6G Business Critical 7.2K LFF LP 1-year Warranty Multi Vendor HDD
<b>Optical Drive Bay</b>	Optional Slimline ODD Bay Kit (P65102-B21) consumes 1 media bay <b>Notes: Up to 1 optical drive bay</b>		
<b>Optical Drive</b>	None ship standard; ODD Optional		
<b>Power Supply</b>	1x HPE ProLiant ML30 Gen10 Plus 350W Platinum ATX FIO Power Supply	2x HPE 500W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	1x HPE 500W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit
<b>Fans</b>	1x Non-hot plug non-redundant system fan		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	4U Tower		
<b>Warranty</b>	Server Warranty includes 3-Year Parts, 1-Year Labor, 1-Year Onsite support with next business day response <b>Notes: APAC, Japan, and PRC Server Warranty includes 3-Year parts, 3-Year Labor, 3-Year Onsite support with next business day response</b>		



## ProLiant Gen11 Smart Choice

HPE ProLiant ML30 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P75337-D65	P75338-D65	P77232-425
<b>Model Name</b>	HPE ProLiant ML30 Gen11 E-2434 3.4GHz 4c 1P 32GB-DR 8SFF 480GB SSD 2x500W RPS IN Server	HPE ProLiant ML30 Gen11 E-2414 2.6GHz 4c 1P 32GB-DR 4LFF 1TB HDD 350W PS IN Server	HPE ProLiant ML30 Gen11 E-2434 3.4GHz 4c 1P 32GB-U 4LFF 2x960GB SSD 800W RPS EU Server
<b>Chassis</b>	HPE ProLiant ML30 Gen11 8SFF Hot Plug Configure-to-order Server	HPE ProLiant ML30 Gen11 4LFF Non-hot Plug Configure-to-order Server	HPE ProLiant ML30 Gen11 4LFF Hot Plug Configure-to-order Server
<b>Processor</b>	E-2434 (4 core, 3.4 GHz, 55W)	E-2414 (4 core, 2.6 GHz, 55W)	E-2434 (4 core, 3.4 GHz, 55W)
<b>Number of Processors</b>	One		
<b>Memory</b>	32 GB (1x32 GB UDIMM, 4800 MT/s)		
<b>Network Controller</b>	Embedded 1Gb 4-Port Ethernet Adapter		
<b>Storage Controller</b>	Embedded Intel VROC SATA software RAID		
<b>Included Drives</b>	HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD	HPE 1TB SATA 6G Business Critical 7.2K LFF RW 1-year Warranty Multi Vendor HDD	2x HPE 960GB SATA 6G Read Intensive LFF LPC Multi Vendor SSD
<b>Optical Drive Bay</b>	Optional Slimline ODD Bay Kit (P65102-B21) consumes 1 media bay <b>Notes: Up to 1 optical drive bay</b>		
<b>Optical Drive</b>	None ship standard; ODD Optional	None ship standard; ODD Optional	None ship standard. Optional: SATA 9.5mm DVD-RW/DVD-ROM Optical Drive
<b>Power Supply</b>	2x HPE 500W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	1x HPE ProLiant ML30 Gen10 Plus 350W Platinum ATX FIO Power Supply	1x HPE 800W Flex Slot Titanium Hot Plug Low Halogen Power Supply Kit
<b>Fans</b>	1x Non-hot plug non-redundant system fan		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	4U Tower		
<b>Warranty</b>	Server Warranty includes 3-Year Parts, 1-Year Labor, 1-Year Onsite support with next business day response <b>Notes: APAC, Japan, and PRC Server Warranty includes 3-Year parts, 3-Year Labor, 3-Year Onsite support with next business day response</b>		





## ProLiant Gen11 Smart Choice

HPE ProLiant ML30 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P78101-295	P78106-295	P78177-295
<b>Model Name</b>	HPE ProLiant ML30 Gen11 E-2414 2.6GHz 4c 1P 16GB-U 4LFF 2x2TB HDD 2x500W PS JP Server	HPE ProLiant ML30 Gen11 E-2414 2.6GHz 4c 1P 16GB-U 8SFF MR416i-p 2x600GB HDD 2x500W PS JP Server	HPE ProLiant ML30 Gen11 E-2414 2.6GHz 4c 1P 16GB-U 4LFF MR416i-p 4x4TB HDD 2x500W PS JP Server
<b>Chassis</b>	HPE ProLiant ML30 Gen11 4LFF Hot Plug Configure-to-order Server	HPE ProLiant ML30 Gen11 8SFF Hot Plug Configure-to-order Server	HPE ProLiant ML30 Gen11 4LFF Hot Plug Configure-to-order Server
<b>Number of Processors</b>	One		
<b>Memory</b>	16 GB (1x16 GB UDIMM, 4800 MT/s)		
<b>Network Controller</b>	Embedded 1Gb 4-Port Ethernet Adapter		
<b>Storage Controller</b>	Embedded Intel VROC SATA software RAID	HPE MR416i-p Gen11 x16 Lanes 8GB Cache PCI SPDM Plug-in Storage Controller	HPE MR416i-p Gen11 x16 Lanes 8GB Cache PCI SPDM Plug-in Storage Controller
<b>Included Drives</b>	2x HPE 2TB SATA 6G Business Critical 7.2K LFF LP 1-year Warranty Multi Vendor HDD	2x HPE 600GB SAS 12G Mission Critical 10K SFF BC 3-year Warranty Multi Vendor HDD	4x HPE 4TB SAS 12G Business Critical 7.2K LFF LP 1-year Warranty Multi Vendor HDD
<b>Optical Drive Bay</b>	Optional Slimline ODD Bay Kit (P65102-B21) consumes 1 media bay <b>Notes: Up to 1 optical drive bay</b>		
<b>Optical Drive</b>	None ship standard. Optional: SATA 9.5mm DVD-RW/DVD-ROM Optical Drive	1x SATA 9.5mm DVD-ROM Optical Drive	1x SATA 9.5mm DVD-ROM Optical Drive
<b>Power Supply</b>	2x HPE 500W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit		
<b>Fans</b>	1x Non-hot plug non-redundant system fan		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	4U Tower		
<b>Warranty</b>	Server Warranty includes 3-Year Parts, 1-Year Labor, 1-Year Onsite support with next business day response <b>Notes: APAC, Japan, and PRC Server Warranty includes 3-Year parts, 3-Year Labor, 3-Year Onsite support with next business day response</b>		



## ProLiant Gen11 Smart Choice

HPE ProLiant ML30 Gen11 - Smart Choice Models	
<b>SKU Number</b>	P78178-295
<b>Model Name</b>	HPE ProLiant ML30 Gen11 E-2414 2.6GHz 4c 1P 32GB-U 8SFF MR416i-p 4x1.2TB HDD 2x500W PS JP Server
<b>Chassis</b>	HPE ProLiant ML30 Gen11 8SFF Hot Plug Configure-to-order Server
<b>Number of Processors</b>	One
<b>Memory</b>	32 GB (1x32 GB UDIMM, 4800 MT/s)
<b>Network Controller</b>	Embedded 1Gb 4-Port Ethernet Adapter
<b>Storage Controller</b>	HPE MR416i-p Gen11 x16 Lanes 8GB Cache PCI SPDM Plug-in Storage Controller
<b>Included Drives</b>	4x HPE 1.2TB SAS 12G Mission Critical 10K SFF BC 3-year Warranty HDD
<b>Optical Drive Bay</b>	Optional Slimline ODD Bay Kit (P65102-B21) consumes 1 media bay <b>Notes: Up to 1 optical drive bay</b>
<b>Optical Drive</b>	1x SATA 9.5mm DVD-ROM Optical Drive
<b>Power Supply</b>	2x HPE 500W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit
<b>Fans</b>	1x Non-hot plug non-redundant system fan
<b>Security</b>	TPM (Trusted Platform Module)
<b>Form Factor</b>	4U Tower
<b>Warranty</b>	Server Warranty includes 3-Year Parts, 1-Year Labor, 1-Year Onsite support with next business day response <b>Notes: APAC, Japan, and PRC Server Warranty includes 3-Year parts, 3-Year Labor, 3-Year Onsite support with next business day response</b>



## ProLiant Gen11 Smart Choice

HPE ProLiant ML110 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P69303-005	P71647-425	P71648-035
<b>Model Name</b>	HPE ProLiant ML110 Gen11 4410Y 12-core 1P 32GB-R MR408i-o 8SFF 2x480GB SSD 2x800W RPS AMS Server	HPE ProLiant ML110 Gen11 3508U 2.1GHz 8-core 1P 32GB-R VROC 4LFF 2x2TB HDD 2x1000W RPS EU Server	HPE ProLiant ML110 Gen11 3508U 2.1GHz 8-core 1P 32GB-R VROC 4LFF 2x2TB HDD 2x1000W RPS UK/IE Server
<b>Chassis</b>	HPE ProLiant ML110 Gen11 SFF Configure-to-order Server	HPE ProLiant ML110 Gen11 LFF Configure-to-order Server	HPE ProLiant ML110 Gen11 LFF Configure-to-order Server
<b>Processor</b>	4410Y (12 core, 2.0 GHz, 150W)	3508U (8 core, 2.1 GHz, 125W)	3508U (8 core, 2.1 GHz, 125W)
<b>Number of Processors</b>	One		
<b>Memory</b>	32 GB (1x32 GB, 4800 MT/s) <b>Notes:</b> Runs at 4000 MT/s due to processor limitation.	32 GB (1x32 GB, 5600 MT/s) <b>Notes:</b> Runs at 4400 MT/s due to processor limitation.	32 GB (1x32 GB, 5600 MT/s) <b>Notes:</b> Runs at 4400 MT/s due to processor limitation.
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Embedded 2-Port 1GbE BCM5720 networking ports		
<b>Storage Controller</b>	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller	Embedded Intel VROC SATA/NVMe <b>Notes:</b> Embedded controller can only support SATA drive, additional storage controller is required to support SAS drive.	Embedded Intel VROC SATA/NVMe <b>Notes:</b> Embedded controller can only support SATA drive, additional storage controller is required to support SAS drive.
<b>Included Drives</b>	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD	2x HPE 2TB SATA 6G Business Critical 7.2K LFF LP 1-year Warranty Multi Vendor HDD	2x HPE 2TB SATA 6G Business Critical 7.2K LFF LP 1-year Warranty Multi Vendor HDD
<b>Optical Drive</b>	Optional. None ship standard.		
<b>Expansion Slots</b>	PCIe Gen5: 2 slots (x16), upgradable to 4 slots (x16); OCP3 with PCIe Gen5: 1 slot (x16)		
<b>Power Supply</b>	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit
<b>Fans</b>	2x Standard Fans <b>Notes:</b> Configurations that require fan kits are provided in later sections.		
<b>Management</b>	HPE iLO Standard with Intelligent Provisioning (embedded), HPE OneView Standard (requires download); HPE iLO Advanced and HPE OneView Advanced (require licenses)		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	4.5U Tower. Optional Tower-to-Rack conversion kit (P47394-B21) to convert the unit to a 5.5U Rack-mount server.		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		

## ProLiant Gen11 Smart Choice

HPE ProLiant ML110 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P71659-425	P71670-035	P71683-005
<b>Model Name</b>	HPE ProLiant ML110 Gen11 4510 12-core 1P 64GB-R MR408i-o 8SFF 2x480GB SSD 2x1000W RPS EU Server	HPE ProLiant ML110 Gen11 4510 12-core 1P 64GB-R MR408i-o 8SFF 2x480GB SSD 2x1000W RPS UK/IE Server	HPE ProLiant ML110 Gen11 3508U 2.1GHz 8-core 1P 32GB-R MR408i-o 4LFF 2x2TB HDD 2x500W RPS AMS Server
<b>Chassis</b>	HPE ProLiant ML110 Gen11 SFF Configure-to-order Server	HPE ProLiant ML110 Gen11 SFF Configure-to-order Server	HPE ProLiant ML110 Gen11 LFF Configure-to-order Server
<b>Processor</b>	4510 (12 core, 2.4 GHz, 150W)	4510 (12 core, 2.4 GHz, 150W)	3508U (8 core, 2.1 GHz, 125W)
<b>Number of Processors</b>	One		
<b>Memory</b>	64 GB (2x32 GB, 5600 MT/s) <b>Notes:</b> Runs at 4400 MT/s due to processor limitation.	64 GB (2x32 GB, 5600 MT/s) <b>Notes:</b> Runs at 4400 MT/s due to processor limitation.	32 GB (1x32 GB, 5600 MT/s) <b>Notes:</b> Runs at 4400 MT/s due to processor limitation.
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Embedded 2-Port 1GbE BCM5720 networking ports		
<b>Storage Controller</b>	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller		
<b>Included Drives</b>	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD	2x HPE 2TB SATA 6G Business Critical 7.2K LFF LP 1-year Warranty Multi Vendor HDD
<b>Optical Drive</b>	Optional. None ship standard.		
<b>Expansion Slots</b>	PCIe Gen5: 2 slots (x16), upgradable to 4 slots (x16); OCP3 with PCIe Gen5: 1 slot (x16)		
<b>Power Supply</b>	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit	2x HPE 500W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit
<b>Fans</b>	2x Standard Fans <b>Notes:</b> Configurations that require fan kits are provided in later sections.		
<b>Management</b>	HPE iLO Standard with Intelligent Provisioning (embedded), HPE OneView Standard (requires download); HPE iLO Advanced and HPE OneView Advanced (require licenses)		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	4.5U Tower. Optional Tower-to-Rack conversion kit (P47394-B21) to convert the unit to a 5.5U Rack-mount server.		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		

## ProLiant Gen11 Smart Choice

HPE ProLiant ML110 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P71687-005	P75329-005	P75330-D65
<b>Model Name</b>	HPE ProLiant ML110 Gen11 4514Y 2.0GHz 16-core 1P 64GB-R MR408i-o 8SFF 2x960GB 2x800W RPS AMS Server	HPE ProLiant ML110 Gen11 4510 2.4GHz 12c 1P 32GB-R 4LFF VROC 4TB HDD 2x500W RPS NA Server	HPE ProLiant ML110 Gen11 3508U 2.1GHz 8c 1P 32GB-R 4LFF VROC 2TB HDD 1x500W RPS IN Server
<b>Chassis</b>	HPE ProLiant ML110 Gen11 SFF Configure-to-order Server	HPE ProLiant ML110 Gen11 LFF Configure-to-order Server	HPE ProLiant ML110 Gen11 LFF Configure-to-order Server
<b>Processor</b>	4514Y (16 core, 2.0 GHz, 150W)	4510 (12 core, 2.4 GHz, 150W)	3508U (8 core, 2.1 GHz, 125W)
<b>Number of Processors</b>	One		
<b>Memory</b>	64 GB (2x32 GB, 5600 MT/s) <b>Notes:</b> Runs at 4400 MT/s due to processor limitation.	32 GB (1x32 GB, 5600 MT/s) <b>Notes:</b> Runs at 4400 MT/s due to processor limitation.	32 GB (1x32 GB, 5600 MT/s) <b>Notes:</b> Runs at 4400 MT/s due to processor limitation.
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Embedded 2-Port 1GbE BCM5720 networking ports		
<b>Storage Controller</b>	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller	Embedded Intel VROC SATA/NVMe <b>Notes:</b> Embedded controller can only support SATA drive, additional storage controller is required to support SAS drive.	Embedded Intel VROC SATA/NVMe <b>Notes:</b> Embedded controller can only support SATA drive, additional storage controller is required to support SAS drive.
<b>Included Drives</b>	2x HPE 960GB SATA 6G Read Intensive SFF BC Multi Vendor SSD	HPE 4TB SATA 6G Business Critical 7.2K LFF LP 1-year Warranty Multi Vendor HDD	HPE 2TB SATA 6G Business Critical 7.2K LFF LP 1-year Warranty Multi Vendor HDD
<b>Optical Drive</b>	Optional. None ship standard.		
<b>Expansion Slots</b>	PCIe Gen5: 2 slots (x16), upgradable to 4 slots (x16); OCP3 with PCIe Gen5: 1 slot (x16)		
<b>Power Supply</b>	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	2x HPE 500W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	1x HPE 500W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit <b>Notes:</b> Additional HPE 500W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit (865408-B21) provides 1+1 power redundancy feature.
<b>Fans</b>	2x Standard Fans <b>Notes:</b> Configurations that require fan kits are provided in later sections.		
<b>Management</b>	HPE iLO Standard with Intelligent Provisioning (embedded), HPE OneView Standard (requires download); HPE iLO Advanced and HPE OneView Advanced (require licenses)		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	4.5U Tower. Optional Tower-to-Rack conversion kit (P47394-B21) to convert the unit to a 5.5U Rack-mount server.		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		

## ProLiant Gen11 Smart Choice

HPE ProLiant ML110 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P77234-425	P78114-DM5	P78115-DM5
<b>Model Name</b>	HPE ProLiant ML110 Gen11 4510 2.4GHz 12c 1P 32GB-R 4LFF 2x4TB HDD 2x1000W PS EU Server	HPE ProLiant ML110 Gen11 3408U 1.8GHz 8c 1P 1x32GB-R 4LFF 2x4TB HDD 500W PS LA Server	HPE ProLiant ML110 Gen11 3408U 1.8GHz 8c 1P 32GB-R 4LFF 2x960GB SATA SSD 500W PS MX Server
<b>Chassis</b>	HPE ProLiant ML110 Gen11 LFF Configure-to-order Server		
<b>Processor</b>	4510 (12 core, 2.4 GHz, 150W)		
<b>Number of Processors</b>	One		
<b>Memory</b>	32 GB (1x32 GB, 5600 MT/s) <b>Notes:</b> Runs at 4400 MT/s due to processor limitation.	32 GB (1x32 GB, 4800 MT/s) <b>Notes:</b> Runs at 4000 MT/s due to processor limitation.	32 GB (1x32 GB, 4800 MT/s) <b>Notes:</b> Runs at 4000 MT/s due to processor limitation.
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Embedded 2-Port 1GbE BCM5720 networking ports		
<b>Storage Controller</b>	Embedded Intel VROC SATA/NVMe <b>Notes:</b> Embedded controller can only support SATA drive, additional storage controller is required to support SAS drive.		
<b>Included Drives</b>	2x HPE 4TB SATA 6G Business Critical 7.2K LFF LP 1-year Warranty Multi Vendor HDD	2x HPE 4TB SATA 6G Business Critical 7.2K LFF LP 1-year Warranty Multi Vendor HDD	2x HPE 960GB SATA 6G Read Intensive LFF LPC Multi Vendor SSD
<b>Optical Drive</b>	Optional. None ship standard.	Optional DVD-ROM or DVD-RW. Optional via ODD cable Kit. Optional Half-Height RDX, up to 1. Refer to the QuickSpecs for more detail.	Optional. None ship standard.
<b>Expansion Slots</b>	PCIe Gen5: 2 slots (x16), upgradable to 4 slots (x16); OCP3 with PCIe Gen5: 1 slot (x16)		
<b>Power Supply</b>	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit	1x HPE 500W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	1x HPE 500W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit
<b>Fans</b>	2x Standard Fans <b>Notes:</b> Configurations that require fan kits are provided in later sections.		
<b>Management</b>	HPE iLO Standard with Intelligent Provisioning (embedded), HPE OneView Standard (requires download); HPE iLO Advanced and HPE OneView Advanced (require licenses)		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	4.5U Tower. Optional Tower-to-Rack conversion kit (P47394-B21) to convert the unit to a 5.5U Rack-mount server.		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		

## ProLiant Gen11 Smart Choice

HPE ProLiant ML110 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P79761-375	P79786-D05	P79787-D05
<b>Model Name</b>	HPE ProLiant ML110 Gen11 4510 2.4GHz 12c 1P 2x32GB-R MR408i-o 2x480GB SATA SSD 2x800W PS AP Server	HPE ProLiant ML110 Gen11 3408U 1.8GHz 8c 1P 1x32GB-R 4LFF 2x4TB HDD 1x500W PS AR Server	HPE ProLiant ML110 Gen11 3408U 1.8GHz 8c 1P 1x32GB-R 4LFF 2x960GB SATA SSD 1x500W PS AR Server
<b>Chassis</b>	HPE ProLiant ML110 Gen11 SFF Configure-to-order Server	HPE ProLiant ML110 Gen11 LFF Configure-to-order Server	HPE ProLiant ML110 Gen11 LFF Configure-to-order Server
<b>Processor</b>	4510 (12 core, 2.4 GHz, 150W)		
<b>Number of Processors</b>	One		
<b>Memory</b>	64 GB (2x32 GB, 5600 MT/s) <b>Notes:</b> Runs at 4400 MT/s due to processor limitation.	32 GB (1x32 GB, 4800 MT/s) <b>Notes:</b> Runs at 4000 MT/s due to processor limitation.	32 GB (1x32 GB, 4800 MT/s) <b>Notes:</b> Runs at 4000 MT/s due to processor limitation.
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Embedded 2-Port 1GbE BCM5720 networking ports		
<b>Storage Controller</b>	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller	Embedded Intel VROC SATA/NVMe <b>Notes:</b> Embedded controller can only support SATA drive, additional storage controller is required to support SAS drive.	Embedded Intel VROC SATA/NVMe <b>Notes:</b> Embedded controller can only support SATA drive, additional storage controller is required to support SAS drive.
<b>Included Drives</b>	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD	2x HPE 4TB SATA 6G Business Critical 7.2K LFF LP 1-year Warranty Multi Vendor HDD	2x HPE 960GB SATA 6G Read Intensive LFF LPC Multi Vendor SSD
<b>Optical Drive</b>	Optional DVD-ROM or DVD-RW. Optional via ODD cable Kit. Optional Half-Height RDX, up to 1. Refer to the QuickSpecs for more detail.		
<b>Expansion Slots</b>	PCIe Gen5: 2 slots (x16), upgradable to 4 slots (x16); OCP3 with PCIe Gen5: 1 slot (x16)		
<b>Power Supply</b>	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	1x HPE 500W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	1x HPE 500W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit
<b>Fans</b>	2x Standard Fans <b>Notes:</b> Configurations that require fan kits are provided in later sections.		
<b>Management</b>	HPE iLO Standard with Intelligent Provisioning (embedded), HPE OneView Standard (requires download); HPE iLO Advanced and HPE OneView Advanced (require licenses)		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	4.5U Tower. Optional Tower-to-Rack conversion kit (P47394-B21) to convert the unit to a 5.5U Rack-mount server.		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		

## ProLiant Gen11 Smart Choice

HPE ProLiant ML350 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P69310-005	P69313-005	P71671-425
<b>Model Name</b>	HPE ProLiant ML350 Gen11 4410Y 12-core 1P 64GB-R MR408i-o 8SFF 2x480GB SSD 2x800W RPS AMS Server	HPE ProLiant ML350 Gen11 5416S 16-core 1P 64GB-R MR408i-o 8SFF 2x480GB SSD 2x800W RPS AMS Server	HPE ProLiant ML350 Gen11 4510 12-core 64GB-R MR408i-o 8SFF 2x960GB SSD 2x1000W RPS EU Server
<b>Chassis</b>	HPE ProLiant ML350 Gen11 SFF Configure-to-order Server		
<b>Backplane</b>	8 SFF		
<b>Processor</b>	4410Y (12 core, 2.0 GHz, 150W)	5416S (16 core, 2.0 GHz, 150W)	4510 (12 core, 2.4 GHz, 150W)
<b>Number of Processors</b>	One with standard heatsink		
<b>Memory</b>	64 GB (2x32 GB, 4800 MT/s) <b>Notes:</b> Runs at 4000 MT/s due to processor limitation.	64 GB (2x32 GB, 4800 MT/s) <b>Notes:</b> Runs at 4400 MT/s due to processor limitation.	64 GB (2x32 GB, 5600 MT/s) <b>Notes:</b> Runs at 4400 MT/s due to processor limitation.
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE <b>Notes:</b> Slot 15 OCP will be occupied along with CPU 1 MCIO port 1.		
<b>Storage Controller</b>	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller <b>Notes:</b> – Slot 14 OCP will be occupied, PCIe expansion slot is not required. – This controller supports up to 8 SAS/SATA/NVMe Drives with performance RAID. – Smart Storage battery included.		
<b>Included Drives</b>	2x HPE 480GB SATA 6G Mixed Use SFF BC Multi Vendor SSD	2x HPE 480GB SATA 6G Mixed Use SFF BC Multi Vendor SSD	2x HPE 960GB SATA 6G Mixed Use SFF BC Multi Vendor SSD
<b>Internal Storage</b>	Default with 8 SFF SAS/SATA/NVMe x1 U.3 Drive Cage Kit (P47217-B21), up to two additional drive cages. <b>Notes:</b> Controller/cable kit is required for additional drive cage.		
<b>Optical Drive</b>	Optional. None ship standard.		
<b>Expansion Slots</b>	Default with 4 x8 PCIe 5.0 slots with primary riser cage. Upgradable with additional riser kit. <b>Notes:</b> Dual processors are required to support expansion card on PCIe slots 5-10.		
<b>Power Supply</b>	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit
<b>Fans</b>	3x Standard Fans <b>Notes:</b> Configurations that require fan kits are provided in later sections	8x Standard Fans <b>Notes:</b> Configurations that require fan kits are provided in later sections	3x Standard Fans <b>Notes:</b> Configurations that require fan kits are provided in later sections
<b>Management</b>	HPE iLO Standard with Intelligent Provisioning (embedded), HPE OneView Standard (requires download); HPE iLO Advanced, HPE OneView Advanced (require licenses), and HPE Compute Ops Management		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	4U Tower, Optional Tower-to-Rack conversion kit (P47394-B21) to convert the unit to a 5U Rack-mount server.		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		



## ProLiant Gen11 Smart Choice

HPE ProLiant ML350 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P71672-035	P71688-005	P74650-D65
<b>Model Name</b>	HPE ProLiant ML350 Gen11 4510 12-core 64GB-R MR408i-o 8SFF 2x960GB SSD 2x1000W RPS UK/IE Server	HPE ProLiant ML350 Gen11 4514Y 16-core 64GB-R MR408i-o 8SFF 2x480GB SSD 2x800W RPS AMS Server	HPE ProLiant ML350 Gen11 4510 2.4GHz 12c 1P 32GB-R 8SFF MR408i-o 2x2.4TB HDD 2x800W RPS IN Server
<b>Chassis</b>	HPE ProLiant ML350 Gen11 SFF Configure-to-order Server		
<b>Backplane</b>	8 SFF		
<b>Processor</b>	4510 (12 core, 2.4 GHz, 150W)	4514Y (16 core, 2.0 GHz, 150W)	4510 (12 core, 2.4 GHz, 150W)
<b>Number of Processors</b>	One with standard heatsink		
<b>Memory</b>	64 GB (2x32 GB, 5600 MT/s) <b>Notes:</b> Runs at 4400 MT/s due to processor limitation.	64 GB (2x32 GB, 5600 MT/s) <b>Notes:</b> Runs at 4400 MT/s due to processor limitation.	32 GB (1x32 GB, 5600 MT/s) <b>Notes:</b> Runs at 4400 MT/s due to processor limitation.
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE <b>Notes:</b> Slot 15 OCP will be occupied along with CPU 1 MCIO port 1.		
<b>Storage Controller</b>	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller <b>Notes:</b> – Slot 14 OCP will be occupied, PCIe expansion slot is not required. – This controller supports up to 8 SAS/SATA/NVMe Drives with performance RAID. – Smart Storage battery included.		
<b>Included Drives</b>	2x HPE 960GB SATA 6G Mixed Use SFF BC Multi Vendor SSD	2x HPE 480GB SATA 6G Mixed Use SFF BC Multi Vendor SSD	2x HPE 2.4TB SAS 12G Mission Critical 10K SFF BC 3-year Warranty 512e HDD
<b>Internal Storage</b>	Default with 8 SFF SAS/SATA/NVMe x1 U.3 Drive Cage Kit (P47217-B21), up to two additional drive cages. <b>Notes:</b> Controller/cable kit is required for additional drive cage.		
<b>Optical Drive</b>	Optional. None ship standard.		
<b>Expansion Slots</b>	Default with 4 x8 PCIe 5.0 slots with primary riser cage. Upgradable with additional riser kit. <b>Notes:</b> Dual processors are required to support expansion card on PCIe slots 5-10.		
<b>Power Supply</b>	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit
<b>Fans</b>	3x Standard Fans <b>Notes:</b> Configurations that require fan kits are provided in later sections	8x Standard Fans <b>Notes:</b> Configurations that require fan kits are provided in later sections	3x Standard Fans <b>Notes:</b> Configurations that require fan kits are provided in later sections
<b>Management</b>	HPE iLO Standard with Intelligent Provisioning (embedded), HPE OneView Standard (requires download); HPE iLO Advanced, HPE OneView Advanced (require licenses), and HPE Compute Ops Management		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	4U Tower, Optional Tower-to-Rack conversion kit (P47394-B21) to convert the unit to a 5U Rack-mount server.		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		

## ProLiant Gen11 Smart Choice

HPE ProLiant ML350 Gen11 - Smart Choice Models			
<b>SKU Number</b>	P75339-D65	P75341-DM5	P77233-425
<b>Model Name</b>	HPE ProLiant ML350 Gen11 4509Y 2.6GHz 8c 1P 32GB-R 4LFF MR408i-o 2x4TB HDD 2x800W RPS IN Server	HPE ProLiant ML350 Gen11 4410Y 2.0GHz 12c 1P 64GB-R 8SFF MR408i-o 2x960GB SSD 2x800W RPS LA Server	HPE ProLiant ML350 Gen11 4514Y 2.0GHz 16c 1P 64GB-R 8SFF MR408i-o 2x2.4TB HDD 2x1000W PS EU Server
<b>Chassis</b>	HPE ProLiant ML350 Gen11 LFF Configure-to-order Server	HPE ProLiant ML350 Gen11 SFF Configure-to-order Server	HPE ProLiant ML350 Gen11 SFF Configure-to-order Server
<b>Backplane</b>	4 LFF	8 SFF	
<b>Processor</b>	4509Y (8 core, 2.6 GHz, 125W)	4410Y (12 core, 2.0 GHz, 150W)	4514Y (16 core, 2.0 GHz, 150W)
<b>Number of Processors</b>	One with standard heatsink		
<b>Memory</b>	32 GB (1x32 GB, 5600 MT/s) <b>Notes:</b> Runs at 4400 MT/s due to processor limitation.	64 GB (2x32 GB, 4800 MT/s) <b>Notes:</b> Runs at 4000 MT/s due to processor limitation.	64 GB (2x32 GB, 5600 MT/s) <b>Notes:</b> Runs at 4400 MT/s due to processor limitation.
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE <b>Notes:</b> Slot 15 OCP will be occupied along with CPU 1 MCIO port 1.		
<b>Storage Controller</b>	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller <b>Notes:</b> – Slot 14 OCP will be occupied, PCIe expansion slot is not required. – This controller supports up to 8 SAS/SATA/NVMe Drives with performance RAID. – Smart Storage battery included.		
<b>Included Drives</b>	2x HPE 4TB SATA 6G Business Critical 7.2K LFF LP 1-year Warranty Multi Vendor HDD	2x HPE 960GB SATA 6G Mixed Use SFF BC Multi Vendor SSD	2x HPE 2.4TB SAS 12G Mission Critical 10K SFF BC 3-year Warranty 512e HDD
<b>Internal Storage</b>	Default with 4LFF SAS/SATA Drive Cage Kit (P47216- B21), up to two additional drive cages. <b>Notes:</b> Controller/cable kit is required for additional drive cage.	Default with 8 SFF SAS/SATA/NVMe x1 U.3 Drive Cage Kit (P47217- B21), up to two additional drive cages. <b>Notes:</b> Controller/cable kit is required for additional drive cage.	
<b>Optical Drive</b>	Optional. None ship standard.		
<b>Expansion Slots</b>	Default with 4 x8 PCIe 5.0 slots with primary riser cage. Upgradable with additional riser kit. <b>Notes:</b> Dual processors are required to support expansion card on PCIe slots 5-10.		
<b>Power Supply</b>	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	2x HPE 1000W Flex Slot Titanium Hot Plug Power Supply Kit
<b>Fans</b>	3x Standard Fans <b>Notes:</b> Configurations that require fan kits are provided in later sections		
<b>Management</b>	HPE iLO Standard with Intelligent Provisioning (embedded), HPE OneView Standard (requires download); HPE iLO Advanced, HPE OneView Advanced (require licenses), and HPE Compute Ops Management		
<b>Security</b>	TPM (Trusted Platform Module)		

## ProLiant Gen11 Smart Choice

<b>Form Factor</b>	4U Tower, Optional Tower-to-Rack conversion kit (P47394-B21) to convert the unit to a 5U Rack-mount server.	
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.	
<b>HPE ProLiant ML350 Gen11 - Smart Choice Models</b>		
<b>SKU Number</b>	P79762-375	P79779-D05
<b>Model Name</b>	HPE ProLiant ML350 Gen11 4510 2.4GHz 12c 2x32GB-R 8SFF MR408i-o 2x480GB SATA SSD 2x800W PS AP Server	HPE ProLiant ML350 Gen11 4410Y 12c 2x32GB-R 8SFF MR408i-o 2x960GB SATA SSD 2x800W PS AR Server
<b>Chassis</b>	HPE ProLiant ML350 Gen11 SFF Configure-to-order Server	
<b>Processor</b>	4510 (12 core, 2.4 GHz, 150W)	4410Y (12 core, 2.0 GHz, 150W)
<b>Number of Processors</b>	One with standard heatsink	
<b>Memory</b>	64 GB (2x32 GB, 5600 MT/s) <b>Notes: Runs at 4400 MT/s due to processor limitation.</b>	64 GB (2x32 GB, 4800 MT/s) <b>Notes: Runs at 4000 MT/s due to processor limitation.</b>
<b>Accelerators</b>	Optional	
<b>Network Controller</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE <b>Notes: Slot 15 OCP will be occupied along with CPU 1 MCI0 port 1.</b>	
<b>Storage Controller</b>	HPE MR408i-o Gen11 x8 Lanes 4GB Cache OCP SPDM Storage Controller <b>Notes:</b> – Slot 14 OCP will be occupied, PCIe expansion slot is not required. – This controller supports up to 8 SAS/SATA/NVMe Drives with performance RAID. – Smart Storage battery included.	
<b>Included Drives</b>	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD	2x HPE 960GB SATA 6G Mixed Use SFF BC Multi Vendor SSD
<b>Optical Drive</b>	Optional DVD-ROM or DVD-RW. Optional Half-Height RDX, up to 1. Refer to the QuickSpecs for more detail.	
<b>Expansion Slots</b>	Default with 4 x8 PCIe 5.0 slots with primary riser cage. Upgradable with additional riser kit. <b>Notes: Dual processors are required to support expansion card on PCIe slots 5-10.</b>	
<b>Power Supply</b>	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	
<b>Fans</b>	3x Standard Fans <b>Notes: Configurations that require fan kits are provided in later sections</b>	
<b>Management</b>	HPE iLO Standard with Intelligent Provisioning (embedded), HPE OneView Standard (requires download); HPE iLO Advanced, HPE OneView Advanced (require licenses), and HPE Compute Ops Management	
<b>Security</b>	TPM (Trusted Platform Module)	
<b>Form Factor</b>	4U Tower, Optional Tower-to-Rack conversion kit (P47394-B21) to convert the unit to a 5U Rack-mount server.	
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.	



## ProLiant Gen10+ v2 Smart Choice

HPE ProLiant MicroServer Gen10 Plus v2 - Smart Choice Models			
<b>SKU Number</b>	P69101-005	P69102-005	P69103-005
<b>Model Name</b>	HPE ProLiant MicroServer Gen10 Plus v2 E-2314 4-core 1P 16GB-U VROC 4LFF-NHP 180W External PS Server	HPE ProLiant MicroServer Gen10 Plus v2 G6405 2-core 1P 16GB-U VROC 4LFF-NHP 180W External PS Server	HPE ProLiant MicroServer Gen10 Plus v2 E-2314 4-core VROC 4LFF-NHP 1TB 180W External PS Server
<b>Number of Processors</b>	One		
<b>Memory</b>	16 GB (1x 16 GB UDIMM DDR4 3200 MT/s) <b>Notes:</b> Total of 2 DIMM slots. With E-2314 processor, memory speed supports up to 3200 MT/s.	16 GB (1x 16 GB UDIMM DDR4 3200 MT/s) <b>Notes:</b> Total of 2 DIMM slots. With G6405 processor, memory speed supports up to 2666 MT/s.	16 GB (1x 16 GB UDIMM DDR4 3200 MT/s) <b>Notes:</b> Total of 2 DIMM slots. With E-2314 processor, memory speed supports up to 3200 MT/s.
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Embedded 1Gb 4-Port Intel i350-AM4 Controller		
<b>Storage Controller</b>	Embedded Intel VROC SATA SW RAID		
<b>Included Drives</b>	None included, four LFF non-hot plug drives supported	None included, four LFF non-hot plug drives supported	1x HPE 1TB SATA 7.2K LFF RW MV HDD
<b>Internal Storage</b>	4 LFF NHP SATA HDD cage		
<b>Optical Drive</b>	N/A		
<b>Expansion Slots</b>	1x standard (Low Profile) PCIe 4.0		
<b>Power Supply</b>	1x 180W External Power Adapter		
<b>Fans</b>	1x non-redundant system fan ships standard		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	Ultra Micro Tower		
<b>Warranty</b>	Server warranty includes 1-Year Parts, 1-Year Labor, 1-Year Onsite support with next business day response.		



## ProLiant Gen10+ v2 Smart Choice

HPE ProLiant MicroServer Gen10 Plus v2 - Smart Choice Models	
<b>SKU Number</b>	P70335-425
<b>Model Name</b>	HPE ProLiant MicroServer Gen10 Plus v2 E-2314 4-core 32GB-U VROC 180W External PS Server
<b>Number of Processors</b>	One
<b>Memory</b>	32 GB (2x 16 GB UDIMM DDR4 3200 MT/s) <b>Notes:</b> <ul style="list-style-type: none"> <li>– Total of 2 DIMM slots.</li> <li>– With E-2314 processor, memory speed supports up to 3200 MT/s.</li> </ul>
<b>Accelerators</b>	Optional
<b>Network Controller</b>	Embedded 1Gb 4-Port Intel i350-AM4 Controller
<b>Storage Controller</b>	Embedded Intel VROC SATA SW RAID
<b>Included Drives</b>	2x HPE 1TB SATA 7.2K LFF RW MV HDD
<b>Internal Storage</b>	4 LFF NHP SATA HDD cage
<b>Optical Drive</b>	N/A
<b>Expansion Slots</b>	1x standard (Low Profile) PCIe 4.0
<b>Power Supply</b>	1x 180W External Power Adapter
<b>Fans</b>	1x non-redundant system fan ships standard
<b>Security</b>	TPM (Trusted Platform Module)
<b>Form Factor</b>	Ultra Micro Tower
<b>Warranty</b>	Server warranty includes 1-Year Parts, 1-Year Labor, 1-Year Onsite support with next business day response.



## ProLiant Gen10+ Smart Choice

HPE ProLiant DL360 Gen10 Plus - Smart Choice Models			
<b>SKU Number</b>	P69298-005	P69299-005	P69749-005
<b>Model Name</b>	HPE ProLiant DL360 Gen10 Plus 4310 2.1GHz 12-core 1P 32GB-R S100i NC 8SFF 800W PS Server	HPE ProLiant DL360 Gen10 Plus 4310 2.1GHz 12-core 1P 32GB-R P408i-a NC 8SFF 800W PS Server	HPE ProLiant DL360 Gen10 Plus 4314 2.4GHz 16-core 1P 128GB-R MR416i-a NC 8SFF 800W PS Server
<b>Chassis</b>	HPE ProLiant DL360 Gen10 Plus 8SFF NC Configure-to-order Server		
<b>Processor</b>	4310 (12 core, 2.1 GHz, 120W)	4310 (12 core, 2.1 GHz, 120W)	4314 (16 core, 2.4 GHz, 135W)
<b>Number of Processors</b>	One with standard heatsink		
<b>Memory</b>	32 GB (1x32 GB, 3200 MT/s) <b>Notes:</b> Runs at 2667 MT/s due to processor limitation.	32 GB (1x32 GB, 3200 MT/s) <b>Notes:</b> Runs at 2667 MT/s due to processor limitation.	128 GB (4x32 GB, 3200 MT/s) <b>Notes:</b> Runs at 2667 MT/s due to processor limitation.
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE <b>Notes:</b> No embedded networking	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE <b>Notes:</b> No embedded networking	Broadcom BCM57416 Ethernet 10Gb 2-port BASE-T OCP3 Adapter for HPE <b>Notes:</b> No embedded networking
<b>Storage Controller</b>	HPE NS204i-p x2 Lanes NVMe PCIe3 x8 OS Boot Device	HPE Smart Array P408i-a SR Gen10 x8 Lanes 2GB Cache SAS 12G Modular Controller	HPE MR416i-a Gen10 Plus x16 Lanes 4GB Cache NVMe/SAS 12G Controller
<b>Included Drives</b>	None ship standard, 8 SFF supported	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD
<b>Optical Drive</b>	Not included (Optical Drive options available)		
<b>Expansion Slots</b>	2 PCIe: 1 x16 FH, 1 x16 LP		
<b>Power Supply</b>	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit		
<b>Fans</b>	7x High Performance fans	7x High Performance fans	5x Standard fans
<b>Management</b>	HPE iLO 5		
<b>Rail Kit</b>	HPE ProLiant DL300 Gen10 Plus 1U SFF Easy Install Rail Kit <b>Notes:</b> Server does not support shelf mounted rail kits ("L" brackets).		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	1U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		

## ProLiant Gen10+ Smart Choice

HPE ProLiant DL360 Gen10 Plus - Smart Choice Models			
<b>SKU Number</b>	P74645-D65	P77128-425	P77171-425
<b>Model Name</b>	HPE ProLiant DL360 Gen10 Plus 4310 2.1GHz 12c 64GB-R 8SFF MR416i-a 2x1.2TB HDD 2x800W RPS IN Server	HPE ProLiant DL360 Gen10 Plus 4309Y 8c 64GB-R 8SFF SR416i-a 2x480GB SATA SSD 2x800W PS EU Server	HPE ProLiant DL360 Gen10 Plus 4309Y 2.8GHz 8c 64GB-R 8SFF SR416i-a 2x2.4TB HDD 2x800W PS EU Server
<b>Chassis</b>	HPE ProLiant DL360 Gen10 Plus 8SFF NC Configure-to-order Server		
<b>Processor</b>	4310 (12 core, 2.1 GHz, 120W)	4309Y (8 core, 2.8 GHz, 105W) <b>Notes: 8/8/8 cores would result in 2.8/2.6/2.3 GHz operating points at 105W/95W/85W TDPs.</b>	4309Y (8 core, 2.8 GHz, 105W) <b>Notes: 8/8/8 cores would result in 2.8/2.6/2.3 GHz operating points at 105W/95W/85W TDPs.</b>
<b>Number of Processors</b>	One with standard heatsink		
<b>Memory</b>	64 GB (2x32 GB, 3200 MT/s) <b>Notes: Runs at 2667 MT/s due to processor limitation.</b>		
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE <b>Notes: No embedded networking</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE <b>Notes: No embedded networking.</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE <b>Notes: No embedded networking.</b>
<b>Storage Controller</b>	HPE MR416i-a Gen10 Plus x16 Lanes 4GB Cache NVMe/SAS 12G Controller	HPE SR416i-a Gen10 Plus x16 Lanes 4GB Cache NVMe/SAS 24G Controller	HPE SR416i-a Gen10 Plus x16 Lanes 4GB Cache NVMe/SAS 24G Controller
<b>Included Drives</b>	2x HPE 1.2TB SAS 12G Mission Critical 10K SFF BC 3-year Warranty HDD	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD	2x HPE 2.4TB SAS 12G Mission Critical 10K SFF BC 3-year Warranty 512e HDD
<b>Optical Drive</b>	Not included (Optical Drive options available)		
<b>Expansion Slots</b>	2 PCIe: 1 x16 FH, 1 x16 LP		
<b>Power Supply</b>	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	2x HPE 800W Flex Slot Titanium Hot Plug Low Halogen Power Supply Kit	2x HPE 800W Flex Slot Titanium Hot Plug Low Halogen Power Supply Kit
<b>Fans</b>	5x Standard fans		
<b>Management</b>	HPE iLO 5		
<b>Rail Kit</b>	HPE ProLiant DL300 Gen10 Plus 1U SFF Easy Install Rail Kit <b>Notes: Server does not support shelf mounted rail kits ("L" brackets).</b>		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	1U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		

## ProLiant Gen10+ Smart Choice

HPE ProLiant DL360 Gen10 Plus - Smart Choice Models			
<b>SKU Number</b>	P78116-DM5	P78123-DM5	P78124-DM5
<b>Model Name</b>	HPE ProLiant DL360 Gen10 Plus 4310 12c 2x32GB-R 8SFF SR416i-a 2x960GB SATA SSD 2x800W PS LA Server	HPE ProLiant DL360 Gen10 Plus 4310 2.1GHz 12c 2x32GB-R 8SFF SR416i-a 2x2.4TB HDD 2x800W PS LA Server	HPE ProLiant DL360 Gen10 Plus 4314 2.4GHz 16c 1P 64GB-R 8SFF NS204i-p NC BCM5719 2x800W PS MX Server
<b>Chassis</b>	HPE ProLiant DL360 Gen10 Plus 8SFF NC Configure-to-order Server		
<b>Processor</b>	4310 (12 core, 2.1 GHz, 120W)	4310 (12 core, 2.1 GHz, 120W)	4314 (16 core, 2.4 GHz, 135W)
<b>Number of Processors</b>	One with standard heatsink		
<b>Memory</b>	64 GB (2x32 GB, 3200 MT/s) <b>Notes:</b> Runs at 2667 MT/s due to processor limitation.		
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE <b>Notes:</b> No embedded networking.		
<b>Storage Controller</b>	HPE SR416i-a Gen10 Plus x16 Lanes 4GB Cache NVMe/SAS 24G Controller	HPE SR416i-a Gen10 Plus x16 Lanes 4GB Cache NVMe/SAS 24G Controller	HPE NS204i-p x2 Lanes NVMe PCIe3 x8 OS Boot Device
<b>Included Drives</b>	2x HPE 960GB SATA 6G Mixed Use SFF BC Multi Vendor SSD	2x HPE 2.4TB SAS 12G Mission Critical 10K SFF BC 3-year Warranty 512e HDD	None ship standard, 8 SFF supported
<b>Optical Drive</b>	Not included (Optical Drive options available)		
<b>Expansion Slots</b>	2 PCIe: 1 x16 FH, 1 x16 LP		
<b>Power Supply</b>	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit		
<b>Fans</b>	5x Standard fans	5x Standard fans	7x High Performance fans
<b>Management</b>	HPE iLO 5		
<b>Rail Kit</b>	HPE ProLiant DL300 Gen10 Plus 1U SFF Easy Install Rail Kit <b>Notes:</b> Server does not support shelf mounted rail kits (“L” brackets).		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	1U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		





## ProLiant Gen10+ Smart Choice

HPE ProLiant DL360 Gen10 Plus - Smart Choice Models			
<b>SKU Number</b>	P78125-DM5	P79765-375	P79766-375
<b>Model Name</b>	HPE ProLiant DL360 Gen10 Plus 4314 16c 2x32GB-R 8SFF SR416i-a 2x960GB SATA SSD 2x800W PS LA Server	HPE ProLiant DL360 Gen10 Plus 4309Y 2.8GHz 8c 1x32GB-R 8SFF SR416i-a 3x600GB HDD 2x800W PS AP Server	HPE ProLiant DL360 Gen10 Plus 4310 2.1GHz 12c 2x32GB-R 8SFF SR416i-a 2x2.4TB HDD 2x800W PS AP Server
<b>Chassis</b>	HPE ProLiant DL360 Gen10 Plus 8SFF NC Configure-to-order Server		
<b>Processor</b>	4314 (16 core, 2.4 GHz, 135W)	4309Y (8 core, 2.8 GHz, 105W) <b>Notes:</b> 8/8/8 cores would result in 2.8/2.6/2.3 GHz operating points at 105W/95W/85W TDPs.	4310 (12 core, 2.1 GHz, 120W)
<b>Number of Processors</b>	One with standard heatsink		
<b>Memory</b>	64 GB (2x32 GB, 3200 MT/s) <b>Notes:</b> Runs at 2667 MT/s due to processor limitation.	32 GB (1x32 GB, 3200 MT/s) <b>Notes:</b> Runs at 2667 MT/s due to processor limitation.	64 GB (2x32 GB, 3200 MT/s) <b>Notes:</b> Runs at 2667 MT/s due to processor limitation.
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE <b>Notes:</b> No embedded networking.		
<b>Storage Controller</b>	HPE SR416i-a Gen10 Plus x16 Lanes 4GB Cache NVMe/SAS 24G Controller		
<b>Included Drives</b>	2x HPE 960GB SATA 6G Mixed Use SFF BC Multi Vendor SSD	3x HPE 600GB SAS 12G Mission Critical 10K SFF BC 3-year Warranty Multi Vendor HDD	2x HPE 2.4TB SAS 12G Mission Critical 10K SFF BC 3-year Warranty 512e HDD
<b>Optical Drive</b>	Not included (Optical Drive options available)		
<b>Expansion Slots</b>	2 PCIe: 1 x16 FH, 1 x16 LP		
<b>Power Supply</b>	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit		
<b>Fans</b>	5x Standard fans		
<b>Management</b>	HPE iLO 5		
<b>Rail Kit</b>	HPE ProLiant DL300 Gen10 Plus 1U SFF Easy Install Rail Kit <b>Notes:</b> Server does not support shelf mounted rail kits ("L" brackets).		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	1U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		



## ProLiant Gen10+ Smart Choice

HPE ProLiant DL360 Gen10 Plus - Smart Choice Models	
<b>SKU Number</b>	P79767-375
<b>Model Name</b>	HPE ProLiant DL360 Gen10 Plus 4314 16c 2x32GB-R 8SFF SR416i-a 2x480GB SATA SSD 2x800W PS AP Server
<b>Chassis</b>	HPE ProLiant DL360 Gen10 Plus 8SFF NC Configure-to-order Server
<b>Processor</b>	4314 (16 core, 2.4 GHz, 135W)
<b>Number of Processors</b>	One with standard heatsink
<b>Memory</b>	64 GB (2x32 GB, 3200 MT/s) <b>Notes:</b> Runs at 2667 MT/s due to processor limitation.
<b>Accelerators</b>	Optional
<b>Network Controller</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE <b>Notes:</b> No embedded networking.
<b>Storage Controller</b>	HPE SR416i-a Gen10 Plus x16 Lanes 4GB Cache NVMe/SAS 24G Controller
<b>Included Drives</b>	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD
<b>Optical Drive</b>	Not included (Optical Drive options available)
<b>Expansion Slots</b>	2 PCIe: 1 x16 FH, 1 x16 LP
<b>Power Supply</b>	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit
<b>Fans</b>	5x Standard fans
<b>Management</b>	HPE iLO 5
<b>Rail Kit</b>	HPE ProLiant DL300 Gen10 Plus 1U SFF Easy Install Rail Kit <b>Notes:</b> Server does not support shelf mounted rail kits (“L” brackets).
<b>Security</b>	TPM (Trusted Platform Module)
<b>Form Factor</b>	1U Rack
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.



## ProLiant Gen10+ Smart Choice

HPE ProLiant DL380 Gen10 Plus - Smart Choice Models			
<b>SKU Number</b>	P69320-005	P69754-005	P69755-005
<b>Model Name</b>	HPE ProLiant DL380 Gen10 Plus 6326 2.9GHz 16-core 1P 32GB-R MR416i-a NC 8SFF 800W PS Server	HPE ProLiant DL380 Gen10 Plus 4310 2.1GHz 12-core 1P 64GB-R MR416i-a NC 8SFF 800W PS Server	HPE ProLiant DL380 Gen10 Plus 4314 2.4GHz 16-core 1P 128GB-R MR416i-a NC 8SFF 800W PS Server
<b>Chassis</b>	HPE ProLiant DL380 Gen10 Plus 8SFF NC Configure-to-order Server		
<b>Processor</b>	6326 (16 core, 2.9 GHz, 185W)	4310 (12 core, 2.1 GHz, 120W)	4314 (16 core, 2.4 GHz, 135W)
<b>Number of Processors</b>	One with high performance heatsink	One with standard heatsink	One with standard heatsink
<b>Memory</b>	32 GB (1x32 GB, 3200 MT/s)	64 GB (2x32 GB, 3200 MT/s) <b>Notes: Runs at 2667 MT/s due to processor limitation.</b>	128 GB (4x32 GB, 3200 MT/s) <b>Notes: Runs at 2667 MT/s due to processor limitation.</b>
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE <b>Notes: No embedded networking</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE <b>Notes: No embedded networking</b>	Broadcom BCM57416 Ethernet 10Gb 2-port BASE-T OCP3 Adapter for HPE <b>Notes: No embedded networking</b>
<b>Storage Controller</b>	HPE MR416i-a Gen10 Plus x16 Lanes 4GB Cache NVMe/SAS 12G Controller		
<b>Included Drives</b>	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD		
<b>Optical Drive</b>	Optional DVD-ROM Optional via Universal Media Bay External support only		
<b>Power Supply</b>	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit		
<b>Fans</b>	6x Maximum Performance Fans	6x Standard Fans	6x Standard Fans
<b>Management</b>	HPE iLO 5		
<b>Rail Kit</b>	HPE DL38X Gen10 Plus 2U SFF Easy Install Rail Kit <b>Notes: Easy Install w/ CMA</b>		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	2U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		



## ProLiant Gen10+ Smart Choice

HPE ProLiant DL380 Gen10 Plus - Smart Choice Models			
<b>SKU Number</b>	P74646-D65	P74647-D65	P77170-425
<b>Model Name</b>	HPE ProLiant DL380 Gen10 Plus 4310 2.1GHz 12c 64GB-R 12LFF MR416i-a 2x4TB HDD 2x800W RPS IN Server	HPE ProLiant DL380 Gen10 Plus 4310 2.1GHz 12c 64GB-R 8SFF MR416i-a 2x1.2TB HDD 2x800W RPS IN Server	HPE ProLiant DL380 Gen10 Plus 4309Y 8c 64GB-R 8SFF SR416i-a 2x480GB SATA SSD 2x800W PS EU Server
<b>Chassis</b>	HPE ProLiant DL380 Gen10 Plus 12LFF NC Configure-to-order Server	HPE ProLiant DL380 Gen10 Plus 8SFF NC Configure-to-order Server	HPE ProLiant DL380 Gen10 Plus 8SFF NC Configure-to-order Server
<b>Processor</b>	4310 (12 core, 2.1 GHz, 120W)	4310 (12 core, 2.1 GHz, 120W)	4309Y (8 core, 2.8 GHz, 105W) <b>Notes:</b> 8/8/8 cores would result in 2.8/2.6/2.3 GHz operating points at 105W/95W/85W TDPs.
<b>Number of Processors</b>	One with standard heatsink		
<b>Memory</b>	64 GB (2x32 GB, 3200 MT/s) <b>Notes:</b> Runs at 2667 MT/s due to processor limitation.		
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE		
<b>Storage Controller</b>	HPE MR416i-a Gen10 Plus x16 Lanes 4GB Cache NVMe/SAS 12G Controller	HPE MR416i-a Gen10 Plus x16 Lanes 4GB Cache NVMe/SAS 12G Controller	HPE SR416i-a Gen10 Plus x16 Lanes 4GB Cache NVMe/SAS 24G Controller
<b>Included Drives</b>	2x HPE 4TB SATA 6G Business Critical 7.2K LFF LP 1-year Warranty Multi Vendor HDD	2x HPE 1.2TB SAS 12G Mission Critical 10K SFF BC 3-year Warranty HDD	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD
<b>Optical Drive</b>	Optional DVD-ROM Optional via Universal Media Bay External support only		
<b>Power Supply</b>	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	2x HPE 800W Flex Slot Titanium Hot Plug Low Halogen Power Supply Kit
<b>Fans</b>	6x Performance Fans	6x Standard Fans	6x Maximum Performance Fans
<b>Management</b>	HPE iLO 5		
<b>Rail Kit</b>	HPE DL38X Gen10 Plus 2U LFF Easy Install Rail Kit <b>Notes:</b> Easy Install w/ CMA	HPE DL38X Gen10 Plus 2U SFF Easy Install Rail Kit <b>Notes:</b> Easy Install w/ CMA	HPE DL38X Gen10 Plus 2U SFF Easy Install Rail Kit <b>Notes:</b> Easy Install w/ CMA
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	2U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		

## ProLiant Gen10+ Smart Choice

HPE ProLiant DL380 Gen10 Plus - Smart Choice Models			
<b>SKU Number</b>	P78126-DM5	P79772-375	P79773-375
<b>Model Name</b>	HPE ProLiant DL380 Gen10 Plus 4310 2.1GHz 12c 64GB-R 8SFF SR416i-a 2x2.4TB HDD 2x800W PS MX Server	HPE ProLiant DL380 Gen10 Plus 4309Y 2.8GHz 8c 1x32GB-R 8SFF SR416i-a 3x600GB HDD 2x800W PS AP Server	HPE ProLiant DL380 Gen10 Plus 4310 2.1GHz 12c 2x32GB-R 8SFF SR416i-a 2x600GB HDD 2x800W PS AP Server
<b>Chassis</b>	HPE ProLiant DL380 Gen10 Plus 8SFF NC Configure-to-order Server		
<b>Processor</b>	4310 (12 core, 2.1 GHz, 120W)	4309Y (8 core, 2.8 GHz, 105W) <b>Notes: 8/8/8 cores would result in 2.8/2.6/2.3 GHz operating points at 105W/95W/85W TDPs.</b>	4310 (12 core, 2.1 GHz, 120W)
<b>Number of Processors</b>	One with standard heatsink		
<b>Memory</b>	64 GB (2x32 GB, 3200 MT/s) <b>Notes: Runs at 2667 MT/s due to processor limitation.</b>	32 GB (1x32 GB, 3200 MT/s) <b>Notes: Runs at 2667 MT/s due to processor limitation.</b>	64 GB (2x32 GB, 3200 MT/s) <b>Notes: Runs at 2667 MT/s due to processor limitation.</b>
<b>Accelerators</b>	Optional		
<b>Network Controller</b>	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE		
<b>Storage Controller</b>	HPE SR416i-a Gen10 Plus x16 Lanes 4GB Cache NVMe/SAS 24G Controller		
<b>Included Drives</b>	2x HPE 2.4TB SAS 12G Mission Critical 10K SFF BC 3-year Warranty 512e HDD	3x HPE 600GB SAS 12G Mission Critical 10K SFF BC 3-year Warranty Multi Vendor HDD	2x HPE 600GB SAS 12G Mission Critical 10K SFF BC 3-year Warranty Multi Vendor HDD
<b>Optical Drive</b>	Optional DVD-ROM Optional via Universal Media Bay External support only		
<b>Power Supply</b>	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit		
<b>Fans</b>	6x Maximum Performance Fans		
<b>Management</b>	HPE iLO 5		
<b>Rail Kit</b>	HPE DL38X Gen10 Plus 2U SFF Easy Install Rail Kit <b>Notes: Easy Install w/ CMA</b>		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	2U Rack		
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		



## ProLiant Gen10+ Smart Choice

HPE ProLiant DL380 Gen10 Plus - Smart Choice Models	
<b>SKU Number</b>	P79774-375
<b>Model Name</b>	HPE ProLiant DL380 Gen10 Plus 4314 16c 2x32GB-R 8SFF SR416i-a 2x480GB SATA SSD 2x800W PS AP Server
<b>Chassis</b>	HPE ProLiant DL380 Gen10 Plus 8SFF NC Configure-to-order Server
<b>Processor</b>	4314 (16 core, 2.4 GHz, 135W)
<b>Number of Processors</b>	One with standard heatsink
<b>Memory</b>	64 GB (2x32 GB, 3200 MT/s) <b>Notes: Runs at 2667 MT/s due to processor limitation.</b>
<b>Accelerators</b>	Optional
<b>Network Controller</b>	Broadcom BCM57412 Ethernet 10Gb 2-port SFP+ OCP3 Adapter for HPE
<b>Storage Controller</b>	HPE SR416i-a Gen10 Plus x16 Lanes 4GB Cache NVMe/SAS 24G Controller
<b>Included Drives</b>	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD
<b>Optical Drive</b>	Optional DVD-ROM Optional via Universal Media Bay External support only
<b>Power Supply</b>	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit
<b>Fans</b>	6x Maximum Performance Fans
<b>Management</b>	HPE iLO 5
<b>Rail Kit</b>	HPE DL38X Gen10 Plus 2U SFF Easy Install Rail Kit <b>Notes: Easy Install w/ CMA</b>
<b>Security</b>	TPM (Trusted Platform Module)
<b>Form Factor</b>	2U Rack
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.



## ProLiant Gen10 Smart Choice

HPE ProLiant DL360 Gen10 - Smart Choice Models			
<b>SKU Number</b>	P69746-005	P69748-005	P71373-425
<b>Model Name</b>	HPE ProLiant DL360 Gen10 4208 2.1GHz 8-core 1P 64GB-R P408i-a 8SFF 800W PS Server	HPE ProLiant DL360 Gen10 4210R 2.4GHz 10-core 1P 64GB-R P408i-a 8SFF 800W PS Server	HPE ProLiant DL360 Gen10 4208 2.1GHz 8c 1P 64GB-R 8SFF P408i-a 2x960GB SSD 2x800W RPS EMEA Server
<b>Chassis</b>	HPE ProLiant DL360 Gen10 8SFF Configure-to-order Server		
<b>Processor</b>	4208 (8 core, 2.1 GHz, 85W)	4210R (10 core, 2.4 GHz, 100W)	4208 (8 core, 2.1 GHz, 85W)
<b>Number of Processors</b>	One		
<b>Memory</b>	64 GB (2x32 GB, 2933 MT/s) <b>Notes: Runs at 2400 MT/s due to processor limitation.</b>	64 GB (2x32 GB, 2933 MT/s) <b>Notes: Runs at 2400 MT/s due to processor limitation.</b>	64 GB (2x32 GB, 2933 MT/s) <b>Notes: Runs at 2400 MT/s due to processor limitation.</b>
<b>Network Controller</b>	Embedded 4 x 1GbE Ethernet Adapter		
<b>Storage Controller</b>	HPE Smart Array P408i-a SR Gen10 x8 Lanes 2GB Cache SAS 12G Modular Controller		
<b>Included Drives</b>	2x 480GB SATA SSD	2x 480GB SATA SSD	2x 960GB SATA SSD
<b>Optical Drive</b>	Not included (Optical Drive options available)	Not included (Optical Drive options available)	Not included
<b>Power Supply</b>	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit	2x HPE 800W Flex Slot Titanium Hot Plug Low Halogen Power Supply Kit
<b>Fans</b>	5 single rotor hot plug fans		
<b>Rail Kit</b>	HPE Gen10 1U SFF Easy Install Rail Kit		
<b>Security</b>	TPM (Trusted Platform Module)		
<b>Form Factor</b>	1U Rack		
<b>Warranty</b>	Server Warranty includes three years of parts, three years of labor, three years of onsite support coverage.		



## ProLiant Gen10 Smart Choice

HPE ProLiant DL380 Gen10 - Smart Choice Models	
<b>SKU Number</b>	P69753-005
<b>Model Name</b>	HPE ProLiant DL380 Gen10 4210R 2.4GHz 10-core 1P 64GB-R P408i-a 8SFF BC 800W PS Server
<b>Chassis</b>	HPE ProLiant DL380 Gen10 8SFF Configure-to-order Server
<b>Processor</b>	4210R (10 core, 2.4 GHz, 100W)
<b>Number of Processors</b>	One
<b>Memory</b>	64 GB (2x32 GB, 2933 MT/s) <b>Notes:</b> Runs at 2400 MT/s due to processor limitation.
<b>Network Controller</b>	1x Embedded 4 x 1GbE Ethernet Adapter
<b>Storage Controller</b>	HPE Smart Array P408i-a SR Gen10 x8 Lanes 2GB Cache SAS 12G Modular Controller
<b>Included Drives</b>	2x 480GB SATA SSD
<b>Internal Storage</b>	8 SFF (upgradeable to 24 SFF front + 6 SFF rear)
<b>Optical Drive</b>	Optional
<b>Expansion Slots</b>	3-slots (x8, x16, x8 with dual m.2) as standard; upgradeable to 8-slots in a 2 processor configuration
<b>Power Supply</b>	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit
<b>Fans</b>	4x Standard
<b>Management</b>	HPE iLO Standard with Intelligent Provisioning (embedded), HPE OneView Standard (requires download); HPE iLO Advanced, HPE iLO Advanced Premium Security Edition and HPE OneView Advanced (require licenses)
<b>Security</b>	TPM (Trusted Platform Module)
<b>Form Factor</b>	2U Rack
<b>Warranty</b>	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response





## MSA Smart Choice

HPE MSA - Smart Choice Models			
<b>SKU Number</b>	P76569-B25	P76570-B25	P76571-B25
<b>Model Name</b>	HPE MSA 2070 SFF 2x10/25GbE iSCSI 4-port Cntrl 12x3.84TB SSD 4x10Gb iSCSI XCVR 46TB Storage Array	HPE MSA 2070 SFF 2x16Gb FC 4-port Controller 12x3.84TB SSD 4x16Gb SFP FC XCVR 46TB Storage Array	HPE MSA 2070 SFF 2x10/25GbE iSCSI 4-port Cntrl 12x1.92TB SSD 4x10Gb iSCSI XCVR 23TB Storage Array
<b>Form Factor</b>	2U rack mount		
<b>Storage Controller</b>	2x 10/25 GbE iSCSI 4-port Controller	2x 16 Gb Fibre Channel 4-port Controller	2x 10/25 GbE iSCSI 4-port Controller
<b>Host Connectivity</b>	10/25 GbE iSCSI	16 Gb Fibre Channel	10/25 GbE iSCSI
<b>Transceivers Included</b>	HPE MSA 10Gb Short Range iSCSI SFP+ 4-pack Transceiver	HPE MSA 16Gb Short Wave Fibre Channel SFP+ 4-pack Transceiver	HPE MSA 10Gb Short Range iSCSI SFP+ 4-pack Transceiver
<b>Available Drive Bays</b>	24 SFF drive bays total; 12 SFF drive bays available.		
<b>Drives Included</b>	12x HPE MSA 3.84TB SAS 12G Read Intensive SFF (2.5in) M2 3yr Wty SSD	12x HPE MSA 3.84TB SAS 12G Read Intensive SFF (2.5in) M2 3yr Wty SSD	12x HPE MSA 1.92TB SAS 12G Read Intensive SFF (2.5in) M2 3yr Wty SSD
<b>Rail Kit</b>	MSA 2U Rail Kit included		
<b>Warranty</b>	Three-year limited warranty, parts exchange next business day delivery on all base arrays and drive enclosures. MSA drives and other options carry a separate warranty.		



## MSA Smart Choice

HPE MSA - Smart Choice Models	
<b>SKU Number</b>	P76572-B25
<b>Model Name</b>	HPE MSA 2070 SFF 2x16Gb FC 4-port Controller 12x1.92TB SSD 4x16Gb SFP FC XCVR 23TB Storage Array
<b>Form Factor</b>	2U rack mount
<b>Storage Controller</b>	2x 16 Gb Fibre Channel 4-port Controller
<b>Host Connectivity</b>	16 Gb Fibre Channel
<b>Transceivers Included</b>	HPE MSA 16Gb Short Wave Fibre Channel SFP+ 4-pack Transceiver
<b>Available Drive Bays</b>	24 SFF drive bays total; 12 SFF drive bays available.
<b>Drives Included</b>	12x HPE MSA 1.92TB SAS 12G Read Intensive SFF (2.5in) M2 3yr Wty SSD
<b>Rail Kit</b>	MSA 2U Rail Kit included
<b>Warranty</b>	Three-year limited warranty, parts exchange next business day delivery on all base arrays and drive enclosures. MSA drives and other options carry a separate warranty.



## Storage Tape Smart Choice

HPE Storage Tape - Smart Choice Models			
<b>SKU Number</b>	P77033-B25	P77034-B25	P77035-B25
<b>Model Name</b>	HPE Storage LTO-8 Ultrium Rack Mount Tape Drive 5x LTO-8 30TB Data Cartridges	HPE Storage LTO-9 Ultrium Rack Mount Tape Drive 5x LTO-9 45TB Data Cartridges	HPE Storage MSL 1/8 Tape Autoloader 1x MSL LTO-8 SAS Drive 5x LTO-8 30TB Data Cartridges
<b>Tape Drive</b>	1x HPE StoreEver LTO-8 Ultrium 30750 Internal Tape Drive	1x HPE StoreEver LTO-9 Ultrium 45000 Internal Tape Drive	1x HPE StoreEver MSL LTO-8 Ultrium 30750 SAS Drive Upgrade Kit
<b>Module</b>	None	None	1x HPE StoreEver MSL 1/8 G2 0-drive Tape Autoloader
<b>Rack-Mount Kit</b>	1x HPE StoreEver 1U Generic Rack Mount Kit	1x HPE StoreEver 1U Generic Rack Mount Kit	1x HPE StoreEver 1/8 G2 Tape Autoloader Rack Kit
<b>Cable Kit</b>	1x HPE StoreEver 4m Mini SAS HD (SFF-8644) LTO Drive Cable for 1U Rack Mount Kit	1x HPE 12Gb Mini SAS High Density (SFF-8644) to LTO Drive 4m Cable for 1U Rack Mount Kit	None
<b>Data Cartridges (media)</b>	5x HPE LTO-8 Ultrium 30TB RW Data Cartridge	5x HPE LTO-9 Ultrium 45TB RW Data Cartridge	5x HPE LTO-8 Ultrium 30TB RW Data Cartridge
<b>Label Pack</b>	None	None	1x HPE LTO-8 Ultrium RW Bar Code Label Pack



## Storage Tape Smart Choice

HPE Storage Tape - Smart Choice Models		
<b>SKU Number</b>	P77036-B25	P77037-B25
<b>Model Name</b>	HPE Storage MSL2024 Tape Library 1x MSL LTO-8 SAS Drive 15x LTO-8 30TB Data Cartridges	HPE Storage MSL3040 Tape Library 1x MSL LTO-9 SAS Drive 20x LTO-9 45TB Data Cartridges
<b>Tape Drive</b>	1x HPE StoreEver MSL LTO-8 Ultrium 30750 SAS Drive Upgrade Kit	1x HPE StoreEver MSL LTO-9 Ultrium 45000 SAS Drive Upgrade Kit
<b>Module</b>	1x HPE StoreEver MSL2024 0-drive Tape Library	1x HPE StoreEver MSL3040 Scalable Library Base Module
<b>Cable Kit</b>	None	None
<b>Data Cartridges (media)</b>	15x HPE LTO-8 Ultrium 30TB RW Data Cartridge	20x HPE LTO-9 Ultrium 45TB RW Data Cartridge
<b>Label Pack</b>	1x HPE LTO-8 Ultrium RW Bar Code Label Pack	1x HPE LTO-9 Ultrium RW Bar Code Label Pack



## Full ProLiant Server QuickSpecs

HPE Smart Choice products are fully configured and ready-to-ship. Core options within the integrated server may not be changed, but in some cases additional options for expansion and upgrade of the product may be possible. To understand potential option choices, please view the Additional Options section of the base product's QuickSpecs.

### Full ProLiant Server QuickSpecs

- HPE ProLiant DL20 Gen11: <https://www.hpe.com/psnow/doc/a50007009enw>
  - HPE ProLiant DL320 Gen11: <https://www.hpe.com/psnow/doc/a50004315enw>
  - HPE ProLiant DL325 Gen11: <https://www.hpe.com/psnow/doc/a50004297enw>
  - HPE ProLiant DL345 Gen11: <https://www.hpe.com/psnow/doc/a50004298enw>
  - HPE ProLiant DL360 Gen11: <https://www.hpe.com/psnow/doc/a50004306enw>
  - HPE ProLiant DL365 Gen11: <https://www.hpe.com/psnow/doc/a50004299enw>
  - HPE ProLiant DL380 Gen11: <https://www.hpe.com/psnow/doc/a50004307enw>
  - HPE ProLiant MicroServer Gen11: <https://www.hpe.com/psnow/doc/a50007028enw>
  - HPE ProLiant DL385 Gen11: <https://www.hpe.com/psnow/doc/a50004300enw>
  - HPE ProLiant ML30 Gen11: <https://www.hpe.com/psnow/doc/a50007008enw>
  - HPE ProLiant ML110 Gen11: <https://www.hpe.com/psnow/doc/a00054055enw>
  - HPE ProLiant ML350 Gen11: <https://www.hpe.com/psnow/doc/a50004308enw>
  - HPE ProLiant MicroServer Gen10 Plus v2: <https://www.hpe.com/psnow/doc/a50004293enw>
  - HPE ProLiant DL20 Gen10 Plus Server: <https://www.hpe.com/psnow/doc/a50002583enw>
  - HPE ProLiant DL360 Gen10 Plus Server: <https://www.hpe.com/psnow/doc/a50002559enw>
  - HPE ProLiant DL380 Gen10 Plus Server: <https://www.hpe.com/psnow/doc/a50002553enw>
  - HPE ProLiant DL360 Gen10 Server: <https://www.hpe.com/psnow/doc/a00008159enw>
  - HPE ProLiant DL380 Gen10 Server: <https://www.hpe.com/psnow/doc/a00008180enw>
- 



## Full Storage Product QuickSpecs

### Full Storage Product QuickSpecs

- HPE StoreEver MSL Entry-level Tape Automation and HPE StoreEver MSL Tape Libraries: <https://www.hpe.com/psnow/doc/c04154359>
  - HPE StoreEver MSL3040 Tape Library: <https://www.hpe.com/psnow/doc/a00026511enw>
  - HPE StoreEver Rack-mount Kits: <https://www.hpe.com/psnow/doc/c04154496>
  - HPE MSA 1060 Storage: <https://www.hpe.com/psnow/doc/a00094628enw>
  - HPE MSA 2060 Storage: <https://www.hpe.com/psnow/doc/a00094629enw>
  - HPE MSA 2062 Storage: <https://www.hpe.com/psnow/doc/a00094630enw>
  - HPE MSA Gen7 Storage: <https://www.hpe.com/psnow/doc/a50009222enw>
- 





## Summary of Changes

Date	Version History	Action	Description of Change
02-Dec-2024	Version 3	Changed	HPE Services SKUs, HPE ProLiant DL20 Gen11, HPE ProLiant DL145 Gen11, HPE ProLiant DL320 Gen11, HPE ProLiant DL325 Gen11, HPE ProLiant DL345 Gen11, HPE ProLiant DL360 Gen11, HPE ProLiant DL365 Gen11, HPE ProLiant DL365 Gen11, HPE ProLiant DL385 Gen11, HPE ProLiant MicroServer Gen11, HPE ProLiant ML30 Gen11, HPE ProLiant ML110 Gen11, HPE ProLiant ML350 Gen11, HPE ProLiant MicroServer Gen10 Plus v2, HPE ProLiant DL360 Gen10 Plus, HPE ProLiant DL360 Gen10 Plus, HPE ProLiant DL380 Gen10 Plus, HPE ProLiant DL360 Gen10, HPE ProLiant DL380 Gen10, HPE MSA - Smart Choice Models and HPE Storage Tape - Smart Choice Models were updated.
30-Sep-2024	Version 2	Changed	HPE ProLiant DL20 Gen11, HPE ProLiant DL320 Gen11, HPE ProLiant MicroServer Gen10 Plus v2, HPE ProLiant DL20 Gen10 Plus, HPE ProLiant DL345 Gen11 and HPE ProLiant DL360 Gen10 Smart Choice Models were updated.
03-Sep-2024	Version 1	New	New QuickSpecs.



## Copyright

Make the right purchase decision.  
Contact our presales specialists.



---

© Copyright 2024 Hewlett Packard Enterprise Development LP. The information contained herein is subject to change without notice. The only warranties for Hewlett Packard Enterprise products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. Hewlett Packard Enterprise shall not be liable for technical or editorial errors or omissions contained herein.

Intel® and Xeon® are registered trademarks of Intel Corporation in the U.S. and other countries.

Microsoft®, Windows®, and Windows Server® are U.S. registered trademarks of the Microsoft group of companies.

For hard drives, 1GB = 1 billion bytes. Actual formatted capacity is less

a50009219enw - 17251 - Worldwide - V3 - 02-December-2024