C2G

10ft (3m) High Speed HDMI® Cable With Gripping Connectors - 4K 60Hz

Part No. CG-29678



The C2G High Speed HDMI with Ethernet Cable supports all HDMI 2.0 features and is perfect for home theater or desktop audio video applications requiring high speed HDMI features and video resolutions up to 4K (4096 x 2160 at 60Hz, 4:4:4). The Ethernet capabilities of the cable allow a user to connect multiple Ethernet enabled HDMI devices through a single Ethernet connection for accessing interactive online content or updating device firmware. This fully-functional, high bandwidth cable is tested to perform at industry standards and is backed by a lifetime warranty. This cable can be utilized for network switch stacking with compatible equipment. Experience the latest HDMI features including:<

Features & Benefits

- Supports all HDMI 2.0 features including resolutions up to 4K (4096 x 2160 at 60Hz, 4:4:4)
- Designed to support High Speed HDMI features including ethernet
- Fully compatible with HDMI Stacking for Network Switches
- Three times greater port retention than standard HDMI connectors
- Gold plated connectors

Specifications

General Info

Product Line	C2G	Color	Black
UPC Number	757120296782	Country Of Origin	China
Application Sector	Residential, Commercial	Warranty Type	Lifetime
Type	Cable		

Dimensions

Cable Length	10 ft

Additional Information

Prop 65 Warning Required	Yes	Prop 65 Warning Language	Cancer and Reproductive Harm

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Wire Gauge	28 AWG
Video Resolution	4K 60Hz, 4K 30Hz, 4K, 1080p	Cable Type	High Speed HDMI, Video
Jacket Rating	Standard Non-Rated	Data Transfer Rate	18 Gbps
Adapter Rear	HDMI Male	Adapter Front	HDMI Male