



# Cisco headsets and webcams

# Contents

03	Wired headsets
04	Wireless headsets
05	Wireless headsets Desk cameras
06	Spec sheets

# Wired headsets

## 320 Series

Wired for desk users

**Professional value:** Wired headset available in mono or stereo ear with fixed RJ or USB-A cable, and optional USB-C adapter. Includes an in-line controller with a Webex or Microsoft Teams button to easily join meetings.



321



322



**In-line controller**  
Webex or Microsoft Teams button available on USB models

## 520 Series

Wired for desk and mobile users

**Professional:** Wired headset available in mono or stereo ear with fixed USB-A or USB-C cable. Includes 3.5mm breakout, in-line controller, and soft carrying case.



521



522



**in-line controller**

## 530 Series

Wired for desk users

**Professional:** Wired headset available in mono or stereo ear with USB-A, USB-C, or RJ cable. Includes an in-line controller on USB models, quick disconnect, soft carrying case, and option to add an agent training cable.



531



532



**in-line controller**

# Wireless headsets

## 560 Series

Wireless for desk users

**Professional:** Wireless DECT 6.0 headset available in mono or stereo ear. Includes an option for a standard base with 1 USB connection or a multi base with 2 USB and 1 Bluetooth® connection.



**561**  
Standard base



**562**  
Standard base



**561**  
Multi base



**562**  
Multi base

## 720 Series

Wireless for hybrid users

**Hybrid:** Wireless headset available in mono or stereo with Bluetooth® 5.0. Includes a boom arm with flip-to-mute, voice activated microphones, Webex or Microsoft Teams\* button, USB HD adapter, and a soft carrying case.



**721**



**722**



USB HD adapter



Webex button  
or Microsoft  
Teams button



## 730

Wireless for hybrid users

**Hybrid:** Wireless headset with Bluetooth® 5.0. Includes a boomless design, Active Noise Cancellation, voice activated microphones, customizable listening modes, smart sensors, USB HD adapter, and hard carrying case. Charging stand is available as an optional accessory.



**730**  
730 Carbon Black with  
optional charging stand



**730**  
Platinum



USB HD adapter

# Wireless headsets

## Bang & Olufsen Cisco 950

Wireless for hybrid users

**Premium hybrid:** True wireless earbuds with Bluetooth® 5.2. Includes premium materials, mono or stereo wearing options, Active Noise Cancellation, B&O Signature Sound with customizable listening modes, optional USB HD adapter.



**Bang & Olufsen Cisco 950**  
Black Anthracite



USB HD adapter  
*Sold separately*

## Bang & Olufsen Cisco 980

Wireless for hybrid users

**Premium hybrid:** Wireless headset with Bluetooth® 5.1. Includes premium materials, Active Noise Cancellation, B&O Signature Sound with customizable listening modes, USB HD adapter, USB-A, 3.5mm cable, and hard carrying case.



**Bang & Olufsen Cisco 980**  
First Light



**Bang & Olufsen Cisco 980**  
Black Anthracite



USB HD adapter

# Desk Cameras

Webcams for any workspace

**Hybrid:** Web camera with easy setup, multiple mounting options, customizable image settings, and a built-in privacy shutter.



**Desk Camera 1080p** includes 1080p video resolution, and a USB-A cable.



**Desk Camera 4K - Carbon Black and Platinum** Includes up to 4K video resolution, intelligent features, 2 color options, and is certified for Webex and Microsoft Teams.



# Headset specs

## Appendix A: Headset specs

WIRED				WIRELESS				
<b>Model</b>	320 Series 321 - 322	520 Series 521 - 522	530 Series 531 - 532	560 Series 561 - 562	720 Series 721 - 722	730	Bang & Olufsen Cisco 950	Bang & Olufsen Cisco 980
<b>Key feature</b>	Webex button	3.5mm breakout in-line controller	Agent training cable	DECT range 300+ft	Webex button	Smart sensors	B&O Signature Sound	B&O Signature Sound
<b>Wearing</b>	On Ear - Mono On Ear - Stereo	On Ear - Mono On Ear - Stereo	On Ear - Mono On Ear - Stereo	On Ear - Mono On Ear - Stereo	On Ear - Mono On Ear - Stereo	On Ear - Stereo	True Wireless Earbuds	Over Ear - Stereo
<b>Ear cushion material</b>	Foam	Leatherette	Leatherette	Leatherette	Foam + Leatherette	Foam + Leatherette	COMPLY™ Foam + 4 silicon tips	Memory Foam + Lamb skin Leather
<b>Wireless</b>	No	No	No	DECT 6.0 Bluetooth with Multi-Base	Bluetooth 5.0 USB HD Adapter	Bluetooth 5.0 USB HD Adapter	Bluetooth 5.2 USB HD Adapter	Bluetooth 5.1 USB HD Adapter
<b>Connection</b>	RJ9, USB-A, or USB-C (via adapter)	USB-A, USB-C, or 3.5mm	RJ9, USB-A or USB-C	USB-A, USB-C (optional), or Y Cable (RJ/AUX)	USB-C to USB-A	USB-C to USB-A & 3.5mm	USB-C to USB-A or Wireless Qi Charging	USB-C to USB-A & 3.5mm
<b>Simultaneous connection</b>	1	1	1	1 (SB) / 3 (MB)	3 (2 Bluetooth + 1 USB)	3 (2 Bluetooth + 1 USB)	2 Bluetooth	3 (2 Bluetooth + 1 USB)
<b>Quick disconnect</b>	No	No	Yes	N/A	N/A	N/A	N/A	N/A
<b>Microphone boom</b>	Yes	Yes	Yes	Yes	Yes	Boomless	Boomless	Boomless
<b>Noise reduction</b>	1x directional mic	1x directional mic	1x directional mic	1x directional mic	2 directional mics, AI Voice Activated Microphones	6 mics, 2 beamforming with AI Voice Activated Microphones	6 mics, 4 beamforming	6 mics, 4 beamforming
<b>Audio quality</b>	30mm speaker	32mm speaker	32mm speaker	32mm speaker	30mm speaker	40mm speaker Qualcomm aptX™ HD Audio	9.2mm speaker Qualcomm aptX™ Adaptive	40mm speaker (Neodymium magnets) Qualcomm aptX™ Adaptive
<b>Passive noise cancelation</b>	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
<b>Active Noise Cancelation</b>	No	No	No	No	No	Yes	Yes	Yes
<b>Talk time</b>	N/A	N/A	N/A	Up to 10 hrs	Up to 23 hrs	Up to 20 hrs	Up to 5 hrs for each earbud	Up to 23 hrs
<b>Enterprise security</b>	Wired	Wired	Wired	128 AES bit encryption	Image authentication Secure Boot	Image authentication Secure Boot	Image authentication Secure Boot	Image authentication Secure Boot
<b>Cisco Management &amp; Analytics</b>	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
<b>Datasheet link</b>	<a href="#">320 Series</a>	<a href="#">500 Series</a>	<a href="#">500 Series</a>	<a href="#">500 Series</a>	<a href="#">720 Series</a>	<a href="#">730 Series</a>	<a href="#">Bang &amp; Olufsen Cisco 950</a>	<a href="#">Bang &amp; Olufsen Cisco 980</a>

# Camera specs

## Appendix B: Camera specs

DESK CAMERAS		
Model	Desk Camera 1080p	Desk Camera 4K
Color	Carbon Black	Carbon Black, Platinum
Material	Plastic	Aluminum
Max resolution	1080p	4K
Best overview	No	Yes
Max frames per second	30	60 (1080p)
Max field of view	83 degrees	81 degrees
Image sensor	8MP	13MP
Infrared sensor	No	Yes
Dedicated AI Chip	No	Yes
Digital zoom	4x	10x
Intelligent features	No	Yes
Certifications		Windows Hello Microsoft Teams
Datasheet link	<a href="#">Desk Camera 1080p</a>	<a href="#">Desk Camera 4K</a>

October 2023



For more information

Explore [headsets](#) and [webcams](#) on [webex.com](#)