

ProLiant Gen10+ Smart Choice

HPE ProLiant DL360 Gen10 Plus - Smart Choice Models			
SKU Number	P79765-375	P79766-375	P79767-375
Model Name	HPE ProLiant DL360 Gen10 Plus 4309Y 2.8GHz 8c 1x32GB-R 8SFF SR416i-a 3x600GB HDD 2x800W PS AP Server	HPE ProLiant DL360 Gen10 Plus 4310 2.1GHz 12c 2x32GB-R 8SFF SR416i-a 2x2.4TB HDD 2x800W PS AP Server	HPE ProLiant DL360 Gen10 Plus 4314 16c 2x32GB-R 8SFF SR416i-a 2x480GB SATA SSD 2x800W PS AP Server
Chassis	HPE ProLiant DL360 Gen10 Plus 8SFF NC Configure-to-order Server		
Processor	4309Y (8 core, 2.8 GHz, 105W) Notes: 8/8/8 cores would result in 2.8/2.6/2.3 GHz operating points at 105W/95W/85W TDPs.	4310 (12 core, 2.1 GHz, 120W)	4314 (16 core, 2.4 GHz, 135W)
Number of Processors	One with standard heatsink		
Memory	32 GB (1x32 GB, 3200 MT/s) Notes: Runs at 2667 MT/s due to processor limitation.	64 GB (2x32 GB, 3200 MT/s) Notes: Runs at 2667 MT/s due to processor limitation.	64 GB (2x32 GB, 3200 MT/s) Notes: Runs at 2667 MT/s due to processor limitation.
Accelerators	Optional		
Network Controller	Broadcom BCM5719 Ethernet 1Gb 4-port BASE-T OCP3 Adapter for HPE Notes: No embedded networking.		
Storage Controller	HPE SR416i-a Gen10 Plus x16 Lanes 4GB Cache NVMe/SAS 24G Controller		
Included Drives	3x HPE 600GB SAS 12G Mission Critical 10K SFF BC 3-year Warranty Multi Vendor HDD	2x HPE 2.4TB SAS 12G Mission Critical 10K SFF BC 3-year Warranty 512e HDD	2x HPE 480GB SATA 6G Read Intensive SFF BC Multi Vendor SSD
Optical Drive	Not included (Optical Drive options available)		
Expansion Slots	2 PCIe: 1 x16 FH, 1 x16 LP		
Power Supply	2x HPE 800W Flex Slot Platinum Hot Plug Low Halogen Power Supply Kit		
Fans	5x Standard fans		
Management	HPE iLO 5		
Rail Kit	HPE ProLiant DL300 Gen10 Plus 1U SFF Easy Install Rail Kit Notes: Server does not support shelf mounted rail kits ("L" brackets).		
Security	TPM (Trusted Platform Module)		
Form Factor	1U Rack		
Warranty	Server warranty includes 3-year parts, 3-year labor, 3-year onsite support with next business day response.		

