VM-24H

2x1:4 HDMI Switchable DA

| HDMI | HDCP Compliant



The VM−24H is a distribution amplifier for HDMI signals. The unit reclocks and equalizes one of two selectable input signals and distributes it to four identical outputs

FEATURES

- Max. Data Rate - 6.75Gbps (2.25Gbps per graphic channel)
- HDTV Compatible
- HDCP Compliant
- HDMI Support - Deep Color, x.v.Color™, Lip Sync, CEC
- 3D Pass-Through
- EDID Pass–through - Pass–through algorithm ensures Plug and Play operation for HDMI source and display systems
- Active Output LED Indicators
- Control - Front panel, RS−232, IR switching
- Worldwide Power Supply - 100−240V AC
- Standard 19” Rack Mount Size - 1U. Rack “ears” included

TECHNICAL SPECIFICATIONS

INPUTS:	2 HDMI connectors
OUTPUTS:	4 HDMI connectors
BANDWIDTH:	6.75Gbps (2.25Gbps per graphic channel)
COMPLIANCE WITH HDMI STANDARD:	Supports HDMI and HDCP
CONTROLS:	EDID SELECT, EDID READ, IN 1, IN 2 buttons, RS−232, IR
INDICATOR LEDs:	Output status LEDs
POWER CONSUMPTION:	100−240V AC, 50/60Hz, 16VA
INCLUDED ACCESSORIES:	Power cord, null−modem adapter, Windows®−based control software
OPTIONS:	External remote IR receiver cable
Product Dimensions	19" x 7.20 x 1U (43.6cm x 18.30cm x 4.36cm) W, D, H
Product Weight	1.6kg (3.5lbs) approx
Shipping Dimensions	55.00cm x 27.60cm x 10.70cm (21.65" x 10.87" x 4.21") W, D, H
Shipping Weight	2.5kg (5.5lbs) approx

