



CS60 and CS60-HC Series Accessory Guide

Single-slot Charge Communication Cradles

- Single-slot Device + Battery Charge Communication Cradle

- Charges 1 Device and 1 Spare Battery

- Part Numbers:

- CR6080-SC100F4WW
 - CS6080 Cordless: Standard Cradle, Inductive, Bluetooth, Midnight Black - 1 Slot for Scanner and 1 Slot for Spare Battery. USB-C Cradle Cable CBL-CS6-S07-04 Sold Separately.
- CR6080-SC100F4CN (China Only)
 - CS6080 Cordless: Standard Cradle, Inductive, Bluetooth, Midnight Black - 1 Slot for Scanner and 1 Slot for Spare Battery. USB-C Cradle Cable CBL-CS6-S07-04 Sold Separately. China Only.



- Single-slot Device Healthcare Cart Mountable Charge Communication Presentation Cradle

- Charges 1 Device

- Part Numbers:

- CR6080-PC100FBWW
 - CS6080 Cordless: Presentation Cradle, Inductive, Bluetooth, Healthcare White. USB-C Cradle Cable CBL-CS6-S07-0B Sold Separately.
- CR6080-PC100FBCN (China Only)
 - CS6080 Cordless: Presentation Cradle, Inductive, Bluetooth, Healthcare White. USB-C Cradle Cable CBL-CS6-S07-0B Sold Separately. China Only



Qi Wireless Charging Pad

- Charges a single device
- Only sold as part of a kit:
(device + charger + USB-A to USB-C cable)
- Part Numbers:
 - CS6080-SR400004QVW
 - CS6080-SR Black Cordless Qi Pad Charger Kit:
CS6080-SR40004VZWW Scanner, CR6080-QZ1000XWW Qi Pad Charger,
USB-C Qi Pad Cable
 - CS6080-SR400004QVK
 - CS6080-SR Black Cordless Qi Pad Charger Kit:
CS6080-SR40004VZK Scanner, CR6080-QZ1000XWW Qi Pad Charger,
USB-C Qi Pad Cable
 - CS6080-SR400004QVC (China Only)
 - CS6080-SR Black Cordless Qi Pad Charger Kit:
CS6080-SR40004VZCN Scanner, CR6080-QZ1000XWW Qi Pad Charger,
USB-C Qi Pad Cable



USB-C (Cradle) to USB-A (Host) Cables for Single-slot Charge Communication Cradles

- USB-C (Cradle) to USB-A (Host) Charge Cable for Single-slot Device + Battery Charge Communication Cradle
 - Part Number:
 - CBL-CS6-S07-04 (Not Pictured)
 - CS6080 Cordless Cradle Cable: USB-C (Cradle) to USB-A (Host) Cable; 7ft. (2.1m), Straight - Midnight Black
- USB-C (Cradle) to USB-A (Host) Charge Cable for Single-slot Device Healthcare Cart Mountable Charge Communication Presentation Cradle
 - Part Number:
 - CBL-CS6-S07-0B (Not Pictured)
 - CS6080 Cordless Cradle Cable: USB-C (Cradle) to USB-A (Host) Cable; 7ft. (2.1m), Straight - HC White

Rack Mountable Multi-slot Chargers

- Device Charger
 - Charges 4 Devices on Single-slot Charge Base
 - Part Number:
 - CR6080-SC400F4WW
 - CS6080 Cordless: 4-Slot Device ShareCradle, Inductive, Midnight Black. Includes Power Supply and DC line cord. 3-wire grounded country specific AC line cord sold separately.
- Battery Charger
 - Charges 4 Spare Batteries on Single-slot Charge Base
 - Part Number:
 - CR6080-BC40004WW
 - CS6080 Cordless: 4-Slot Battery ShareCradle, Inductive, Midnight Black. Includes Power Supply and DC line cord. 3-wire grounded country specific AC line cord sold separately.
- 19" Rack Mounting Accessory Part Number (BRKT-SCRD-SMRK-01)



Multi-slot Charge Cups

- Device Charge Cup
 - 4 Device Charge Cup (sold separately from the charge base) can be installed on any Single, Double or 5 slot charge base
 - Part Number:
 - CR6080-SA40004WW
 - CS6080 Cordless: 4-Slot Device Cradle Adapter Cup, Inductive, Midnight Black
- Battery Charge Cup
 - 4 Battery Charge Cup (sold separately from the charge base) can be installed on any Single, Double or 5 slot charge base
 - Part Number:
 - CR6080-BA40004WW
 - CS6080 Cordless: 4-Slot Battery Cradle Adapter Cup, Inductive, Midnight Black



Spare Batteries

- CS60 735 mAh Lithium Polymer Spare Battery
 - Part Numbers:
 - BTRY-CS60EAB0E-04
 - Spare Battery, CS6080-SR
 - BTRY-CS60EAB0E-04K
 - Spare Battery, CS6080-SR - India, Korea, Japan Only
- CS60-HC 735 mAh Lithium Polymer Spare Battery
 - Part Numbers:
 - BTRY-CS60EABHE-0B
 - Spare Battery, CS6080-HC
 - BTRY-CS60EABHE-0BK
 - Spare Battery, CS6080-HC - India, Korea, Japan Only



Corded USB-A (Host) Converter

- Converts the CS60 cordless device to a corded device
 - Part Number:
 - CVTR-U70060C-04
 - 7 ft (2.1m) Corded USB Converter - CS6080-SR (Midnight Black)
- Converts the CS60-HC cordless device to a corded device
 - Part Number:
 - CVTR-U70060C-0B
 - 7 ft (2.1m) Corded USB Converter - CS6080-HC (HC White)



Wearable Accessories

- Lanyard, Multi-purpose Retractor and Silicon Sleeve (sold together): Comfortably and safely wear the CS60 or CS60-HC on a neck lanyard or belt loop; includes silicone protector.
 - Part Number:
 - LNYD-000060W-04
 - Lanyard, Retractor, Silicon Sleeve - CS6080 Cordless (Midnight Black)



Gooseneck Intellistands and Accessories

- Non-weighted
 - Part Numbers:
 - STND-GS0060C-04
 - Gooseneck Intellistand - CS6080-SR Corded (Midnight Black)
 - STND-GS0060C-0B
 - Gooseneck Intellistand - CS6080-HC Corded (HC White)
- Weighted
 - Part Numbers:
 - STND-WS0060C-04 (Not Pictured)
 - Gooseneck Intellistand, Weighted - CS6080-SR Corded (Midnight Black)
 - STND-WS0060C-0B (Not Pictured)
 - Gooseneck Intellistand, Weighted - CS6080-HC Corded (HC White)
- Cups (Compatible with Non-weighted and Weighted Intellistands)
 - Part Numbers:
 - CUP-GS0060C-04
 - Gooseneck Cup - CS6080-SR Corded (Midnight Black)
 - CUP-GS0060C-0B
 - Gooseneck Cup - CS6080-HC Corded (HC White)



Wall Charger – For use with Single-slot Device + Battery Charge Communication Cradle

Wall Charger – Power Supply

PWR-WUA5V12W0XX

Power Supply-100-240 VAC, 5 V, 2.5 A with country specific plugs.



Country	Power Supply Part Number
United States	PWR-WUA5V12W0US
Great Britain	PWR-WUA5V12W0GB
Europe	PWR-WUA5V12W0EU
Australia	PWR-WUA5V12W0AU
China	PWR-WUA5V12W0CN
Argentina	PWR-WUS5V12W0AR
Brazil	PWR-WUA5V12W0BR
Korea	PWR-WUA5V12W0KR
India	PWR-WUA5V12W0IN

AC Line Cords – Country Specific

Country	Three Wire AC Line Cord
Abu Dhabi	50-16000-220R: 1.8M long, CEE 7/7 plug
Australia	50-16000-217R: 1.9M long, AS 3112 plug
Bolivia	50-16000-220R: 1.8M long, CEE 7/7 plug
Brazil	50-16000-727R: 18AWG, 250V, 16A, BR (3w)
China	50-16000-217R: 1.9M long, AS 3112 plug 50-16000-257R: 1.8M long, IEC 60320 C13 plug
Dubai	50-16000-220R: 1.8M long, CEE 7/7 plug
Egypt	50-16000-220R: 1.8M long, CEE 7/7 plug
Europe	50-16000-220R: 1.8M long, CEE 7/7 plug
Hong Kong	50-16000-219R: 1.8M long, BS1363 plug
India	50-16000-669R: 1.9M long, BS 546 plug
Iran	50-16000-220R: 1.8M long, CEE 7/7 plug
Iraq	50-16000-219R: 1.8M long, BS1363 plug

Country	Three Wire AC Line Cord
Israel	50-16000-672R: 1.9M long, S132 plug
Italy/Chile	50-16000-671R: 1.8M long, CIE 23-16 plug
Japan	50-16000-218R: 1.8M long, NEMA 1-15P plug
Korea	50-16000-220R: 1.8M long, CEE 7/7 plug 50-16000-256R: 1.8M long, CEE7/7 plug
Malaysia	50-16000-219R: 1.8M long, BS1363 plug
New Guinea	50-16000-217R: 1.9M long, AS 3112 plug
Russia	50-16000-220R: 1.8M long, CEE 7/7 plug
Singapore	50-16000-219R: 1.8M long, BS1363 plug
UK	50-16000-219R: 1.8M long, BS1363 plug
US	23844-00-00R: 7.5 feet long 50-16000-221R: 1.8M long, USA NEMA 5-15P
Vietnam	50-16000-220R: 1.8M long, CEE 7/7 plug