Imageable Proximity Card

APSM2

imageable proximity card

Features

- Up to 7in read range
- Digital Radio Frequency Identification (RFID) technology
- Frequency 125kHz
- Pack quantity: 25 cards
- 1 year warranty
- NDAA Compliant*



Technical Specification	
Technology	Proximity
Frequency	125 kHz
Operation	Passive (no battery)
Type	ISO
Format	Wiegand 26-bit
Material	PVC
Color	Glossy White
Slot Punch	Vertical and horizontal indicators
Marking	Date code and ID
Read Range	Up to 7 inches (176mm)
Warranty	1 year warranty
Dimensions	2.1" W x 3.4" H x 0.031" D (53mm x 86mm x .79mm)
Weight	0.19oz (5.5g)
Operating Temperature	-35°F to 122°F (-37°C to 50°C)
Humidity	0-95% non-condensing
Technology Supported	Certain HID® 125 kHz Proximity protocols supported
Supported Readers	AP300HA, AP500HA, AP620HA, AP640HA

NDAA COMPLIANT

*Products are in compliance with NDAA Section 889 Part B Guidelines

Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 1/19/22