

Technical Accessory Guides (TAGs)

For Associates, Resellers, ISVs and Alliance Partners

Global



Version: Active-Only

Will only show products that are known to be available for sale

Need to provide an update or change?

Contact <mailto:pgw786@zebra.com>



For Internal Use by
PartnerConnect Members Only



TC73/TC78 Series Technical Accessory Guide



Does not include TC70/TC72/TC75/TC77 accessories. See separate guide for these TC7X series accessories.

NOTE: This document is only for general reference. Solutions Pathway and related PMBs should be used for product availability, pricing, and final solution selection.




* Zebra does not endorse or specifically recommend any **third-party products, accessories, or hardware**. ZEBRA DISCLAIMS ANY AND ALL LIABILITY, INCLUDING ANY EXPRESS OR IMPLIED WARRANTIES, WHETHER ORAL OR WRITTEN, FOR SUCH THIRD PARTY PRODUCTS, ACCESSORIES, OR HARDWARE. THE CUSTOMER ACKNOWLEDGES THAT NO REPRESENTATION HAS BEEN MADE BY ZEBRA AS TO THE FITNESS OF THE THIRD-PARTY PRODUCTS, ACCESSORIES, OR HARDWARE FOR THE CUSTOMER'S INTENDED PURPOSE.


Cradles and Charging

Single Device Cradles



Part Number	Picture	Description	Notes	Required Items
CRD-NGTC7-2SC1B		Single Slot Charge-Only ShareCradle KIT	<ul style="list-style-type: none"> ▶ Will charge TC73/TC78 and a spare battery. ▶ Will charge standard size battery in device from 0-80% in as little as 1.5 hours ▶ Compatible with devices units with hand strap or Pistol Grip Handle attached. ▶ Kit includes: <ul style="list-style-type: none"> - Single Slot Charge-Only Cradle (CRD-NGTC5TC7-2SC1B) - Power Supply (PWR-BGA12V50W0WW) - DC Line Cord (CBL-DC-388A1-01) - shim for device (SHIM-CRD-NGTC7) ▶ Connects to charge contacts on bottom of device. 	<ul style="list-style-type: none"> ▶ AC Line Cord (23844-00-00F or country specific version)
CRD-NGTC7-2SE1B		Single Slot USB/Charging Cradle KIT	<ul style="list-style-type: none"> ▶ Will charge TC73/TC78 and a spare battery. ▶ Will charge standard size battery in device from 0-80% in as little as 1.5 hours ▶ Compatible with devices units with hand strap or Pistol Grip Handle attached. ▶ Kit includes: <ul style="list-style-type: none"> - Single Slot USB/Charging Cradle (CRD-NGTC5TC7-2SE1B) - Power Supply (PWR-BGA12V50W0WW) - DC Line Cord (CBL-DC-388A1-01) - shim for device (SHIM-CRD-NGTC7) ▶ Connects to charge contacts and USB-C port on bottom of device. ▶ Can be enhanced to provide Ethernet communications by installing USB to Ethernet Module (MOD-MT2-EU1-01). 	<ul style="list-style-type: none"> ▶ AC Line Cord (23844-00-00F or country specific version) ▶ For USB communication: Micro USB Cable (25-124330-01R)

CRD-NTC7X-1SNWS-01		Workstation Connect Cradle	<ul style="list-style-type: none"> ▶ An enhanced single-slot charging cradle allowing users to use the TC73/TC78 as a workstation or kiosk. ▶ Cradle includes the following additional ports: <ul style="list-style-type: none"> - HDMI - Ethernet - 4 USB ports for keyboard, mouse, and other supported USB devices. ▶ Connects to I/O connector on rear of device. ▶ Cover on rear of cradle can be secured using screw to prevent unauthorized access to ports. ▶ Not compatible with snap-on accessories. 	<ul style="list-style-type: none"> ▶ Power Supply (PWR-BGA12V50W0WW) ▶ DC Line Cord (CBL-DC-388A2-01). <ul style="list-style-type: none"> - CBL-DC-388A1-01 may also be used, but CBL-DC-388A2-01 is recommended to provide easier installation of peripheral cables and the cradle's port cover. ▶ AC Line Cord (23844-00-00F or country specific version)
MOD-MT2-EU1-01		USB to Ethernet Module	<ul style="list-style-type: none"> ▶ Attaches to USB/Charging ShareCradle (CRD-NGTC5TC7-2SE1B) to provide Ethernet support ▶ Mechanical switch selects between USB B port and RJ45 Ethernet jack. ▶ 10/100/1000 Mbps speed ▶ LEDs on module indicate connectivity and speed. 	USB/Charging ShareCradle Kit (CRD-NGTC5-2SE1B)
Multi-Device Cradles				
Part Number	Picture	Description	Notes	Required Items
CRD-NGTC7-5SC5D		5-Slot Charge-Only ShareCradle KIT	<ul style="list-style-type: none"> ▶ Will charge up to five devices. ▶ Will charge standard battery in device from 0-80% in as little as 1.5 hours. ▶ Does not charge spare batteries ▶ Compatible with devices with hand strap or Pistol Grip Handle attached. ▶ Kit includes: <ul style="list-style-type: none"> - 5-Slot Charge-Only Cradle (CRD-NGTC5TC7-5SC5D) - Power Supply (PWR-BGA12V108W0WW) - DC Line Cord (CBL-DC-381A1-01) - shim for device (SHIM-CRD-NGTC7) - QTY 5 ▶ Can be racked/ mounted in a standard 19 inch rack system via the mounting accessory (BRKT-SCRD-SMRK-01) ▶ Connects to charge contacts on bottom of device. 	<ul style="list-style-type: none"> ▶ AC Line Cord (23844-00-00F or country specific version)



<p>CRD-NGTC7-5SC4B</p>		<p>5-Slot Charge-Only ShareCradle with Spare Battery Charging slot KIT</p>	<ul style="list-style-type: none"> ▶ Will charge up to four devices and four spare batteries. ▶ Will charge standard battery in device from 0-80% in as little as 1.5 hours. ▶ Compatible with devices with hand strap or Pistol Grip Handle attached. ▶ Kit includes: <ul style="list-style-type: none"> - 5-Slot Charge-Only ShareCradle with Spare Battery Charger (CRD-NGTC5TC7-5SC4B) - Power Supply (PWR-BGA12V108W0WW) - DC Line Cord (CBL-DC-381A1-01) - shim for device (SHIM-CRD-NGTC7) - QTY 4 ▶ Can be racked/ mounted in a standard 19 inch rack system via the mounting accessory (BRKT-SCRD-SMRK-01) ▶ Connects to charge contacts on bottom of device. 	<ul style="list-style-type: none"> ▶ AC Line Cord (23844-00-00P or country specific version)
<p>CRD-NGTC7-5SE5D</p>		<p>5-Slot Ethernet/Charging ShareCradle KIT</p>	<ul style="list-style-type: none"> ▶ Allows network speeds up to 1 Gb ▶ Will charge standard battery in device from 0-80% in as little as 1.5 hours. ▶ Does not charge spare batteries ▶ Compatible with devices with hand strap or Pistol Grip Handle attached. ▶ Kit includes: <ul style="list-style-type: none"> - 5-Slot Ethernet+Charge Cradle (CRD-NGTC5TC7-5SE5D) - Power Supply (PWR-BGA12V108W0WW) - DC Line Cord (CBL-DC-381A1-01) - shim for device (SHIM-CRD-NGTC7) - QTY 5 ▶ Can be racked/ mounted in a standard 19 inch rack system via the mounting accessory (BRKT-SCRD-SMRK-01) ▶ Connects to charge contacts and USB-C port on bottom of device. 	
<p>BRKT-SCRD-SMRK-01</p>		<p>5-Slot ShareCradle Mounting Bracket</p>	<ul style="list-style-type: none"> ▶ Allows for rack and wall mounting of one 5-Slot ShareCradle, up to four Single Slot ShareCradles, or up to four 4-Slot Battery Chargers. ▶ Bracket can be mounted on standard 19" network rack or on a wall. ▶ Has cable routing slots and removable power supply tray that stores and conceals power supplies. ▶ Adjustable tabs & screw mounts for easy hanging/installation. ▶ Adjustable orientations: <ul style="list-style-type: none"> - 25° High Density (5-Slot Charge Only Cradle) - Horizontal (Single Slot Cradle or 4-Slot Battery Chargers). ▶ See the Bluetooth-Generic Accessories TAG for info on 3rd party Network Racks that can be used for mounting this bracket. 	



ADP-TC7X-PLT-FX		5-Slot ShareCradle Mounting Bracket Adapter Plate for Honeywell	<ul style="list-style-type: none"> ▶ Allows Zebra Multi-Slot ShareCradles to be mounted on legacy Honeywell Flex Cradle Wall Mount Brackets (HON SKU #203-641-002). ▶ Includes hardware to attach plate to HON wall bracket and secure ShareCradle to plate. ▶ NOTE: This is a custom product. Please work with your Zebra representative to open a Custom Product Request (CPR) if you would like to order this item. 	
-----------------	---	---	---	--

Misc. Cradle Accessories


Part Number	Picture	Description	Notes	Required Items
CRDCUP-NGTC7-01 (single cup) CRDCUP-NGTC7-05 (set of 5 cups)		TC73/TC78 Charge-Only ShareCradle Cup Conversion Kit	<ul style="list-style-type: none"> ▶ Can be used to replace a legacy TC7X series cradle cup when migrating from legacy TC7X to TC73/TC78. ▶ Can also be used to replace a damaged cradle cup or to create a multi-slot cradle supporting a mixed combination of devices (i.e. two TC21/TC26 and three TC73/TC78). ▶ Only compatible with cradles that use ShareCradle design (i.e. TC5X series). ▶ Kit includes: <ul style="list-style-type: none"> - ShareCradle Cup (CRDCUP-NGTC5TC7) - shim for device (SHIM-CRD-NGTC7) - screw for attaching cup to cradle 	
SHIM-CRD-NGTC7		Replacement ShareCradle Cup Insert/Shim (1 shim)	<ul style="list-style-type: none"> ▶ Replacement cradle insert/shim that are typically included with each TC73/TC78 ShareCradle. ▶ Order to replace lost/damaged shims or when swapping legacy TC7X cradle cups for TC73/TC78 cups (also requires CRDCUP-NGTC5TC7) or when migrating from TC53/TC58 to TC73/TC78. ▶ Black color 	

Battery Charging


Part Number	Picture	Description	Notes	Required Items
SAC-NGTC5TC7-4SCHG		4-Slot Battery Charger	<ul style="list-style-type: none"> ▶ Charges up to four spare Standard capacity or Extended capacity batteries ▶ Standard capacity batteries will charge from 0-90% in about 4 hours ▶ Can be used standalone or up to 4 Chargers can be mounted on Mounting Bracket (BRKT-SCRD-SMRK-01) 	<ul style="list-style-type: none"> ▶ Power Supply (PWR-BGA12V50W0WW) ▶ DC Line Cord (CBL-DC-388A1-01) ▶ AC Line Cord (23844-00-00F or country specific version)



SAC-NGTC5TC7-4SCHG-01		4-Slot Battery Charger Kit	<ul style="list-style-type: none"> ▶ Charges up to four spare Standard capacity or Extended capacity batteries ▶ Standard capacity batteries will charge from 0-90% in about 4 hours ▶ Kit includes: <ul style="list-style-type: none"> - 4-Slot Battery Charger (SAC-NGTC5TC7-4SCHG) - Power Supply (PWR-BGA12V50W0WW) - DC Line Cord (CBL-DC-388A1-01) ▶ Can be used standalone or up to 4 Chargers can be mounted on Mounting Bracket (BRKT-SCRD-SMRK-01) 	▶ AC Line Cord (23844-00-00F or country specific version)
BTRCUP-NGTC5TC7-01		4-Slot Battery Charger Conversion Kit	<ul style="list-style-type: none"> ▶ Used to replace a legacy TC7X series Battery Charger on a Multi-Slot ShareCradle when migrating from legacy TC7X to TC73/TC78. ▶ Please Note: When replacing legacy TC7X Battery Charger on Multi-Slot ShareCradles the 4-Slot Battery Charger Adapter Cup must also be removed. 	

Direct to Device Charging


Part Number	Picture	Description	Notes	Required Items
CBL-TC5X-USBC2A-01 or CBL-TC2Y-USBC90A-01		USB-A to USB-C cable	<ul style="list-style-type: none"> ▶ USB-A to USB-C cable ▶ Attaches to USB-C port on bottom of device ▶ Cable length is 1M (~3.25 ft.) ▶ CBL-TC2Y-USBC90A-01 features USB-A connector with a 90° bend allowing cable to be used in tighter locations. Cable length is about 1.1M (45"). 	

Communication Cables

Part Number	Picture	Description	Notes	Required Items
CBL-TC5X-USBC2A-01 or CBL-TC2Y-USBC90A-01		USB-C cable	<ul style="list-style-type: none"> ▶ USB-A to USB-C cable ▶ Attaches to USB-C port on bottom of device. ▶ Cable length is 1M (~3.25 ft.) ▶ CBL-TC2Y-USBC90A-01 features USB-A connector with a 90° bend allowing cable to be used in tighter locations. Cable length is about 1.1M (45"). ▶ Can be used with USB Cigarette Lighter Adapter (CHG-AUTO-USB1-01) for in-vehicle charging. 	




3rd party *		USB-C cable	▶ Attaches to USB-C port on bottom of device.	
25-124330-01R		Single Slot Cradle to PC/Host USB cable	▶ Used with Single Slot USB/Charging Cradle ▶ Micro USB connection on cradle end ▶ Cable length is 48 inches	

Snap-On Accessories

Part Number	Picture	Description	Notes	Required Items
TRG-NGTC7-ELEC-01		Pistol Grip Trigger Handle	<ul style="list-style-type: none"> ▶ Uses electrical trigger via contacts on back side of TC73/TC78. ▶ Trigger Handle accessory offers customers the option of using the product in a gun form factor, ideal for scan-intensive situations. ▶ Does not block access to rear facing camera and flash allowing camera to be used while using the trigger handle. ▶ Compatible with both Standard and Extended capacity batteries ▶ Optional Wrist Strap (SG-PD40-WLD1-01) also available. 	



Soft Goods - Cases/Holsters

Part Number	Picture	Description	Notes	Required Items
-------------	---------	-------------	-------	----------------

<p>SG-NGTC5TC7-HLSTR-01</p>		<p>Soft Holster</p>	<ul style="list-style-type: none"> ▶ Vertical orientation with Open Bucket design to accommodate TC73/TC78 or device with optional Pistol Grip Trigger Handle. ▶ Strap on rear of holster allows adjustment for use with the accessory options mentioned above. ▶ Leather material. ▶ Includes Loop for storage of optional stylus. ▶ Non rotating for maximum durability. ▶ Holster includes cut-out for speaker output. 	
<p>SG-NGTC5TC7-HDSTP-01 (single strap)</p> <p>SG-NGTC5TC7-HDSTP-03 (pack of 3)</p> <p>SG-NGTC5TC7-HDSTP-1K (case of 1000)</p> <p><small>NOTE: 1000 count case is a custom product. Please work with your Zebra representative to open a Custom Product Request (CPR) if you would like to order this item.</small></p>		<p>Hand Strap</p>	<ul style="list-style-type: none"> ▶ Allows device to be easily held in palm of hand. ▶ Attaches directly to TC73/TC78 ▶ Includes loop for holding optional stylus. 	
<p>SG-PD40-WLD1-01</p>		<p>Wrist Strap for Trigger Handle</p>	<ul style="list-style-type: none"> ▶ Attaches to bottom of Pistol Grip Trigger Handle (TRG-NGTC7-ELEC-01) 	

Vehicle Cradles and Holders



Powered Cradles and Holders (provides device charging and/or communication)				
Part Number	Picture	Description	Notes	Required Items
CRD-TC78-WCVC-01		Charge-Only Vehicle Cradle - Wireless Charging	<ul style="list-style-type: none"> ▶ Device inserts bottom first and is retained by top latch. ▶ Uses four mounting screws with AMPSS hole pattern. ▶ Includes stylus holder (stylus not included) which can be mounted on left or right side of cradle or can be removed if not needed. Optional Stylus (SG-STYLUS-TCX-MTL-03) will fit into holder. ▶ Does not support Pistol Grip Handle. ▶ Wireless charging only supported on TC78. Not supported on TC73. 	<ul style="list-style-type: none"> ▶ Wireless Charging Battery (BTRY-NGTC5TC7-44MAWC-01) ▶ For Charging: Cigarette Lighter Auto Charge Cable (CHG-AUTO-CLA1-01) OR Hard Wired Auto Charge Cable (CHG-AUTO-HWIRE1-01) OR Vehicle Charger Cable for USB I/O Hub and ZQ500/ZQ600 Series Printers (VAM-MPP-VHCH1-01) OR Legacy Zebra Vehicle Cradle Adapter Cable (CBL-TC7X-GFS-01) OR Lind (Gamber-Johnson) Isolated Power Supply when installed on higher voltage vehicles ▶ For Mounting: Windshield Suction Mount (RAM-B-166U) OR See other RAM or ProClip mounting bracket options below.
3PTY-RAM-HOL-ZE17-1U		RAM Charge-Only Non-Locking Vehicle Cradle	<ul style="list-style-type: none"> ▶ Spring-loaded cradle allows easy one handed insertion and removal. ▶ Compatible with RAM two-hole AMPSS pattern diamond bases that will connect to B and C size ball mounts, allowing for a wide variety of mounting options. ▶ Compatible when using optional handstrap. ▶ Includes stylus holder (stylus not included) which is fixed mounted on left side of cradle. Optional Stylus (SG-STYLUS-TCX-MTL-03) will fit into holder. ▶ Uses RAM Mount RAM-HOL-ZE17-1U 	<ul style="list-style-type: none"> ▶ For Charging: <i>RAM GDS Modular Charger</i>, see In-Vehicle Power Supplies section below ▶ For Mounting: Windshield Suction Mount (RAM-B-166U) OR Vehicle Cradle RAM mount ball (RAM-B-238U) and additional RAM mount hardware
3PTY-RAM-HOL-ZE17L-1U		RAM Charge-Only Locking Vehicle Cradle	<ul style="list-style-type: none"> ▶ Spring-loaded cradle allows easy one handed insertion and removal. ▶ Includes lock. ▶ Compatible with RAM two-hole AMPSS pattern diamond bases that will connect to B and C size ball mounts, allowing for a wide variety of mounting options. ▶ Compatible when using optional handstrap. ▶ Includes stylus holder (stylus not included) which is fixed mounted on left side of cradle. Optional Stylus (SG-STYLUS-TCX-MTL-03) will fit into holder. ▶ Uses RAM Mount RAM-HOL-ZE17L-1U 	<ul style="list-style-type: none"> ▶ For Charging: <i>RAM GDS Modular Charger</i>, see In-Vehicle Power Supplies section below ▶ For Mounting: Windshield Suction Mount (RAM-B-166U) OR Vehicle Cradle RAM mount ball (RAM-B-238U) and additional RAM mount hardware

<p>RAM-HOL-ZE17-1U (non-locking version)</p> <p>RAM-HOL-ZE17L-1U (locking version)</p> <p>(3rd party) *</p> <p>https://www.rammount.com</p>		<p>RAM Charge-Only Vehicle Cradle</p> 	<ul style="list-style-type: none"> ▶ Spring-loaded cradle allows easy one handed insertion and removal. ▶ Compatible with RAM two-hole AMPS pattern diamond bases that will connect to B and C size ball mounts, allowing for a wide variety of mounting options. ▶ Compatible when using optional handstrap. ▶ Includes stylus holder (stylus not included) which is fixed mounted on left side of cradle. Optional Stylus (SG-STYLUS-TCX-MTL-03) will fit into holder. 	<p>For Charging RAM GDS Modular Charger, see In-Vehicle Power Supplies section below</p> <p>For Mounting ▶ Windshield Suction Mount (RAM-B-166U) OR ▶ see RAM website for other options</p>
--	---	---	--	---

Un-Powered Cradles and Holders (passive holders, no charging support)

Part Number	Picture	Description	Notes	Required Items
CRD-TC7NG-NCCD-01		Vehicle Holder	<ul style="list-style-type: none"> ▶ Holds device in vehicle installations. ▶ Spring tension on holder. ▶ Provides access to USB-C port on bottom of device allowing device to be charged. ▶ Does not support Pistol Grip Handle. 	<p>For Mounting: Windshield Suction Mount (RAM-B-166U) OR See other RAM or ProClip mounting bracket options below.</p>




Vehicle Mounting Hardware

Part Number	Picture	Description	Notes	Required Items
RAM-B-166U		Vehicle Cradle Windshield Suction Cup Mount	<ul style="list-style-type: none"> ▶ RAM Twist Lock Suction Cup with Double Socket Arm and Diamond Base Adapter ▶ Overall Length: 6.75" ▶ Attaches to back of Vehicle Cradles 	
RAM-B-238U		Vehicle Cradle RAM Mount ball	<ul style="list-style-type: none"> ▶ RAM 2.43" x 1.31" Diamond Ball Base w/ 1" Ball ▶ Attaches to back of Vehicle Cradles 	Requires additional RAM hardware to mount vehicle cradle

3PTY-PCLIP-241476		ProClip Forklift/Vehicle Cradle Clamp Mount - for Pipe/Bar mounting	<ul style="list-style-type: none"> ▶ Attaches to circular pipes/bars of vehicles/forklifts. ▶ Accommodates bars from 3/4" to 1 1/8" diameter (19 to 30 mm). ▶ Uses AMPS hole pattern for mounting ProClip cradles like 3PTY-PCLIP-241475. ▶ NOTE: This is a custom product. Please work with your Zebra representative to open a Custom Product Request (CPR) if you would like to order this item. 	
3PTY-PCLIP-241477		ProClip Forklift/Vehicle Cradle Clamp Mount with Backplate - for Pipe/Bar mounting	<ul style="list-style-type: none"> ▶ Attaches to circular pipes/bars of vehicles/forklifts. ▶ Accommodates bars from 3/4" to 1 1/8" diameter (19 to 30 mm). ▶ Includes 3PTY-PCLIP-241476 with an attached backplate that uses AMPS hole pattern for mounting vehicle cradles. ▶ NOTE: This is a custom product. Please work with your Zebra representative to open a Custom Product Request (CPR) if you would like to order this item. 	
3PTY-PCLIP-241478		ProClip Forklift/Vehicle Cradle Clamp Mount - for square frame mounting	<ul style="list-style-type: none"> ▶ Attaches to square bars of vehicles/forklifts. ▶ Clamp is 5.125" x 3.75" and can accommodate bars of varying thicknesses. ▶ 6" long arm on clamp uses AMPS hole pattern for mounting ProClip cradles like 3PTY-PCLIP-241475. 	
3PTY-PCLIP-215500		ProClip Tilt Swivel Mount For TC7X/TC5X Vehicle Cradles	<ul style="list-style-type: none"> ▶ For mounting Vehicle Cradle on any flat surface. ▶ Angles/Tilts 15 degrees ▶ Swivels 360 degrees ▶ Extends 1 inch / 2.54 cm ▶ Base Plate and Face Plate has AMPS hole pattern ▶ Weight capacity 25 lbs / 11.34 kgs ▶ NOTE: Restricted Product - Must open CPR at http://cpr.zebra.com (Zebra internal site). Sample devices shall then be provided, and once the customer approves these demo devices, the SKU shall be opened for sale to that customer. Refer to PMB 2756 for details. 	Vehicle Cradle (CRD-TC56-CVCD1-01 or CRD-TC56-UVCD1-01)

<p>3PTY-PCLIP-710836</p>	 	<p>2" tall Pedestal Mounting Kit - Horizontal Adjustment, For TC7X/TC5X Vehicle Cradle</p> 	<ul style="list-style-type: none"> ▶ 2 inch Solid-core Aluminum quick-adjust interlocking joint. ▶ The round bases provide an industry-standard 4-hole AMPS mounting pattern with approximately 20 degrees of rotation to facilitate the perfect mounting angle and device placement. ▶ Adjustable for optimal positioning ▶ Weight capacity over 300 lbs ▶ NOTE: Restricted Product - Must open CPR at http://cpr.zebra.lan (Zebra internal site). Sample devices shall then be provided, and once the customer approves these demo devices, the SKU shall be opened for sale to that customer. Refer to PMB 2756 for details. 	<p>Vehicle Cradle (CRD-TC56-CVCD1-01 or CRD-TC56-UVCD1-01)</p>
<p>3PTY-PCLIP-710834</p>	 	<p>ProClip 4" tall Pedestal Mounting Kit For TC7X/TC5X Vehicle Cradles - Horizontal & Vertical Adjustment</p> 	<ul style="list-style-type: none"> ▶ 4 inch Solid-core Aluminum quick-adjust interlocking joints. ▶ Mount also features a 2 inch 90-degree offset extension rod to enable both horizontal and vertical adjustment to achieve optimal device/cradle positioning. ▶ AMPS hole pattern in mount bases ▶ Quick and easy installation ▶ Adjustable for optimal positioning ▶ Weight capacity over 300 lbs ▶ NOTE: Restricted Product - Must open CPR at http://cpr.zebra.lan (Zebra internal site). Sample devices shall then be provided, and once the customer approves these demo devices, the SKU shall be opened for sale to that customer. Refer to PMB 2756 for details. 	<p>Vehicle Cradle (CRD-TC56-CVCD1-01 or CRD-TC56-UVCD1-01)</p>
<p>3PTY-PCLIP-710835</p>	 	<p>4" tall Pedestal Mounting Kit For TC7X/TC5X Vehicle Cradles - Horizontal Adjustment</p> 	<ul style="list-style-type: none"> ▶ 4 inch Solid-core Aluminum quick-adjust interlocking joints. ▶ Mount also features a 2 inch Horizontal extension rod between mount bases ▶ AMPS hole pattern in mount bases ▶ Quick and easy installation ▶ Adjustable for optimal positioning ▶ Weight capacity over 300 lbs ▶ NOTE: Restricted Product - Must open CPR at http://cpr.zebra.lan (Zebra internal site). Sample devices shall then be provided, and once the customer approves these demo devices, the SKU shall be opened for sale to that customer. Refer to PMB 2756 for details. 	<p>Vehicle Cradle (CRD-TC56-CVCD1-01 or CRD-TC56-UVCD1-01)</p>



3PTY-PCLIP-241479		ProClip Standard Duty 5\" Pedestal Mount 	<ul style="list-style-type: none"> ▶ Standard Duty mount is designed to be used in smooth-riding vehicles and areas with low risk of external contact. ▶ Length of arm assembly is 5". ▶ Uses AMPS hole pattern for mounting ProClip cradles like CRD-TC56-CVCD2-02. ▶ NOTE: This is a custom product. Please work with your Zebra representative to open a Custom Product Request (CPR) if you would like to order this item. 	Vehicle Cradle (CRD-TC56-CVCD1-01 or CRD-TC56-UVCD1-01)
3PTY-PCLIP-710837		ProClip 6" tall Pedestal Mounting Kit - Horizontal & Vertical Adjustment, For TC7X/TC5X Vehicle Cradles	<ul style="list-style-type: none"> ▶ 6 inch Solid-core Aluminum quick-adjust interlocking joint. ▶ The round bases provide an industry-standard 4-hole AMPS mounting pattern with approximately 20 degrees of rotation to facilitate the perfect mounting angle and device placement. ▶ Adjustable for optimal positioning ▶ Weight capacity over 300 lbs ▶ NOTE: Restricted Product - Must open CPR at http://cpr.zebra.lan (Zebra internal site). Sample devices shall then be provided, and once the customer approves these demo devices, the SKU shall be opened for sale to that customer. Refer to PMB 2756 for details. 	Vehicle Cradle (CRD-TC56-CVCD1-01 or CRD-TC56-UVCD1-01)
3PTY-PCLIP-710838		ProClip 8" tall Pedestal Mounting Kit - Horizontal Adjustment, For TC7X/TC5X Vehicle Cradles	<ul style="list-style-type: none"> ▶ 8 inch Solid-core Aluminum quick-adjust interlocking joint. ▶ The round bases provide an industry-standard 4-hole AMPS mounting pattern with approximately 20 degrees of rotation to facilitate the perfect mounting angle and device placement. ▶ Adjustable for optimal positioning ▶ Weight capacity over 300 lbs ▶ NOTE: Restricted Product - Must open CPR at http://cpr.zebra.lan (Zebra internal site). Sample devices shall then be provided, and once the customer approves these demo devices, the SKU shall be opened for sale to that customer. Refer to PMB 2756 for details. 	Vehicle Cradle (CRD-TC56-CVCD1-01 or CRD-TC56-UVCD1-01)
Misc				
Part Number	Picture	Description	Notes	Required Items

SG-STYLUS-TCX-MTL-03 (pack of 3)		Fiber Tipped Stylus	<ul style="list-style-type: none"> ▶ Black Passive Stylus with Zebra logo ▶ 5" length ▶ Heavy duty - made from stainless steel and brass. No plastic parts - real pen feel. ▶ Can be used in rain. ▶ Micro-Knit Hybrid Mesh Fiber Tip provides silent, smooth gliding use. ▶ Big improvement over rubber tipped or plastic tipped stylus. ▶ Compatible with all capacitive touch screen devices. ▶ Can be tethered to device using SG-TC5NGTC7NG-TETHR-03. 	
SG-TC5NGTC7NG-TETHR-03 (pack of 3)		Tether for Stylus	<ul style="list-style-type: none"> ▶ String type tether prevents loss of stylus ▶ NOTE: Other Zebra coiled tethers are not recommended for use with TC73/TC78 as they may interfere with other accessories. ▶ NOTE: This tether is recommended when using Fiber Tipped Stylus (SG-STYLUS-TCX-MTL-03). Other tethers may not fit easily through the tether loop hole on the stylus. 	
SG-NGTC7-SCRNP-03 (pack of 3)		Screen Protectors	<ul style="list-style-type: none"> ▶ Tempered glass ▶ Includes alcohol wipes, cleaning cloth and tools needed for screen protector installation. 	

Headset/Audio Accessories


Wired Headsets and Audio Accessories

NOTE: Wired headsets with 2.5mm or 3.5mm jacks are not supported on TC73/TC78 devices since they do not include a headset jack.

Part Number	Picture	Description	Notes	Required Items
HDST-USBC-PTT1-01		PTT Headset (USB-C connector)	 <ul style="list-style-type: none"> ▶ For Push-To-Talk (PTT) applications. ▶ Compatible with Zebra PTT Express and PTT Pro. ▶ Connects to USB-C port on device. ▶ Rotating earpiece allows for right or left ear configuration. ▶ Provides PTT button, volume up/volume down buttons. ▶ Cable length is 32 in. (81 cm) ▶ mono with microphone ▶ includes clip for attaching PTT button to clothing. 	

Bluetooth Headsets and Audio Accessories

NOTE: Bluetooth headsets with PTT function not supported by Zebra PTT Express application. Check with Engineering to verify compatibility with Zebra PTT Pro application.









Part Number	Picture	Description	Notes	Required Items
See HS2100-HS3100 Accessories Document		HS3100 Rugged Bluetooth Headset for VDP applications	<ul style="list-style-type: none"> ▶ HD Voice, also known as Wide Band Audio, brings incredible audio clarity ▶ Built to handle the everyday inevitable drops ▶ Dustproof, sprayproof and waterproof ▶ Ready for the freezer and outdoor subzero temperatures ▶ Feather-light for extraordinary comfort ▶ Noise cancellation tuned for VDP (voice directed picking) applications. ▶ Not designed for the aggressive noise cancellation required for VoIP or voice calls. Headset's send level is not tuned to satisfy VoIP or voice standards and will result with audio being quieter at the far end and delivering more noise. ▶ Swap batteries on the fly — without losing the Bluetooth connection ▶ Split-second tap-to-pair simplicity using NFC. ▶ Detachable swivel boom minimizes costs. ▶ Swivelling boom mutes microphone allowing uses to prevent voice pick applications from recognizing non-voice pick conversations. ▶ User-replaceable pads and windscreens maximize comfort and hygiene ▶ 15 hours of battery power 	See HS2100/HS3100 Accessories Document for headset accessories
various Bluetooth models B550-XT B350-XT C400-XT C300-XT (3rd party) * http://www.blueparrott.com		BlueParrott Bluetooth Headsets	<ul style="list-style-type: none"> ▶ Various Bluetooth models available with options that include: <ul style="list-style-type: none"> - Blocking out 96% of background noise - Over 24 hours of talk time - NFC Tap to Pair capable - Bluetooth wireless range capable up to 300 ft. - Convertible wearing options: over the head, behind the neck. See BlueParrot site for model specific options.	
APTT1 (3rd party) * https://www.aina-wireless.com/		Aina Push-To-Talk (PTT) Bluetooth Voice Responder Remote Speaker/Mic (RSM)	<ul style="list-style-type: none"> ▶ Bluetooth speaker-microphone designed to work with different walkie talkie style Push-to-Talk applications, including Zebra PTT Pro (check with Zebra PTT Pro engineering team for current device/OS support). ▶ Includes clip for attaching device to clothing for lapel speaker/mic usage. ▶ Features several buttons which the application developers can assign to different functions. ▶ Users can remotely control functions such as push-to-talk, phone calls, channel switching and emergency alerts. ▶ Device is ruggedized, MIL-STD 810G and IP67. ▶ Long lasting battery designed for 24 hour approx battery life. Can be recharged via micro-USB port. ▶ Includes 3.5mm headset jack allowing headphones to be connected for keeping conversations more private. ▶ Can be easily paired to mobile computer using NFC tap-to-pair. 	

<p>H3-B-1 (3rd party) *</p> <p>https://www.dellking.com</p>		<p>Wandfu H3 Push-To-Talk (PTT) Bluetooth Remote Speaker/Mic (RSM)</p>	<ul style="list-style-type: none"> ▶ Bluetooth speaker-microphone designed to work with different walkie talkie style Push-to-Talk applications, including Zebra PTT Pro (check with Zebra PTT Pro engineering team for current device/OS support). ▶ Includes clip for attaching device to clothing for lapel speaker/mic usage. ▶ Includes 3.5mm headset jack allowing headphones to be connected for keeping conversations more private. 	
<p>BTR-155 (3rd party) *</p> <p>https://www.savoxaccessories.com</p>		<p>Savox BTR-155 Bluetooth Remote Speaker/Mic (RSM)</p>	<ul style="list-style-type: none"> ▶ Bluetooth speaker-microphone designed to work with different walkie talkie style Push-to-Talk applications, including Zebra PTT Pro (check with Zebra PTT Pro engineering team for current device/OS support). ▶ Includes clip for attaching device to clothing for lapel speaker/mic usage. ▶ Rugged wireless speaker microphone IP55. ▶ Allows cable-free movement ▶ Familiar speaker microphone functions; PTT and volume buttons ▶ Includes 2.5mm headset jack allowing headphones to be connected for keeping conversations more private. ▶ LED status indication ▶ High speaker volume ▶ Includes: <ul style="list-style-type: none"> - Savox RSM - Modular Wired earpiece - Wall Charger - USB Cable - Quick Start Guide - Carrying Strap 	
<p>BTH-101 (3rd party) *</p> <p>https://www.savoxaccessories.com</p>		<p>Savox Push-To-Talk (PTT) Bluetooth Headset</p>	<ul style="list-style-type: none"> ▶ Bluetooth headset designed to work with different walkie talkie style Push-to-Talk applications, including Zebra PTT Pro (check with Zebra PTT Pro engineering team for current device/OS support). ▶ Also operates as standard Bluetooth headset for taking phone calls. ▶ Device is lightweight and ruggedized, IP55. 	





Power Cords/Power Supplies


AC Cords and Power Supplies

Part Number	Picture	Description	Notes	Required Items
-------------	---------	-------------	-------	----------------







CBL-DC-388A1-01		DC Power Cord	<ul style="list-style-type: none"> ▶ Used to power Single Slot Cradles and 4-Slot Battery Chargers when using Level VI Efficiency power supply (PWR-BGA12V50W0WW) ▶ Cable length is 1.8 meters ▶ NOTE: All TC73/TC78 Cradles include this cable. 	
CBL-DC-388A2-01		DC Power Cord for Workstation Cradles	<ul style="list-style-type: none"> ▶ Used along with Power Supply PWR-BGA12V50W0WW to power Workstation Cradle (CRD-NTC7X-1SNWS-01). ▶ Barrel Jack connector is straight and ferrite is in a different location vs. L-shaped connector on CBL-DC-388A1-01. ▶ Cable length is 1.8 meters ▶ NOTE: CBL-DC-388A1-01 may also be used with Workstation Cradles, but CBL-DC-388A2-01 is recommended to provide easier installation of peripheral cables and the cradle's port cover. 	
PWR-BGA12V50W0WW		Power Supply	<ul style="list-style-type: none"> ▶ Replaces PWRS-14000-148R ▶ Used to power Single Slot Cradle and 4-Slot Battery Charger ▶ 100-240 VAC, 12VDC, 3.33A ▶ Level VI Efficiency rated ▶ NOTE: All TC73/TC78 Cradles include this power supply. 	<ul style="list-style-type: none"> ▶ DC Power Cord (CBL-DC-388A1-01) ▶ AC Line Cord (23844-00-00F or country specific version)
KIT-PWR-12V50W		Power Supply Kit	<ul style="list-style-type: none"> ▶ Includes Power Supply (PWR-BGA12V50W0WW) and DC Line Cord (CBL-DC-388A1-01) 	<ul style="list-style-type: none"> ▶ AC Line Cord (23844-00-00F or country specific version)
CBL-DC-381A1-01		DC Power Cord	<ul style="list-style-type: none"> ▶ Used to power 5-Slot ShareCradles when using Level VI Efficiency power supply (PWR-BGA12V108W0WW) ▶ NOTE: All TC73/TC78 Multi-Slot ShareCradles include this cable. ▶ This cable does not include the black extension release latch which is not required when used on Multi-Slot ShareCradles. 	
CBL-DC-382A1-01		DC Power Cord	<ul style="list-style-type: none"> ▶ Used to power 5-Slot ShareCradles when using Level VI Efficiency power supply (PWR-BGA12V108W0WW) ▶ Cable has black extension tab for releasing the cable from the back of the cradle. This isn't required when using Multi-Slot ShareCradles. ▶ CBL-DC-381A1-01 is normally used with TC73/TC78 multi-device cradles. 	
CBL-DC-523A1-01		2-Way DC Y Power Cord	<ul style="list-style-type: none"> ▶ Used to power two 4-Slot Battery Chargers from one Power Supply (PWR-BGA12V108W0WW) 	
PWR-BGA12V108W0WW		Power Supply	<ul style="list-style-type: none"> ▶ Used to power 5-Slot ShareCradles or two 4-Slot Spare Battery Chargers ▶ 9A, 108W ▶ Level VI Efficiency rated ▶ NOTE: All TC73/TC78 Cradles include this power supply. 	<ul style="list-style-type: none"> ▶ DC Line Cord (CBL-DC-381A1-01 or CBL-DC-523A1-01) ▶ AC Line Cord (23844-00-00F or country specific version)

23844-00-00R		AC Line Cord	<ul style="list-style-type: none"> ▶ Used to power Cradles. ▶ This AC Line Cord is for use in North America. See the AC Line Cords by Country TAG for comparable line cords to use in other countries. 	
PWR-WUA5V12W0US (US plug style) PWR-WUA5V12W0GB (UK plug style) PWR-WUA5V12W0EU (EU plug style) PWR-WUA5V12W0AU (Australia plug style) PWR-WUA5V12W0CN (China plug style) PWR-WUA5V12W0IN (India plug style) PWR-WUA5V12W0KR (Korea plug style) PWR-WUA5V12W0BR (Brazil plug style) PWR-WUA5V12W0LA (Argentina/Chile/Mexico plug styles)		USB Power Supply	<ul style="list-style-type: none"> ▶ Used with USB-C Cable (CBL-TC5X-USBC2A-01) to charge device. ▶ Provides higher current (2.5A) for faster charging ▶ 100-240 VAC, 5 V, 2.5 A 	
In-Vehicle Power Supplies				
Part Number	Picture	Description	Notes	Required Items
CHG-AUTO-USB1-01 CHG-AUTO-USB1-BR (for Brazil)		USB Cigarette Lighter Adapter	<ul style="list-style-type: none"> ▶ Used with USB-C Cable (CBL-TC5X-USBC2A-01) to charge device. ▶ Includes two USB A ports providing higher current (2.5A) for faster charging 	
CHG-AUTO-CLA1-01		Cigarette Lighter Auto Charger Cable for Vehicle Cradle	<ul style="list-style-type: none"> ▶ 12/24V ▶ Includes tab on Barrel jack end for ensuring a reliable connection to Vehicle Cradle (CRD-TC78-WCVC-01). ▶ Only compatible with Vehicle Cradle (CRD-TC78-WCVC-01) 	
CHG-AUTO-HWIRE1-01		Hard Wired Auto Charger Cable for USB I/O Hub	<ul style="list-style-type: none"> ▶ 12/24V ▶ Includes tab on Barrel jack end for ensuring a reliable connection to Vehicle Cradle (CRD-TC78-WCVC-01). ▶ Bare wire end connects directly to vehicle power source. ▶ Only compatible with Vehicle Cradle (CRD-TC78-WCVC-01) ▶ Approximate cable length is 13 ft. 	

<p>CBL-TC7X-GFS-01</p>		<p>Zebra Legacy Vehicle Cradle Power Adapter Cable</p>	<p>► Allows Vehicle Cradle (CRD-TC78-WCVC-01) to use power cables from legacy Zebra device vehicle cradles including: MC5x/MC6x, MC7x, MC9x-Brick, MC9x-Short, or MC95 which use cable SKUs 25-128973-01R, 25-61987-01R, or 25-128974-01R. ► Cable length is 11.5" ► NOTE: This is a custom product. Please work with your Zebra representative to open a Custom Product Request (CPR) if you would like to order this cable.</p>	
<p>ADPCBL-TC7X-USPS</p>		<p>Honeywell Legacy Vehicle Cradle Power Adapter Cable</p>	<p>► Allows Vehicle Cradle (CRD-TC78-WCVC-01) to use power cables from legacy Honeywell vehicle cradles providing 12V - typically Honeywell 99ex. ► Cable length is about 12". ► NOTE: This is a custom product. Please work with your Zebra representative to open a Custom Product Request (CPR) if you would like to order this cable.</p>	
<p>VAM-MPP-VHCH1-01 (CPR required for use with TC73/TC78)</p>		<p>Vehicle Charger Cable for Vehicle Cradle and ZQ500/ZQ600 Series Printers</p>	<p>► Charger with charge both the Vehicle Cradle (CRD-TC78-WCVC-01) a ZQ500 or ZQ600 series printer. ► Includes the following: (1) Power Supply (P1093358) which has square locking connector and one USB-A port which can be used to charge an additional device. (2) cable for charging Vehicle Cradle (CRD-TC78-WCVC-01) (includes tab on Barrel jack end for ensuring a reliable connection to the cradle) and ZQ500/ZQ600 printer (3) cable for charging legacy TC7X Charging Cable Cup, Serial/Charge Cable, or USB/Charge Cable Cups and ZQ500/ZQ600 printer - will not be used with TC73/TC78. (4) Cigarette Lighter Adapter power cord (5) Hard Wired (bare wire) power cord Choose preferred power cord (4) or (5) ► NOTE: This charging solution has not been officially validated with the TC73/TC78. Please submit a CPR at http://cpr.zebra.lan (Zebra internal site) if you would like to use this cable with the TC73/TC78.</p>	
<p>7300-0466 (12-32 VDC input) 7300-0467 (20-60 VDC input) 7300-0418 (72-110 VDC input) Gamber Johnson (3rd party) * http://www.gamberjohnson.com</p>		<p>Lind 12V Isolated Power Supply for Vehicle Cradle</p>	<p>► Typically used when powering Vehicle Cradle (CRD-TC78-WCVC-01) from higher voltage vehicles. ► Provides 12V DC output required by cradle.</p>	

<p>RAM-GDS-CAB-USBA-DC90-1U (plugs into existing USB-A port, only includes USB-A to 5.5mm DC connector adapter cable)</p> <p>RAM-GDS-CHARGE-M55-V7B1U (for 10-30V vehicles)</p> <p>RAM-GDS-CHARGE-M55-V8BU (for 30-64V vehicles)</p> <p>(3rd party) *</p> <p>https://www.rammount.com</p>		<p>RAM GDS Modular Chargers</p>	<p>► Used to power RAM Vehicle Cradles</p> <p>► Chargers includes:</p> <ul style="list-style-type: none"> - USB Type-A male connection to 5.5mm DC connector adapter cable - Hard wired power adapter, USB Type-A female connector; 10-30V or 30V-64V input range, 5V output <p>► When upgrading devices, avoid rewiring by unplugging power connector and attaching new charger components</p>	
--	---	---------------------------------	---	--

Batteries

Part Number	Picture	Description	Notes	Required Items
<p>BTRY-NGTC5TC7-44MA-01 (single)</p> <p>BTRY-NGTC5TC7-44MA-10 (pack of 10)</p>		<p>Spare 1X Standard Capacity Battery with PowerPrecision Plus (4400 mAh)</p> 	<p>► Designed, manufactured & tested to meet rigorous controls & standards</p> <p>► Premium-grade cells with higher capacity & longer life cycle</p> <p>► Designed to help prevent overcharging & electrical shock</p> <p>► Strong & robust housing for optimal performance & durability</p> <p>► Information available:</p> <ul style="list-style-type: none"> - Advanced state of Charge (shows the remaining battery power based on two factors: present charge and present real-time usage patterns of the device. - Advanced State of Health (highly accurate end-of-life prediction) - Dynamic usage patterns are constantly calculated, factoring in criteria such as the applications that are in use and scanning frequency). 	
<p>BTRY-NGTC5TC7-44MABLE-01</p>		<p>Spare 1X Standard Capacity Battery with PowerPrecision Plus (4400 mAh) and BLE beacon</p> 	<p>► Designed, manufactured & tested to meet rigorous controls & standards</p> <p>► Premium-grade cells with higher capacity & longer life cycle</p> <p>► Designed to help prevent overcharging & electrical shock</p> <p>► Strong & robust housing for optimal performance & durability</p> <p>► Information available:</p> <ul style="list-style-type: none"> - Advanced state of Charge (shows the remaining battery power based on two factors: present charge and present real-time usage patterns of the device. - Advanced State of Health (highly accurate end-of-life prediction) - Dynamic usage patterns are constantly calculated, factoring in criteria such as the applications that are in use and scanning frequency). <p>► Includes Bluetooth beacon allowing device to be located while powered off using solutions like Zebra Device Tracker.</p> <p>► Once the battery can no longer power the device the BLE beacon in the battery will continue to beacon for about 7-10 days.</p> <p>► Battery purchase is eligible for discounted Device Tracker 1-year or 3-year subscription. See PMB 10837 for details.</p>	 <p>► Typically purchased along with a Device Tracker 1-year or 3-year subscription. Battery is eligible for a discounted Device Tracker subscription:</p> <p>SW-BLE-DT-SP-1YR (1 year) or SW-BLE-DT-SP-3YR (3 year)</p> <p>See PMB 10837 for details.</p> 

<p>BTRY-NGTC5TC7-44MAWC-01</p>		<p>Spare 1X Standard Capacity Battery with PowerPrecision Plus (4400 mAh) and Wireless Charging</p> 	<ul style="list-style-type: none"> ▶ Designed, manufactured & tested to meet rigorous controls & standards ▶ Premium-grade cells with higher capacity & longer life cycle ▶ Designed to help prevent overcharging & electrical shock ▶ Strong & robust housing for optimal performance & durability ▶ Information available: <ul style="list-style-type: none"> - Advanced state of Charge (shows the remaining battery power based on two factors: present charge and present real-time usage patterns of the device. - Advanced State of Health (highly accurate end-of-life prediction) - Dynamic usage patterns are constantly calculated, factoring in criteria such as the applications that are in use and scanning frequency). ▶ Includes support for wireless charging only supported on TC78. Not supported on TC73. 	
<p>BTRY-NGTC5TC7-66MA-01</p>		<p>Spare 1.5X Extended Capacity Battery with PowerPrecision Plus (6600 mAh)</p> 	<ul style="list-style-type: none"> ▶ Designed, manufactured & tested to meet rigorous controls & standards ▶ Premium-grade cells with higher capacity & longer life cycle ▶ Designed to help prevent overcharging & electrical shock ▶ Strong & robust housing for optimal performance & durability ▶ Information available: <ul style="list-style-type: none"> - Advanced state of Charge (shows the remaining battery power based on two factors: present charge and present real-time usage patterns of the device. - Advanced State of Health (highly accurate end-of-life prediction) - Dynamic usage patterns are constantly calculated, factoring in criteria such as the applications that are in use and scanning frequency). 	