Ortronics

Fusion Splice-On Connector for 3.0mm Fiber, SC, Multimode OM1, Beige boot, 6 pk

Part No. 205KNF3FA-62



''

Using a factory-terminated and pre-polished connector, this Splice-On Connector (SOC) provides a connection that meets or exceeds industry standards for loss and back reflection. The Connector is provided with a factory-cleaved 900um fiber stub to ensure ease of use and optimal performance.

Features & Benefits

- Unique boot allows the entire splice to be concealed and protected
- Extended brass crimp sleeve provides extra protection to the splice
- Kevlar for maximized pull strength
- Tubing insert to accommodate 1.6/2.0/3.0 cordage

Specifications

General Info

Product Line	Ortronics	Color	Beige
UPC Number	662875001515	Country Of Origin	United States
Connector Color	Beige	Application Sector	Commercial, Data Center
Standard	Telcordia GR-326	Type	Connector
Boot Color	Beige		

Dimensions

Product Width US	0.379 in	Product Depth US	3.1 in
Product Height US	0.4 in		

Technical Information

Fiber Optic Cable Type	OM1	Service Life	500 matings, < 0.2dB typical change
Splice Type	Fusion	Temperature Rating	-40° - 85° C
Return Loss	35 dB	Connector Type	SC
Ferrule Diameter	2.5 mm	Fiber Size	62.5/125
Maximum Insertion Loss	0.4 dB	Connectivity Footprint	Infinium
Typical Insertion Loss	0.25 dB		