Product data sheet

Specifications



3.5kW split system Indoor unit, Gravity Drain

ACRMD4KT-1

Overview

Lead Time	Special Order - Call for Quoted Lead Times

Main

Main Input Voltage	200...240 V
Number Of Rack Unit	5U
Provided Equipment	120/240V power supply Built-in modbus protocol adapter

Physical

Height	8.58 in (21.8 cm)
Width	18.66 in (47.4 cm)
Depth	29.61 in (75.2 cm)
Net Weight	57.32 lb(US) (26 kg)
Mounting Preference	No preference
Mounting Mode	Not rack-mountable

Input

Number Of Power Feeds	1
Input Frequency	60 Hz

Conformance

Product Certifications	UL Listed

Environmental

Ambient Air Temperature For Operation	-4…122 °F (-20…50 °C)
Ambient Air Temperature For Storage	-4…122 °F (-20…50 °C)
Relative Humidity	20…80 %
Audible Noise At 1 Meter From Surface Of Unit	74 dBA

Ordering and shipping details

Gtin	731304408093

Packing Units

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Unit Type Of Package 1	PCE
Number Of Units In Package 1	1
Package 1 Height	12.99 in (33 cm)
Package 1 Width	37.40 in (95 cm)
Package 1 Length	22.83 in (58 cm)
Package 1 Weight	66.14 lb(US) (30 kg)

Contractual warranty

Warranty	1 year (parts only)

Sustainability

Green Premium^{TM} label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO_2 products.

Learn more about Green Premium ›

Eu Rohs Directive	Under investigation
Weee	The product must be disposed on European Union markets following specific waste collection and never end up in rubbish bins.