Ortronics

Fusion Splice-On Connector for 3.0mm Fiber, SC, Single-Mode OS2, White boot, 6 pk

Part No. 205KNF3RA-09



Legrand 3.0mm Splice-On Connectors have a unique boot that allows the entire splice to be concealed and protected. The addition of an extended brass crimp sleeve provides extra protection to the splice and utilizes the Kevlar for maximized pull strength.

Features & Benefits

- Unique boot allows the entire splice to be concealed and protected
- Extended brass crimp sleeve provides extra protection to the splice
- Kevlar for maximized pull strength
- Tubing insert to accommodate 1.6/2.0/3.0 cordage

Specifications

General Info

Product Line	Ortronics	Color	Blue
UPC Number	662875001140	Country Of Origin	United States
Product Type	Splice-On Connector	Connector Color	Blue
Application Sector	Commercial, Data Center	Standard	TIA-568.3;Telcordia GR-326
Boot Color	White		

Dimensions

Product Width US	0.379 in	Product Depth US	3.1 in
Product Height US	0.4 in		

Technical Information

Fiber Optic Cable Type	OS2	Service Life	500 matings, < 0.2dB typical change
Splice Type	Fusion	Temperature Rating	-40° - 85° C
Return Loss	55 dB	Connector Type	SC
Ferrule Diameter	2.5 mm	Fiber Size	9/125
Maximum Insertion Loss	0.3 dB	Connectivity Footprint	Infinium
Typical Insertion Loss	0.15 dB		