Ortronics

Infinium Fusion Splice-On Connector, ST OM1, beige 900 micron boot, packaged in boxes of 6

Part No. 205KNF9EA-62



Splice-On Connector ST PC OM1 Beige Housing Beige Boot, Box of 6

Features & Benefits

- Better Insertion Loss & Return Loss Performance: Support high-bandwidth/high-speed transmission to 25G, 40G and 100G applications
- Available in LC, SC and ST, Single-Mode or Multimode: Multiple connector types available
- UV Cure Protection Sleeves: Strain relief boot protects the splice point
- 3mm Version: Brass crimp to protect splice
- Factory-cleaved, pre-polished 900-micron fiber stub: Provides a quicker termination
- 900-micron boot conceals and protects the splice: Enables better cable management
- 3mm Version: 3mm boot protects splice for easy cable management
- 3mm Version: Tubing insert to accommodate 1.6/2.0/3.0 cordage

Specifications

General Info

Product Line	Ortronics	UPC Number	662875915263
Country Of Origin	United States		

Dimensions

Product Width US	2.46 in	Product Depth US	2.46 in
Product Height US	0.4 in		