

Hi-Speed USB Active Extension Cable

Daisy-Chainable, A Male / A Female, 20 m (65 ft.)

SKU: 150958 | EAN-13: 0766623150958 | UPC: 766623150958

Easily overcome distance limitations to connect USB devices

Use the Manhattan Hi-Speed USB Active Cable to connect a computer USB port to a USB device almost anywhere in the room. Daisy-chain 2 cable extensions to provide a convenient, 40m (131-ft.) connection. Manhattan Hi-Speed USB Active Cable with built-it repeater is fully-compliant with USB 1.1 and Hi-Speed USB specifications to help devices operate at maximum performance. Plug-and-play capability, Windows/Macintosh versatility and no external power or driver requirements help provide greater flexibility in computer and peripheral placement and office layout.

Features:

- Extends and boosts the signal to any USB device — supports data transfer speeds up to 480 Mbps
- Built-in repeater helps maintain Hi-Speed USB signal quality, electrical and timing specifications
- Overcomes the 20m (65-ft.) USB distance limitation — ideal for connecting enclosures and other peripherals
- Daisy-chain two extensions for total distance of 40 m (131 ft.)
- Plug and play; Windows and Mac compatible; bus powered — requires no external power supply
- Three-Year Warranty

Specifications:

Standards and Certifications
• CE
• USB 2.0

Electrical:
USB power output: 5.0 V ±5% / 0.09 A / 0.45 W

Ports
• Standard-A male
• Standard-A female

General
• Throughput: 480 Mbps
• Bus powered
• Maximum length: 40 m (131 ft.)
• All USB-supported operating systems

Physical
• Length: 20 m (65 ft.)
• Net weight: 520 g (1.15 lbs.)
• Gross weight: 610 g (1.34 lbs.)

Package Contents
• Hi-Speed USB Active Cable

For more information on Manhattan products, consult your local dealer or visit www.manhattan-products.com.
All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.













For more information on Manhattan products, consult your local dealer or visit www.manhattan-products.com.
All names of products or services mentioned herein are trademarks or registered trademarks of their respective owners. Distribution and reproduction of this document, and use and disclosure of the contents herein, are prohibited unless specifically authorized.