Ortronics

Infinium Fusion Splice-On Connector, LC, OS2, white 900 micron boot, packaged in boxes of 6

Part No. 205KNF9SA-09



..

Splice-On Connector LC UPC OS2

Features & Benefits

Better Insertion Loss & Return Loss Performance: Support high-bandwidth/high-speed transmission to 25G, 40G and 100G applications

Factory-cleaved, pre-polished 900-micron fiber stub: Provides a quicker termination

Available in LC, SC and ST, Single-Mode or Multimode: Multiple connector types available

900-micron boot conceals and protects the splice: Enables better cable management

UV Cure Protection Sleeves: Strain relief boot protects the splice point

3mm Version: 3mm boot protects splice for easy cable management

3mm Version: Brass crimp to protect splice

3mm Version: Tubing insert to accommodate 1.6/2.0/3.0 cordage

Specifications

General Info

Product Line	Ortronics	UPC Number	662875512769
Country Of Origin	United States	Adapter Color	Blue

Dimensions

Product Width US	2.56 in	Product Depth US	2.46 in
Product Height US	0.4 in		

Technical Information

Connector Type	LC