

OKI® MICROLINE® 490/491

24-Pin Impact Printers



Reliable and fast with letter-quality output.



Narrow Carriage
MICROLINE 490



Highlights:

Rated at 20,000 hours MTBF

3-year standard warranty

Print speeds up to 475 cps¹

Integrated USB and IEEE Parallel connectivity standard

Optional OkiLAN® 6120i 10/100 Base-T Ethernet® internal print server

Crisp, clear printing – on letterhead or 5-part forms

Expandable head gap – accommodates multi-part forms and cut-sheet stock including labels and stiff index stock

128 KB receive buffer/memory

7.5 million-character ribbon life

200-million character printhead life

Small footprint – ideal for retail countertops

Uses the same accessories as ML390/391 Turbo Series

¹ Utility/Draft Mode.

² Q4 2003 IDC Quarterly Tracker and Evans Research.

Exceptional forms-printing performance, backed by a 3-Year standard warranty

High-volume versatility in forms and correspondence.

Whether you need regular output of continuous multi-part forms, fine business correspondence—or combinations of both—24-pin OKI® ML490/491 printers are the commanding solution.

They handle the printing needs of the most demanding environments—including point-of-sale, automation and utility applications such as wholesale or retail sales counters, financial departments, and manufacturing or warehouse sites. Yet they also produce letter-quality type and high-resolution graphics for the office and executive suite.

Unequaled performance technology. The ML490/491 sport features that give them a strong edge over their predecessors as well as the competition:

- An internal cooling fan provides continuous airflow for the printhead—maximizing throughput productivity for long, unattended print jobs
- Additional feed rollers provide precise forms handling and printed-character placement accuracy
- 3-piece top cover provides easy access and unsurpassed break resistance

Fast, with finesse. ML490/491 printers run the gamut of paper types and envelopes at lightning speed—reaching 475 cps in Utility/Draft mode and 105 cps in Letter-quality. Their rugged printhead (200 million-character average life expectancy) is made up of powerful samarium magnets and stored-energy pins that deliver precise, sharp characters all the way through to the last page of a 5-part form.

The patented OKI closed-loop feedback system assures character placement accuracy. And a zero-tear feature accurately positions continuous forms for a clean tear at the perforation to eliminate wasted stock.

Sturdy and sophisticated. Field-proven reliability is just one reason OKI MICROLINE printers are the most widely-used impact printers in North America².

The rugged, reliable OKI ML490/491 printers are sure to win you over, too!

OKI®
COMMAND
PERFORMANCE™

OKI® MICROLINE® 490/491

24-Pin Impact Printers

Built to last, inside and out. The performance-optimized power supply of the OKI® MICROLINE® 490/491 has been enlarged to easily handle harsh printing conditions. Its energy management capabilities match power expenditures to print-job size, maximizing the life of the 24-pin printhead and other components. These are just a few of the reasons why OKI MICROLINE Impact printers are the most widely used in North America.¹

A long-lasting rack-and-pinion drive system ensures print quality longer than belt or cable systems.

And the ergonomically-designed, impact-resistant chassis protects the ML490/491 from damage, even in the toughest working environments.

All this performance is user-friendly. Controls are conveniently placed on the front panel for fast access. The automatic loading of continuous and cut stock makes every print job easier, and the design of the internal sheet separator enables easy loading of tractor-fed paper into the rear push tractor.

OKI provides the edge in performance no competing printer can claim—and backs it with 3 years of warranty coverage² and a network of authorized OKI Dealer Service Centers and Service Depots.

The high-quality, highly reliable and highly affordable ML490/491 Impact printers from OKI. Put them to work in your office or behind the counter—and watch them drive your productivity to new limits while they improve the look of your forms printing.



Wide-carriage MICROLINE 491

Specifications

Technology, Speed and Print Characteristics

- **Printhead:** 24-Pin SIDM
 - **Graphics Resolution:** 360 (H) x 360 (V) dpi maximum
 - **Feed Rate:** 4.5 ips (11.4 cm/sec.)
 - **Print Speed and Character Matrix:**
 - **Print Speed and Character Matrix:**
- | Mode | Letter Quality
(12 cpi) | Utility
(12 cpi) | Hi-Speed Draft
(10 cpi) | Utility
(15 cpi) |
|----------------|----------------------------|---------------------|----------------------------|---------------------|
| Speed (in cps) | 126 | 315 | 420 | 475 |

Emulation, Interface and Memory

- **Emulation:** Epson® LQ, IBM® ProPrinter®, IBM AGM, IBM XL24
- **Interface: Standard** – IEEE Parallel and USB;
Optional – RS-232C Serial and Ethernet® via OkilAN® 6120 i 10/100 Base-T Internal Print Server (no AC power adapter required); Twin-ax/Co-ax through 3rd Party
- **Memory:** 128K

Compatibility

- **Operating Systems:** Windows® XP, 2000, 98/95, 3.x and NT® 4.0; MS-DOS®

Paper Handling

- **Paper Input:** Single-part, Multi-part, Continuous forms, Cut sheet, Index stock, Envelopes, Labels
- **Number of Copies:** 5
- **Thickness:** 0.017" (0.43 mm) maximum
- **Paper Feeding:** Rear Push and Friction Feed
- **Options:** Bottom Push Tractor, Top Pull Tractor, Cut Sheet Feeder, Roll Paper Stand

Warranty and Reliability

- **Limited Warranty:** 3-Year parts and labor, 2-Year printhead
- **MTBF:** 20,000 hours (25% duty cycle/35% page density)
- **Reliability:**
ML420 – 20,000 pg./mo. duty cycle
ML421 – 12,000 pg./mo. duty cycle
- **Printhead Life:** 200 million characters
- **Ribbon Life:** 7.5 million characters

Environmental

- **Size (WxDxH):**
ML490 – 15.7" x 13.6" x 6.0" (39.8 cm x 34.5 cm x 15.2 cm);
ML491 – 21.7" x 13.6" x 6.0" (55.1 cm x 34.5 cm x 15.2 cm)
- **Net Weight:**
ML490 – 16.4 lb. (7.43 kg); ML491 – 21.2 lb. (9.6 kg)
- **Acoustic Noise:** 56 dBA
- **Power Requirements:**
120V Model: 120 VAC +6%, -15%;
230V Model: 230 VAC +15%, -14%

Ordering Information

Description	Part Numbers
MICROLINE 490/Parallel/120V	62418901
MICROLINE 490/Parallel/230V	62418902
MICROLINE 491/Parallel/120V	62419001
MICROLINE 491/Parallel/230V	62419002

Accessories

Top-Mount Pull Tractor Kit with acoustic cover:	
ML490	70030501
ML491	70030601
Bottom Push Tractor Kit:	
ML490	70030701
ML491	70030801
Cut Sheet Feeder	70030101
Roll Paper Stand (ML490 only)	70023301
RS-232C Serial Interface (19.2K baud max.)	70012801
OkilAN® 6120i 10/100 Base-T Ethernet Internal Print Server	70046501
OkilAN® 6020e 10/100 Base-T Ethernet External Print Server	70036001
OkilAN 6010e 10 Base-T Ethernet External Print Server	70034401
Self-inking Ribbon Cartridge	42377801
Co-ax Adapter	70047201
Twin-ax/Co-ax (Available through Third Party. Call 1-800-OKI-DATA.)	

OKicare® Overnight Exchange Warranty Extensions³

	U.S.	Canada
OKI ML400 Series 1-Yr. Warranty Ext.	58264901	58263111
OKI ML400 Series 2-Yr. Warranty Ext.	58264902	58263112

OKicare® Depot Warranty Extensions³

	U.S.	Canada
OKI ML400 Series 1-Yr. Warranty Ext.	58264701	58265511
OKI ML400 Series 2-Yr. Warranty Ext.	58264702	58265512
Upgrade to 3-Yr. Overnight Exchange	58264801	58264811

For more information on OKI Impact Printers and supplies, including OKicare® Extended Service Programs: **1-800-OKI-DATA** (800-654-3282).

¹ Q4 2003 IDC Quarterly Tracker and Evans Research.

² 3-year standard warranty parts and labor/2-year printhead.

³ Available in the U.S. and Canada only.

All specifications subject to change without notice.

© 2004 Oki Data Americas, Inc. OKI Reg. T.M., M.D., M.R., MICROLINE, OkilAN, OKicare Reg. T.M., Oki Electric Industry Co., Ltd. 7-Day/24-Hour logo T.M., Oki Data Americas, Inc. Epson Reg. T.M., Seiko Epson Corp. IBM, ProPrinter Reg. T.M., International Business Machines, Inc. Windows, Windows NT, MS-DOS Reg. T.M., Microsoft Corp. Ethernet Reg. T.M., SCO. Energy Star Reg. T.M., U.S. EPA. USB-Logo T.M. Universal Serial Bus Implementers Forum, Inc.

OKI®

*Oki, Network Solutions
for a Global Society*

To contact Oki Data Americas, Inc.

In USA: 2000 Bishops Gate Blvd.
Mount Laurel, NJ 08054-4620
Tel: 800.OKI.DATA (800.654.3282)
Fax: 856.222.5320

In Canada: 2735 Matheson Blvd. East
Mississauga, Ontario L4W 4M8
Tel: 905.238.4250
Fax: 905.238.4421

In Latin America and Mexico:

2000 Bishops Gate Blvd.
Mount Laurel, NJ 08054-4620
Tel: 856.231.0002
Fax: 856.222.5071

