C2G

250ft (76.2m) Bulk 18 AWG Shielded Speaker Wire - Plenum CMP-Rated

Part No. CG-29206



Audio/video installations in educational and commercial settings often require plenum-rated cabling. . This wire is constructed from two color-coded 18 AWG twisted pair copper cables (one red, one black) to ensure easy identification. The speaker wire is twisted within a naturally colored jacket for easier pulling and installation.

Each conductor is made from seven strands of 26 AWG copper wires and features 100% foil shield with stranded copper drain wire for easy grounding connections. CMP rating meets building code requirements to run within walls and air plenums without the need for conduit. Wire shows footage markers for easy length tracking.

Note: Always check with your local authority on building requirements to verify cable requirements before beginning any installation.

Features & Benefits

- Two color-coded 18 AWG twisted pair copper cables (one red, one black) to ensure easy identification
- 100% foil shield with stranded copper drain wire for easy grounding connections
- Plenum CMP rated for cable runs through walls and drop ceilings with plenum air space

Specifications

General Info

Product Line	C2G	Color	White
UPC Number	757120292067	Country Of Origin	China
Application Sector	Residential, Commercial	Warranty Type	Lifetime
Type	Speaker Wire		

Dimensions

Product Length US	250.0 FT

Technical Information

Jacket Application	Plenum Rated	Cable Type	Audio
Jacket Rating	CMP Rated, FT6 Rated		