Ortronics

LC, 62.5 OM1 Multi-Mode, Infinium Field Installable Mechanical Splice Connector

Part No. 205KNT9GA-62

LC PC reusable connector, field-installable, 62.5/125 LOMF, beige housing, white 900 micron boot



Features & Benefits

- 900um boot protects splice for easy cable management
- Includes color coded 900um buffer, boot, cleave protector and extended dust cap for easy fiber indentification
- No epoxy or polishing and requires no special tools
- Reusable termination capability saves time and money while reducing scrap
- The VFL window enables immediate feedback on successful termination

Specifications

General Info

Product Line	Ortronics	Color	Beige
UPC Number	662875333166	Country Of Origin	Japan
Connector Color	Beige	Application Sector	Commercial, Data Center
Type	Connector	Boot Color	White

Dimensions

Product Width US	2.56 in	Product Height US	0.35 in

Additional Information

Product Environmental Profile	Yes

Technical Information

Fiber Optic Cable Type	OM1	Service Life	500 matings, < 0.2dB typical change
Splice Type	Mechanical	Temperature Rating	-40° - 75° C
Connector Type	LC	Ferrule Diameter	1.25 mm
Fiber Size	62.5/125	Connectivity Footprint	Infinium