Product datasheet

Specifications



InRow Dual Coil 300mm 27kW Indoor Unit, 200-240V, Humidifier & Reheat, CE/UL

ACRH301P

Overview

Lead Time	Usually in Stock

Main

Main Input Voltage	200...240 V AC 1 phase
Number Of Rack Unit	42U
Provided Equipment	Installation guide Operations and maintenance manual

General

Humidification Flow	2.99 kg/hr
Air Discharge Option	Horizontal
Intake Air Option	Rear return
Air Flow	1374.31 l/s

Physical

Colour	Dark grey
Height	1991 mm
Width	300 mm
Depth	1095 mm
Net Weight	200 kg

Input

Input Power	930 W
Network Frequency	50...60 Hz

Conformance

Product Certifications	CE UL RCM

Communications & Management

Control Panel	Touch screen LCD user interface

Packing Units

Unit Type Of Package 1	PCE

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Number Of Units In Package 1	1

Contractual warranty

Warranty	1 year (parts only), 1 year on-site repair or replace with factory authorized Start-Up

Sustainability

Green Premium^{TM} label is Schneider Electric's commitment to delivering products with best-in-class environmental performance. Green Premium promises compliance with the latest regulations, transparency on environmental impacts, as well as circular and low-CO_2 products.

Guide to assessing product sustainability is a white paper that clarifies global eco-label standards and how to interpret environmental declarations.

Learn more about Green Premium >

Guide to assess a product's sustainability >



Transparency



RoHS/REACh

Well-being performance

Mercury Free	
Rohs Exemption Information	Yes

Certifications & Standards

Reach Regulation	REACh Declaration
Eu Rohs Directive	Compliant with Exemptions
China Rohs Regulation	China RoHS declaration Product out of China RoHS scope. Substance declaration for your information
Environmental Disclosure	Product Environmental Profile
Circularity Profile	End of Life Information