CHIEF®
A brand of legrand



FLOOR & ON-WALL MOUNTED KIOSK SOLUTIONS

IMPACT™ SERIES



IMPACT SERIES™

Chief is answering your need to house digital content for wayfinding, advertising and self-service applications. Our kiosk designs are easily serviceable, flexible and attractive. Impact™ Floor Mounted and On-Wall Kiosks are available now.

Impact™ Kiosks enhance interactive installations like:

- Ordering stations within quick-service restaurants
- Digital signage options replacing traditional static wayfinding and advertising
- E-commerce in brick and mortar stores, allowing customers to browse and order products not found on-shelf
- Municipal and government applications for advertising, wayfinding, surveillance, charging and security





FLOOR MOUNTED KIOSKS

The Chief Impact™ Floor Mounted Portrait Kiosks provide an aesthetic solution for enclosing displays in open areas. Designed with no exposed fasteners while maintaining full access and serviceability. Our exclusive design keeps the display mounted to the frame when opened. Keyed locking security keeps displays safe, and a universal AV Storage plate holds supporting equipment.









SERVICABILITY



KEYED LOCKING



CABLE PATHWAYS



UNIVERSAL DESIGN

- Unparalleled front service and maintenance access
- Aesthetically pleasing with no exposed fasteners
- Keyed locking security
- Tool free removable storage panels
- Universal AV storage space
- Internal knockouts for electrical junction boxes and 2RU rack spaces
- External cable pathway knockouts
- Integrated passive cooling
- Available in black and white
- UL Listed
- Custom colors, logos and protective glass can be special ordered



IMPACT SERIES™

FREESTANDING BASE OPTIONS

Freestanding base accessories preserve floor finishes, and accommodate movement of kiosks in temporary installations. Bases are offered in single-sided and back-to-back configurations. Tested and approved to UL 2442 ensuring safety for interactive use and servicing—see Accessories page for more details.



IMPACT SERIES™

FLOOR MOUNTED KIOSKS
DIMENSIONS & COMPATIBILITY

SINGLE SIDED

Model	Color	Weight Capacity	Mounting Patterns	Max Display Depth	Max TV Width	Max TV Height	Image Diagonal (A)	Overall Width (B)	Overall Height (C)	Overall Dept (D)	Side Bezels (E)	Top Bezels (F)
LF40UBP	Black	100 lbs. (45.3 kg)	200 x 200 mm 300 x 300 mm 400 x 400 mm	3.5" (88.9mm)	43" (1092.2 mm)	26" (660.4 mm)	40"	31.28" (794.5 mm)	73.76" (1873.5 mm)	8.5" (216 mm)	5.84" (148.3 mm)	7.2" (182.8 mm)
LF40UWP	White											
LF42UBP	Black						42"				5.44" (138.1 mm)	5.95" (151.1 mm)
LF42UWP	White											
LF43UBP	Black						43"				5.19" (131.8 mm)	5.75" (146 mm)
LF43UWP	White											
LF46UBP	Black						46"				4.39" (111.5 mm)	4.2" (106.6 mm)
LF46UWP	White											
LF47UBP	Black						47"				4.14" (105.1 mm)	3.8" (96.5 mm)
LF47UWP	White											
LF48UBP	Black						48"				3.89" (98.8 mm)	3.5" (88.9 mm)
LF48UWP	White											
LF49UBP	Black	125 lbs . (56.7 kg)	300 x 300 mm 400 x 400 mm 600 x 400mm	3.5" (88.9mm)	51" (1295.4 mm)	30" (762.0 mm)	49"	35.25" (895.4 mm)	77.13" (1959.2 mm)	8.5" (216 mm)	5.73" (164.5 mm)	6.48" (164.5 mm)
LF49UWP	White											
LF50UBP	Black						50"				5.48" (139.1 mm)	6.08" (154.3 mm)
LF50UWP	White											
LF55UBP	Black						55"				4.23" (107.3 mm)	3.83" (97.2 mm)
LF55UWP	White											

BACK TO BACK

Model	Color	Weight Capacity	Mounting Patterns	Max Dis-play Depth	Max TV Width	Max TV Height	Image Diagonal (A)	Overall Width (B)	Overall Height (C)	Viewing Area Width (D)	Side Bezels (E)	Top Bezels (F)
LF40UBP-B2B	Black	100 lbs. (45.3 kg)	200 x 200 mm 300 x 300 mm 400 x 400 mm	3.5" (88.9mm)	43" (1092.2 mm)	26" (660.4 mm)	40"	31.28" (794.5 mm)	73.76" (1873.5 mm)	8.5" (216 mm)	5.84" (148.3 mm)	7.2" (182.8 mm)
LF40UWP-B2B	White											
LF42UBP-B2B	Black						42"				5.44" (138.1 mm)	5.95" (151.1 mm)
LF42UWP-B2B	White											
LF43UBP-B2B	Black						43"				5.19" (131.8 mm)	5.75" (146 mm)
LF43UWP-B2B	White											
LF46UBP-B2B	Black						46"				4.39" (111.5 mm)	4.2" (106.6 mm)
LF46UWP-B2B	White											
LF47UBP-B2B	Black						47"				4.14" (105.1 mm)	3.8" (96.5 mm)
LF47UWP-B2B	White											
LF48UBP-B2B	Black						48"				3.89" (98.8 mm)	3.5" (88.9 mm)
LF48UWP-B2B	White											
LF49UBP-B2B	Black	125 lbs . (56.7 kg)	300 x 300 mm 400 x 400 mm 600 x 400mm	3.5" (88.9mm)	51" (1295.4 mm)	30" (762.0 mm)	49"	35.25" (895.4 mm)	77.13" (1959.2 mm)	8.5" (216 mm)	5.73" (164.5 mm)	6.48" (164.5 mm)
LF49UWP-B2B	White											
LF50UBP-B2B	Black						50"				5.48" (139.1 mm)	6.08" (154.3 mm)
LF50UWP-B2B	White											
LF55UBP-B2B	Black						55"				4.23" (107.3 mm)	3.83" (97.2 mm)
LF55UWP-B2B	White											

Note: Add "G" to end of SKUs for bonded 5/32" (4 mm) tempered glass providing protection for your LCD display.





AV STORAGE CAPACITIES

Image diagonals 40" – 48"
(H x W x D) 20" x 28.1" x 5.84"
(508 mm x 715 mm x 148 mm)

Image diagonals 49" – 55"
(H x W x D) 16.7" x 32.1" x 5.84
(423 mm x 814 mm x 148 mm)

IMPACT SERIES™

ON-WALL KIOSKS

The Impact™ On-Wall Kiosk brings new flexibility to the digital signage enclosure market while maintaining a sleek aesthetic to complement a variety of environments. A depth-adjustable exterior frame allows for a variety of displays to be used. Reversible hinges help avoid installation and service obstructions, and the exclusive design keeps the display mounted to the frame when opened, providing unparalleled service and maintenance access.



Chief's newest Landscape On-Wall Kiosk includes a scissor-arm extension providing unparalleled service and maintenance access by extending the display up to 8" (203 mm) from the wall. A large interior area accommodates Chief PAC in-wall boxes and other storage components for clean, aesthetic cable management and organization.







DEPTH ADJUSTMENT



KIOSK LATCH



LEVER LOCK™



VENTILATION LOUVERS





FEATURES

- Depth-adjustable exterior frame
- Unparalleled service and maintenance access
- Integrated passive cooling vents with active thermal management options
- Designed to compensate for uneven walls, keeping front of frame flat
- Tamperproof security hardware protects technology investments
- Tool-free on-wall storage with Middle Atlantic's Lever Lock™ technology
- Optimize storage using Chief's PAC Series In-Wall Storage Boxes
- Available in black and white
- Custom colors, logos and protective glass can be special ordered
- UL Listed

IMPACT SERIES™

ON-WALL KIOSKS
DIMENSIONS & COMPATIBILITY

PORTRAIT ON-WALL KIOSKS

*175 lbs. for wood stud, plywood backed steel stud, block & concrete. 125 lbs. in steel stud. Note: Add "G" to end of SKUs for bonded 5/32" (4 mm) tempered glass providing protection for your LCD display.



WATCH THE VIDEO

Model	Color	Weight Capacity	Mounting Patterns	Max Display Depth	Max TV Width	Max TV Height	Image Diagonal (A)	Overall Width (B)	Overall Height (C)	Overall Depth (D)	Side Bezels (E)	Top/Bottom Bezels (F)
LW40UBP	Black	100 lbs. (45.3 kg)	200 x 200 mm 300 x 300 mm 400 x 400 mm	3.75" (95.3 mm)	38.2" (970.3 mm)	23.4" (594.4 mm)	40"	26.0" (660.4 mm)	43.0" (1092.2 mm)	3-5" (76-127 mm)	3.20" (81.3 mm)	4.4" (113.0 mm)
LW40UWP	White											
LW42UBP	Black						42"				2.80" (71.1 mm)	3.2" (81.3 mm)
LW42UWP	White											
LW43UBP	Black						43"				2.55" (64.8 mm)	3.0" (76.2 mm)
LW43UWP	White											
LW46UBP	Black	100 lbs. (45.3 kg)	300 x 300 mm 400 x 400 mm	3.75" (95.3 mm)	43" (1092.2 mm)	26" (660.4 mm)	46"	28.5" (723.9 mm)	46.5" (1181.1 mm)	3-5" (76-127 mm)	3" (76.2 mm)	3.2" (81.3 mm)
LW46UWP	White											
LW47UBP	Black						47"				2.75" 69.9 mm)	2.8" (71.1 mm)
LW47UWP	White											
LW48UBP	Black						48"				2.5" (63.5 mm)	2.5" (63.5 mm)
LW48UWP	White											
LW49UBP	Black	125 lbs. (56.7 kg)	300 x 300 mm 400 x 400 mm	3.75" (95.3 mm)	51" (1295.4 mm)	30" (762.0 mm)	49"	32.5" (825.5 mm)	54.5" (1384.3 mm)	3-5" (76-127 mm)	4.35" (109.2 mm)	6.1" (154.9 mm)
LW49UWP	White											
LW50UBP	Black						50"				4.1" (104.1 mm)	5.7" (144.8 mm)
LW50UWP	White											
LW55UBP	Black						55"				2.85" (72.4 mm)	3.45" (87.6 mm)
LW55UWP	White											
LW65UBP	Black	175 lbs.* (79.4 kg)	300 x 300 mm 400 x 400 mm 600 x 400 mm 600 x 600 mm	3.75" (95.3 mm)	63" (1600.2 mm)	36.5" (927.1 mm)	65"	39" (990.6 mm)	66.5" (1689.1 mm)	3-5" (76-127 mm)	3.7" (94 mm)	5.15" (129.5 mm)
LW65UWP	White											
LW70UBP	Black						70"				2.45" (61 mm)	2.95" (74.9 mm)
LW70UWP	White											
LW75UBP	Black				68" (1727.2 mm)	39" (990.6 mm)	75"	41.5" (1054.1 mm)	71.5" (1816.1 mm)	3-5" (76-127 mm)	2.5" (63.5 mm)	3.25" (82.6 mm)
LW75UWP	White											

LANDSCAPE ON-WALL KIOSKS

*For screens with 600mm wide VESA patterns and FHBUL.



WATCH THE VIDEO

LW40UB	Black	100 lbs (45.3 kg)	200 x 200 mm 300 x 300 mm 400 x 400 mm	3.4 (86.4mm)	38.2 (970.3 mm)	23.4 (594.4 mm)	40"	42.0" (1066.8 mm)	27.3" (692.2 mm)	J = L - K - 1/2"	3.95" (100.3 mm)	3.83" (97.2 mm)
LW40UW	White											
LW42UB	Black						42"				2.7" (68.6 mm)	3.43" (87 mm)
LW42UW	White											
LW43UB	Black						43"				2.5" (63.5 mm)	3.18" (80.6 mm)
LW43UW	White											
LW49UB	Black	125 lbs (56.7 kg)	200 x 200 mm 300 x 300 mm 400 x 400 mm	3.4" (86.4mm)	51.75" (1314.5 mm)	32" (762.0 mm)	49"	53.25" (1352.5 mm)	33.5" (850.9 mm)	J = L - K - 1/2"	5.48" (139.1 mm)	4.85" (123.2 mm)
LW49UW	White											
LW50UB	Black						50"				5.1" (128.9 mm)	4.6" (116.8 mm)
LW50UW	White											
LW55UB	Black						55"				2.78" (70.6 mm)	3.33" (84.5 mm)
LW55UW	White											
LW65UB	Black	175 lbs (79.4 kg)	300 x 300 mm 400 x 400 mm 600 x 400 mm 600 x 600 mm	3.4" (86.4mm)	63" (1600.2 mm)	36.5" (927.1 mm)	65"	65.5" (1663.7 mm)	40.1" (1019.3 mm)	J = L - K - 1/2"	4.65" (118.1 mm)	4.27" (108.3 mm)
LW65UW	White											
LW70UB	Black						70"				2.45" (62.2 mm)	3.02" (76.6 mm)
LW70UW	White											
LW75UB	Black				68" (1727.2 mm)	39" (990.6 mm)	75"	70" (1778 mm)	42.6" (1082.7 mm)		2.5" (63.5 mm)	3.06" (77.8 mm)
LW75UW	White											



Front of Frame



Front of Frame



Side of Frame



SPECIFICATIONS

Orientation: Portrait and Landscape

Exterior Frame Depth Range: 3 - 5" (76 - 127mm)

On-Wall Storage Depth (J): Dependent on depth of display and desired frame depth; see Side of Frame view and below equations for details.

- **Overall Kiosk Depth:** D = 1.25" + K
- **On-Wall Storage Depth:** J = D - K - 3/4"

CHIEF
A brand of legrand

ACCESSORIES

FLOOR & ON-WALL



RLNK-215
PDU with RackLink™



FWD-SIDECLMP-4
AV Storage Mounting Clamps



FHBUL
VESA Adapter Bracket Extends
VESA range up to 200 mm

ADDITIONAL FLOOR



DCFANKIT-4
100 CFM Active
Cooling Fan



UCP-FAN
15 CFM Active
Cooling Fan



PACLFB, PACLFW
Single-Sided
Freestanding Base



PACLFB-B2B, PACLFW-B2B
Back-to-Back
Freestanding Base

ADDITIONAL ON-WALL



PAC525, PAC526 & PAC527
In-Wall Storage Boxes

Note: Compatible with Portrait and Landscape On-Wall Kiosks



LL-VP2110
Lever Lock™ 21x10" (533 x 254mm)
On-Wall AV Storage Tray

Note: Only compatible with Portrait On-Wall Kiosk



PACFAN1
Active Thermal Management
Fan Kit Options

Note: Only compatible with Portrait On-Wall Kiosk

LEGRAND | AV COMMERCIAL BRANDS
C2G | Chief | Da-Lite | Luxul | Middle Atlantic | Vaddio | Wiremold

INSTALLER INSPIRED | legrandav.com

USA 866.977.3901 av.chief.support@legrand.com **CANADA** 877.345.4329 av.chief.canada@legrand.com
EMEA +31 495 580 840 av.emea.sales@legrand.com **APAC** +852 2145 4099 av.asia.sales@legrand.com

©2022 Legrand AV Inc. 220165 Rev D 4/22 Chief is a registered trademark of Legrand AV Inc. All other brand names or marks are used for identification purposes and are trademarks of their respective owners. All patents are protected under existing designations. Other patents pending.