

15U Rack Enclosure Server Cabinet - 27.6 in. Deep - Built-in Fans

Product ID: 2636CABINET



This 15U, 36 in (depth) cabinet features a plexiglass front door, full steel design, and three-fan filtered ventilation helping to keep your servers and other critical equipment cool and protected. This TAA compliant product adheres to the requirements of the US Federal Trade Agreements Act (TAA), allowing government GSA Schedule purchases.

The server equipment cabinet/rack is black, making an attractive addition to your server room, and to ensure maximum versatility, the rack/cabinet includes casters, making it easier to position server equipment as needed.

Certifications, Reports and Compatibility



Features

- Extruded aluminum construction provides rounded corners and edges for an attractive appearance
- Fully forward/back adjustable mounting rails inside cabinet
- TAA compliant for GSA Schedule purchases
- Front and back doors are removable and can be switched to open left or right
- Rolling casters provide full mobility
- Three (3) roof-mounted fans exhaust up to 300 CFM of air
- Many accessory options available like mounting shelves, keyboard drawers, storage drawers, sliding shelves, front blanking plates, etc.
- Comes fully assembled
- Includes (3) 5" ball bearing AC fans moving up to 300 CFM of air, air filter and adjustable levelers at each corner
- Also comes with front flip-up stabilizers, removable smoked acrylic front door with 2 keys, removable rear door and 50 Philips-head mounting screws

Hardware	Warranty	Lifetime
	Back Door Type	Solid Steel
	Casters	Included
	Fan(s)	Yes
	Fans	3 - 120 mm
	Frame Type	Steel
	Front Door Type	Steel w/ Window
	Industry Standards	EIA RS310-C
	Key Lock	Yes
	Rack Type	4-Post
	Side Panel Type	Solid Steel
	U Height	15U
Wallmountable	No	
Performance	Air Flow Rate	82.8 CFM (each)
	Noise Level	39 dBA
	Weight Capacity	2210 lb [1000 kg]
Power	Input Current	0.13/0.14 A
	Input Voltage	115V AC
Physical Characteristics	Color	Black
	External Depth	35.4 in [900 mm]
	External Height	30.1 in [764 mm]
	External Width	22 in [560 mm]
	Height with Casters	33.1 in [841 mm]
	Internal Depth	31.4 in [797.6 mm]
	Internal Height	26.3 in [668 mm]
	Internal Width	18.3 in [465 mm]
	Maximum Mounting Depth	27.6 in [700 mm]
Packaging Information	Flat Pack	No
	Shipping (Package) Weight	185.6 lb [84 kg]
What's in the Box	Included in Package	1 - 26X36X19 Inch 15U Cabinet Equipment Rack

1 - Bag of screws, fasteners and keys

Product appearance and specifications are subject to change without notice.