

10 ft IEEE-1394 FireWire Cable 6-6 M/M

Product ID: 1394_10



This 10ft IEEE 1394 FireWire Cable provides two FireWire 6-pin male connectors and is expertly designed and constructed of high quality materials and IEEE-1394 rated wire to ensure optimum performance and reliability.

Capable of data transfer rates of up to 400Mbps, FireWire technology provides a high speed link that saves time during large file transfers (e.g. transferring digital video files from a DV camcorder to a computer, etc.).

Certifications, Reports and Compatibility



	Warranty	Lifetime
Hardware	Cable Jacket Type	PVC - Polyvinyl Chloride
	Connector Plating	Nickel
	Number of Conductors	6
Connector(s)	Connector A	1 - FireWire 400 (6 pin, IEEE 1394a) Male
	Connector B	1 - FireWire 400 (6 pin, IEEE 1394a) Male
Physical Characteristics	Cable Length	10 ft [3 m]
	Color	Black
	Product Height	0 in [0 mm]
	Product Length	10 ft [3 m]
	Product Width	0 in [0 mm]
	Weight of Product	5.8 oz [165 g]
Packaging Information	Package Height	1 in [25 mm]
	Package Length	8.9 in [22.5 cm]
	Package Width	4.9 in [12.5 cm]
	Shipping (Package) Weight	6 oz [170 g]
What's in the Box	Included in Package	1 - 10 Ft IEEE-1394 FireWire Cable 6-6 M/M

Product appearance and specifications are subject to change without notice.