

Cat5e 350 MHz Snagless Molded (UTP) Ethernet Cable (RJ45 M/M) - Gray, 150 ft. (45.72 m)

MODEL NUMBER: **N001-150-GY**



Features

- Cabling for category 5 (Cat5) and 5e (Cat5e) applications
- Length: 150- Ft. Color: gray Connectors: RJ45 male
- Feature molded connectors with integral strain relief
- Snagless design protects the locking tabs on the RJ45 connectors from being damaged or snapped off during installation
- PVC 4-pair Solid UTP
- Rated for 350MHz/ 1Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801 and ETL (category 5e draft 11)
- Available in other colors and lengths
- Also available without the snagless feature (N002 series)
- Also available - Cat6 cables (N201 series)

Highlights

- Cabling for Category 5 (Cat5) and 5e (Cat5e) applications
- Solid Conductor wire for long distance performance
- Snagless boots protect the locking tabs on the RJ45 connectors from being damaged during installation
- Feature molded connectors with integral strain relief. Rated for 350 MHz/ 1 Gbps communication
- Meets most current industry standards including IEEE 802.3ab, IEEE 802.5, ANSI/EIA/TIA 568, ISO/IEC 11801, and ETL (Category 5e, draft 11)

System Requirements

- For 1000Base-T (1Gbps Ethernet), 10/100Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type3 applications.

Package Includes

- 150-ft. Gray Snagless Cat5e Patch Cable

Specifications

| OVERVIEW | |
|------------|--------------|
| UPC Code | 037332041913 |
| Technology | Cat5/5e |



| PHYSICAL | |
|--------------------------------------|------------------------------|
| Color | Gray |
| Cable Shielding | UTP |
| Cable Jacket Material | PVC |
| Cable Jacket Rating | CM |
| Number of Conductors | 4 Pair |
| Conductor Material | Solid Copper |
| Conductor Gauge | 26 AWG |
| Cable Length (ft.) | 150 |
| Cable Length (m) | 45.7 |
| Cable Length (in.) | 1800 |
| Cable Length (cm) | 4572 |
| Shipping Dimensions (hwd / cm) | 40.64 x 45.72 x 1.27 |
| Shipping Dimensions (hwd / in.) | 16.00 x 18.00 x 0.50 |
| Shipping Weight (kg) | 1.81 |
| Shipping Weight (lbs.) | 4.00 |
| COMMUNICATIONS | |
| Bandwidth per TIA Standard | 100 MHz |
| Maximum Bandwidth as Tested | 350 MHz |
| Maximum Data Rate | 1Gbps |
| Network Speed | 1Gbps |
| CONNECTIONS | |
| Side A - Connector 1 | RJ45 (MALE) |
| Side B - Connector 1 | RJ45 (MALE) |
| Connector Type | Molded; Snagless |
| Wiring Configuration | EIA/TIA 568B |
| FEATURES & SPECIFICATIONS | |
| Cable Style | Unshielded; Molded; Snagless |
| SPECIAL FEATURES | |
| IP68 Rated | No |
| Snagless Connector | Yes |
| Antibacterial | No |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| STANDARDS & COMPLIANCE | |
|-------------------------------------|---|
| Approvals | For 1000 Base-T (1Gbps Ethernet), 10/100 Base-T (Ethernet), 100 Mbps TPDDI, 155 Mbps ATM, ISDN, voice and Token Ring Type 3 applications. |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>