Rugged Mobile Computing Solutions

F120
ACCESSORY SPEC BROCHURE



Getac USA
15495 Sand Canyon Ave. Suite 350 Irvine, CA 92618 Tel : 949-681-2900
GetacSales_US@getac.com | www.getac.com/us/

Copyright © 2026 Getac Technology Corporation and/or any of its affiliates. All Rights Reserved.

CARRY BAG

Features & Benefits

Constructed of durable Nylon / air mesh fabric, and featuring an adjustable padded shoulder strap, this compact carry bag provides sturdy protection for your tablet while giving maximum comfort. The functional pockets inside offer the optimal solution to transport the tablet and needed accessories together in one case, delivering extra convenience and go-anywhere productivity to mobile professionals.

Product Information

Dimensions : L 340 x W 260 x D 65 mm
Weight : 760g
Main Material : Nylon, air mesh fabric

SKU ID

GMBCX2



100W TYPE-C AC ADAPTER

Features & Benefits

The 100W Type-C AC adapter as an additional charging solution to charge Getac rugged tablets and laptops with inherent USB type-C ports as well as the power delivery functionality. The Type-C adapter features a reversible connector type that reduces connector damages due to misuse.

Product Information

Input : 100V-240V
Output : 20V, 5A, 100W
Dimensions : L 140 x W 65 x H 25mm
Weight : 326g
Input cable length : 1830mm
Output cable length : 1500mm

SKU ID

GAT1E1 (EU Power Cord)
GAT1U1 (US Power Cord)
GAT1K1 (UK Power Cord)
GAT1A1 (AU Power Cord)
GAT1C1 (CHN Power Cord)
GAT1T1 (TW Power Cord)
GAT1I1 (IN Power Cord)



120W DC-DC VEHICLE ADAPTER

Features & Benefits

The 120W vehicle adapter comes with a choice of two types of connections: a bare wire with individual wire ends already stripped, and a cigarette lighter plug for easy connection to the cigarette lighter socket in the vehicle interior, providing a convenient way to charge and power your tablet while you are on the road.

Product Information

Input Voltage : 11VDC~ 32VDC
Output Voltage : 19VDC
Output current : 6.32A Max.
Case Dimensions : L 131.5 x W 65.6 x H 30mm
Weight : 362g
Input cable length : 1900mm
Output cable length : 1000mm

SKU ID

GAD2X4 (Cigarette Lighter Plug Version)
GAD2X8 (Bare Wire Version)



90W MIL-STD-461 AC ADAPTER

Features & Benefits

This MIL-STD-461G AC adapter has passed the military standard and testing specification to ensure the conducted emissions (CE), conducted susceptibility (CS), radiated emissions (RE), and radiated susceptibility (RS) of the adapter can meet the requirements for the control of electromagnetic interference.

Product Information

Input : 115V-230V, 1.6A 50~60Hz
Output : 19V, 4.74A, 90W
Dimensions : L 170 x W 75 x H 45mm
Weight : 880g (without power cord)
Input cable length : 1530mm
Output cable length : 1800mm

SKU ID

GAAGE5 (EU Power Cord)
GAAGU5 (US Power Cord)
GAAGK5 (UK Power Cord)
GAAGC5 (CHN Power Cord)
GAAGA5 (AU Power Cord)
GAAGI5 (IN Power Cord)
GAAGT5 (TW Power Cord)



DIGITIZER PEN WITH TETHER

Features & Benefits

The digitizer pen provides a more accurate and easy way for data entry and handwritten signature. A shortcut button allows the right mouse button functionality when using the pen.

Product Information

Stylus Dimensions : 109mm ; Ø9mm
Tip size : 2.0mm ; Ø1.65mm
Tether Length : 292mm

SKU ID

GMPDX6



GETAC DS100 USB-C DOCKING STATION WITH AC ADAPTER

Features & Benefits

The Getac DS100 USB-C Docking Station, featuring a slim and compact design, seamlessly consolidates cables on the workstation. This allows users to swiftly create a personalized workspace and organize their daily office environment. Compatible with various Getac laptop and tablet models, it provides extra connectivity and multiple I/O ports for additional peripherals and data sources.With support for MAC Address Pass-Through, Wake-on-LAN (WoL), and PXE Boot, the DS100 aids IT administrators in maintaining a secure, efficient, and well-managed network infrastructure.

Product Information

Dimensions: L 207 x W 90 x H 34.1mm
Weight (without 135W AC Adapter): 372.4g (0.82lbs)
Power Cable Length: 1.8m
USB-C Upstream Cable Length: 1m
I/O Ports: DC in Jack x 1, USB 3.2 Gen 1 Type-A x 3,
USB 3.2 Gen 2 Type-C x 2, LAN x 1, HDMI 2.0 x 1, DisplayPort 1.4 x 2,
Kensington lock, Kensington nano slot
(For use in non-hazardous areas only)



SKU ID

GDDSE2 (EU Power Cord)
GDDSU2 (US Power Cord)
GDDSK2 (UK Power Cord)
GDDSA2 (AU Power Cord)
GDDSC2 (CHN Power Cord)
GDDST2 (TW Power Cord)
GDDSI2 (IN Power Cord)

SHOULDER HARNESS 4-POINT

Features & Benefits

This shoulder harness has four snap hooks which attach to the corner rings on the tablet, and can be easily detached as well. The harness is worn in a backpack style, allowing the tablet to be carried hands-free in front of the user at a belt level for easy accessibility. It also delivers optimal support and a comfortable fit during movement, thanks to its wide soft padding and adjustable straps.

Product Information

Dimensions : 1380 x 372mm
Main Material : Polyester

SKU ID

GMS4X4





SHOULDER STRAP 2-POINT

Features & Benefits

This shoulder strap attaches via two holders at the back of the tablet and is adjustable to fit most body sizes for both cross-body and shoulder carry. With its durable, sturdy design, the strap not only provides a comfortable, grip-free carrying option of the tablet but also helps in avoiding accidental drops while on the move. The shoulder strap can also attach to the detachable keyboard (sold separately) via two D-rings on the built-in handle.

Product Information

Dimensions : 38 x 1530mm
Main Material : Polyeste

SKU ID

GMS2X8



CAPACITIVE STYLUS & TETHER

Features & Benefits

This capacitive hard tip stylus is lightweight and easy to control, allowing smooth and comfortable interaction with the touch screen without worrying about scratching the screen or leaving fingerprints on it. The stylus comes with a detachable tether to keep the stylus attached to the device, so it doesn't get lost or misplaced.

Product Information

Stylus Dimensions : 110mm ; Ø9mm
Tip size : 4mm ; Ø5.5mm
Tether Length : 304mm

SKU ID

GMPSXW
* MOQ : 10pcs



SCREEN PROTECTION FILM

Features & Benefits

This screen protection film is cut precisely to fit the F120 tablet and is easy to install and remove without leaving a sticky residue. With anti-glare coating, it not only protects the screen from the rigors of daily use but also help diffuses light on the screen and reduces glare, providing effortless readability for displayed information under common ambient lighting conditions.

Product Information

Dimensions : L 269.09 x W 175.7mm
Main Material : PET

SKU ID

GMPFXX



STANDARD BATTERY 4070MAH (1-PACK)

Features & Benefits

The hot-swappable battery can support full-shift computing with no downtime. It is a great solution for mobile professionals who require long battery life for all-day operation.

Product Information

Battery Type : Lithium-ion Polymer
Voltage : 7.74V
Capacity : Typical 4070mAh ; Min. 3800mAh
Dimensions : L 133 x W 74 x H 10mm
Weight : 146g

SKU ID

GBM2X4



65W AC ADAPTER WITH POWER CORD

Features & Benefits

This adapter is designed to power the device and charge its internal battery from an AC power source. A country-specific power cord is included with the adapter to fit the local power outlet in your designated country.

Product Information

Input : 100V-240V, 50~60Hz, 1.5A
Output : 19V, 3.42A, 65W
Dimensions : L 108.3 x W 46.3 x H 30mm
Weight : 250g
Input cable length : 1830mm
Output cable length. : 1500mm

SKU ID

GAA6E5 (EU Power Cord)
GAA6U5 (US Power Cord)
GAA6K5 (UK Power Cord)
GAA6A5 (AU Power Cord)
GAA6C5 (CHN Power Cord)
GAA6T5 (TW Power Cord)
GAA6G5 (ARG Power Cord)
GAA6I5 (IN Power Cord)



HIGH-CAPACITY BATTERY 4070MAH (1-PACK)

Features & Benefits

The high-capacity battery pack extends the system run time up to two times compared to the standard battery pack, providing a great solution for mobile professionals who require extra battery life for operation longer than one day.

Product Information

Battery Type : Lithium-ion Polymer
Voltage : 11.61V
Capacity : Typical 4070mAh ; Min. 3800mAh
Dimensions : L 133 x W 74 x H 16.8mm
Weight : 205g

SKU ID

GBM3X8



GETAC RUGGED KEYBOARD

Features & Benefits

The Getac Rugged Keyboard is designed with VESA and AMPS mounting capability that allow it to be placed firmly in the vehicle. It has gone through vigorous test that comply with MIL-STD 810G and IP65. It also features with 88 full sized keys, red LED backlight with five levels of brightness and impressive key response that will truly enhance user experience.

Product Information

Dimension : 307.7 x 194 x 32 mm
Weight : 870g
Compatibility : Windows 11 Pro
Backlit : Red LED. five levels of brightness
Coiled Cable Length : USB 2.0 interface, 1.83m



SKU ID

Getac Rugged Keyboard	Getac Rugged Keyboard with Smart card and USB 2.0	Getac Rugged Keyboard with Smart card and LF/HF RFID
GDKBU9 (US) GDKBC9 (UK) GDKBB9 (DE) GDKBD9 (FR) GDKBM9 (ES) GDKBF9 (Canadian French)	GDKBU6 (US) GDKBC6 (UK) GDKBB6 (DE) GDKBD6 (FR) GDKBM6 (ES) GDKBF6 (Canadian French)	GDKBU7 (US) GDKBC7 (UK) GDKBB7 (DE) GDKBD7 (FR) GDKBM7 (ES) GDKBF7 (Canadian French)

65W USB-C AC ADAPTER

Features & Benefits

This adapter is designed to power the device and charge its internal battery from an AC power source.

Product Information

Input : 100V-240V, 50~60Hz, 1.6A
Output : 5V/3A, 9V/3A, 12V/3A, 15V/3A, 20V/3.25A
Dimensions : L 90 x W 51 x H 28.5mm
Weight : 220g ±15g
Input cable length : 1830mm
Output cable length. : 1500mm

SKU ID

GAT6U1 (US Power Cord)
GAT6E1 (EU Power Cord)
GAT6K1 (UK Power Cord)
GAT6A1 (AU Power Cord)
GAT6C1 (CHN Power Cord)
GAT6T1 (TW Power Cord)



EXTERNAL DUAL-BAY BATTERY CHARGER

Features & Benefits

This external dual-bay battery charger is designed to charge up to two batteries at the same time. It provides the benefit of charging and storing the 2 batteries together when there is limited space and power socket.

Product Information

AC Input : 100V~240V
DC Output : 13.05V, 2.4A Max.
Number of charge bay : 2 Bay
Dimensions : L 160 x W 180 x H 72.5mm
Weight : 1.2kg ,not including battery packs
Support main batteries and high-capacity batteries.



SKU ID

GCMCET (EU Power Cord)
GCMCUT (US Power Cord)
GCMCKT (UK Power Cord)
GCMCAT (AU Power Cord)
GCMCCT (CHN Power Cord)
GCMCTT (TW Power Cord)
GCMCGT (ARG Power Cord)
GCMCIT (IN Power Cord)

MULTI-BAY BATTERY CHARGER EIGHT BAY

Features & Benefits

The 8-bay multi-battery charger is designed to charge multiple battery packs simultaneously and provide users an efficient charging solution.

Product Information

AC Input : 100V~240V AC, 4.2A 50~60Hz
DC Output : 19.5V, 16.9A
* w / 330W AC Adapter
Number of charge bays : 8 bays
Dimensions : L 465 x W 245 x H 95.3~111.3mm
Weight : 4.7 kg ,not including battery packs
Support main batteries and high-capacity batteries.



SKU ID

GCECET (EU Power Cord)
GCECUT (US Power Cord)
GCECKT (UK Power Cord)
GCECAT (AU Power Cord)
GCECCT (CHN Power Cord)
GCECTT (TW Power Cord)
GCECIT (IN Power Cord)

ROTATING HAND STRAP & KICKSTAND

Features & Benefits

The Rotating Hand Strap is designed to make using the tablet easier and more convenient to carry. The hand strap is adjustable to fit most hand sizes and can be rotated 360 degrees to find the ideal viewing angle while on-the-go. It also includes a built-in kickstand that allows for handsfree usage on flat surfaces, providing more on-the-job flexibility.

Product Information

Dimensions : L 236 x W 136 x H 25mm
Weight: 202g
Main Material : PU

SKU ID

GMHRXQ



SPARE MAIN STORAGE WITH CANISTER

Features & Benefits

Getac Spare Main Storage with canister is designed to provide you the ease of installation and allow you to remove your confidential data when your device is sent for service.

Product Information

Capacity : PCIe NVMe 256GB/512GB/1TB/2TB
Dimension : L 162.4 x W 28.2 x H 5.6mm
Weight : 30g

SKU ID

GSSEXC (Removable 256GB PCIe SSD w/ Canister)
GSSFXD (Removable 512GB PCIe SSD w/ Canister)
GSSGXE (Removable 1TB PCIe SSD w/ Canister)
GSSHXC (Removable 2TB PCIe SSD w/ Canister)



HARD HANDLE

Features & Benefits

The multi-functional hard handle offers extra mobility to field workers to grab-and-go when situation required.

Product Information

Dimensions : L 309.73 x W 65.1 x H 28.7mm
Weight : 170g
Main Material : PC

SKU ID

GMHDXC



KEYBOARD DOCK

Features & Benefits

Featuring 4-level red backlighting, 83 full-size keys and an integrated touchpad, the keyboard dock allows for a user-friendly, laptop-like operation to minimize mistakes and increase the efficiency as you perform data-intensive tasks. It also carries a variety of I/O ports for connections to peripherals and other devices .Its Double-locking mechanism strengthens the tablet-keyboard connection and prevents the keyboard from accidentally falling off.

Product Information

Dimension : L 312 x W 260 x H 21.7mm / L 312 x W 260 x H 57.7mm (with holder)
Weight : 980g
Structure : IP66; membrane
Drop : 4ft
Layout : 83 keys
I/O Interfaces : USB 3.1 Gen 1 Type-A x 1, LAN x 1
Docking Connector (to tablet)



SKU ID

GDKBUS (US)
GDKBBS (DE)
GDKBCS (UK)
GDKBDS (FR)
GDKBES (IT)
GDKBGS (Traditional Chinese)
GDKBMS (Spanish)
GDKBTS (Turkey)
GDKBWS (US International)
GDKBFS (Canadian French)

SLIM HAND STRAP WITH STYLUS HOLDER 2-POINT

Features & Benefits

The adjustable strap is designed to keep the tablet securely in the user's hand for easier carrying, and comes with a built-in stylus holder for added convenience.

Product Information

Dimensions : L 155 x W 45 x H 8mm
Weight : 37g
Main Material : Polyester

SKU ID

GMHSXF



GETAC RUGGED KEYBOARD V2.0

Features & Benefits

The Getac Rugged Keyboard V2.0 features VESA and AMPS mounting for secure vehicle placement and complies with MIL-STD 810G and IP65 standards for extreme durability. The newly optimized 83-key layout integrates navigation keys to save space, while maintaining a five-level red LED backlight and impressive key response. It also introduces a dedicated Copilot key for instant AI access, empowering modern productivity.

Product Information

Dimension : 307.7 x 194 x 32 mm
Weight : 870g
Compatibility : Windows 11 Pro
Backlit : Red LED. five levels of brightness
Coiled Cable Length : USB 2.0 interface, 1.83m



SKU ID

Getac Rugged Keyboard V2.0	Getac Rugged Keyboard V2.0 with Smart card and USB 2.0	Getac Rugged Keyboard V2.0 with Smart card and LF/HF RFID
GDKBUT (US) GDKBCT (UK) GDKBBT (DE) GDKBDT (FR) GDKBMT (ES) GDKBFT (Canadian French)	GDKBUU (US) GDKBCU (UK) GDKBBU (DE) GDKBDU (FR) GDKBMU (ES) GDKBFU (Canadian French)	GDKBUV (US) GDKBCV (UK) GDKBBV (DE) GDKBDV (FR) GDKBMV (ES) GDKBFV (Canadian French)