HP Color LaserJet Lunar Gray 2100 sheet High Capacity Paper Tray/Stand (65A37A)



Overview

Increase input capacity by 2,100 sheets and easily relocate the printer.

Reduce trips to the printer to reload paper with this paper input accessory. Print more pages without having to reload paper.

Help individuals and workteams save time and be more productive with additional paper capacity of 2,100 sheets. Use the wheeled stand to relocate the printer to where it's needed.

The HP Color LaserJet 2100 sheet High Capacity Paper Tray/Stand enables printing on different types of paper. It supports A4, letter and legal paper.

Specifications

Product Dimensions (metric)	520 x 520 x 393 mm
Product Dimensions (imperial)	20.5 x 20.5 x 15.5 in
Weight (metric)	~21.36 kg
Weight (imperial)	~47 lb
Package Dimensions (metric)	758 x 788 x 540 mm
Package Weight (metric)	~26.36 kg
UPC Number	196548169665
Manufacturer Warranty	90 Day Parts Only warranty. (warranty code 3R; warranty ID A065)
What Is In The Box	HP Color LaserJet Stand Lunar Gray 2100 sheet High Capacity Paper Tray/Stand; 4 Stability Feet; Installation Instructions

Additional specifications

Business Filter	cMPS
Cartons Per Layer	1
Compatibility Statement	HP Color LaserJet Enterprise 6700dn 6QN33A; HP Color LaserJet Enterprise 6701dn 58M42A; HP Color LaserJet Enterprise X654dn 6QQ00A; HP Color LaserJet Enterprise X65455dn 49L02A; HP Color LaserJet Enterprise X65465dn 49L04A; HP Color LaserJet Enterprise Flow MFP 6800zf 6QN36A; HP Color LaserJet Enterprise Flow MFP 6800zfsw 6QN37A; HP Color LaserJet Flow MFP 6800zfw+ 6QN38A; HP Color LaserJet Enterprise Flow MFP X677zs 6QQ02A; HP Color LaserJet Enterprise Flow MFP X677z+ 6QQ03A; HP Color LaserJet Enterprise Flow MFP X67755zs 49K87A; HP Color LaserJet Enterprise Flow MFP X67765zs 49K91A; HP Color LaserJet Enterprise Flow MFP X67755z+ 49K88A; HP Color LaserJet Enterprise Flow MFP X67765z+ 49K92A
Component Type	Printer accessories
Count of Layers In Pallet	3
Input Capacity, Max	Up to 2100 sheets
Media Sizes Custom (imperial)	4.0 x 5.8 to 8.5 x 14 in
Media Sizes Custom (metric)	101.6 x 148 to 215.9 x 355.6 mm
Media Types	Paper (plain, light, intermediate, light bond, bond, recycled, mid-weight, heavy, mid-weight glossy, heavy glossy, extra heavy, extra heavy glossy, cardstock, card glossy), color transparency, labels, letterhead, envelope, preprinted, prepunched, colored, rough, opaque film, user-defined
Package Dimensions (imperial)	29.84 x 31.02 x 21.26 in
Package Weight (imperial)	~58 lb
Pallet Dimensions (imperial)	29.92 x 31.1 x 68.78 in
Pallet Dimensions (metric)	760 x 790 x 1747 mm
Pallet Weight (imperial)	381 lb
Pallet Weight (metric)	173.18 kg
Product Number orderable	65A37A
Quantity Per Pallet	3
Tariff Numbers	8443995015; 8443999000; 84439990
UNSPSC Code	44101705
Warranty Standard Statement	90 Day Parts Only warranty. Warranty and support options vary by product, country and local legal requirements. Contact your Contractual Vendor or go to hp.com/support to learn about HP award winning service and support options in your region. (warranty code 3R; warranty ID A065)

Disclaimer — Copyright

© Copyright 2026 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Apr 03, 2026 10:19 PM UTC+0000