C2G

3ft (0.9m) Serial RS232 DB9 Cable with Low Profile Connectors M/F - In-Wall CMG-Rated

Part No. CG-52156



Audio/Video installations in educational and commercial settings often require in-wall rated cable. Our CMG-rated line was specifically engineered to meet this requirement while overcoming common challenges faced by installers in these environments. Low-Profile connectors (1.25 in total depth) save valuable space in the gang box, while the rounded shape accommodates smaller monitor mounts so that the cable can be easily hidden from view.

Specifically designed to support RS-232/Serial communications, this cable is fully shielded to prevent unwanted EMI/RFI interference. The fully molded cable design delivers excellent strain relief, while connector thumbscrews provide a quick and easy connection every time.

The transmit and receive signals are crossed to ensure proper data transmission.

CMG-rated cables meet with many NEC requirements for Communications Cables - General Purpose In Wall Use . Our cables meet the following ratings: CMG, FT4 (Canada)

Features & Benefits

- Designed to support RS-232/Serial communications
- CMG-rated for in-wall use
- Shielded to prevent unwanted EMI/RFI interference
- Connector thumbscrews for a quick and easy connection

Specifications

General Info

Product Line	C2G	Color	Black
UPC Number	757120521563	Country Of Origin	Vietnam
Features	RS232	Application Sector	Residential, Commercial, Industrial
Type	Cable		

Dimensions

Cable Length	3 ft		

Additional Information

Prop 65 Warning Required	Yes	Prop 65 Warning Language	Cancer and Reproductive Harm

Technical Information

Jacket Material	PVC (Polyvinyl Chloride)	Wire Gauge	28 AWG
Cable Type	Serial	Jacket Rating	CMG (FT4) Rated
Adapter Rear	DB9 Female	Adapter Front	DB9 Male