ThinkVision T65 62F3KATCUS

PSREF
Product Specifications Reference

PERFORMANCE

Display Size
65″

View Area
1428.5x803.5 mm

Panel
In-Plane Switching

Backlight
DLED

Aspect Ratio
16:9

Resolution
3840x2160

Pixel Pitch
0.3720x0.3720 mm

Dot / Pixel Per Inch
67 dpi

View Angle (H / V)
178° / 178°

Response Time
8ms

Color Support
1.07 Billion

Refresh Rate
60Hz

Brightness
400 cd/m²

Contrast Ratio
1200:1

Color Gamut
85% NTSC, 99%sRGB

Screen Surface Treatment
Anti-glare

Curvature
None

Camera
None

Microphone
8x, Array

Speakers
15Wx2

Power Consumption (Typical / Maximum)
199W / 251W

Power Adapter
Integrated

Touchscreen
20-point IR Touch

Smart System
Android™ 9.0 / 4x A73 Cores / 4 GB / 64 GB / Remote Control with Battery

DESIGN

Stand
None

Case Color
Raven Black

Side Bezel Width
28.84 mm

Dimensions with Stand (HxWxD)
952.0x1527.5x87.8 mm / 37.5x60.1x3.5 inches

Weight (Including Stand)
40.5 kg / 89.29 lbs

Mounting
Supports VESA mount 600 x 400 mm

ThinkCentre® M Series Support
None

CONNECTIVITY

USB Port
3x USB 3.0, 2x USB-C® 3.0, 1x USB 2.0, 1x USB-B (Touch), 1x USB-B (Touch Out)

Video Connector
4x HDMI® 2.0, 1x HDMI 2.0 out, 1x DP 1.2, 1x VGA, 1x AV, 2x USB-C 3.0

Network Connectivity
1x RJ45 In, 1x RJ45 Out, Bluetooth® 5.0+802.11ac (2.4 and 5 GHz bands)

SERVICE

Base Warranty
3-year

CERTIFICATIONS

Environmental Certification
RoHS Compliant

Ergonomic Certification
TÜV Rheinland® Low Blue Light, TÜV Rheinland Flicker Free

Sync Technology
None

Special Features
- HDR10 Compliance
- 1x Human Detection Sensor
- 1x Ambient Light Sensor

SOFTWARE

Operating System
Android™ 9 (Pie)

ACCESSORIES

Video Cables
HDMI® cable, USB Type-A to Type-B cable

MODEL

Announce Date	: 2023-05-15	**EAN / UPC / JAN**	: 0196803819069 / 196803819069 / None



Product image is a sample, it may not match the real color of this model

Premium Care - **Advanced Support from Real People. Real Fast.**

REAL PERSON
Choose how you want to reach us - through the phone, chat or email - our expert technicians will take care of you.

REAL FAST
Highly trained technicians will provide you real-time solutions, whatever the issue, on your first contact. If needed, our team will schedule an onsite visit for the next business day.

HASSLE FREE
'Getting started' and 'how-to' assistance for hardware and software. Easy solutions that are simple to reach - that's how Premium Care delivers you the ideal support experience.

PC HEALTH CHECK
Free annual PC Health Check that allows our experts to spot issues before you do so they can resolve them quickly and help you avoid PC problems.







Accidental Damage Protection - **Protection of your PC from the unexpected.**

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty – **Included with the systems you purchase, default 1- or 3-year coverage window.**

Warranty Extensions & Upgrades – **Service and protection that's right for your circumstances.**

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Lenovo **PSREF**
Product Specifications Reference