DTEN

Designed for zoom

DTEN ON 55”

SPECIFICATIONS

All-in-One
Zoom Rooms Appliance





*DTEN ON in this image is not in 1:1 ratio

PRODUCT	DTEN ON 55"
SOFTWARE	DTEN OS
ALL-IN-ONE	Multi-Touch Display 4K Camera 16-Microphone Array Integrated Speakers
DISPLAY	LED 55",Ultra HD 4K,16:9 Capacitive Touch Screen Display
CAMERA SYSTEM	Fixed Lens, Infinite Focus F-value: 2.8,4K Diagonal Field of View (FOV): Up tp 120 Degrees
AUDIO SYSTEM	16-Microphone Array Microphone Pickup Range 0-60 ft. Speaker Range 0-60 ft. Integrated Stereo Speakers High Quality Audio Acoustic Echo Cancellation Automatic Gain Control (AGC) Automatic Noise Reduction
NETWORK	Ethernet (RJ-45) 100/1000 Mbps Wi-Fi 802.11a/b/g/n, 802.11ac (2.4 and 5 GHz) IPv4 Dynamic Host Configuration Protocol (DHCP)/ Static HTTP/HTTPS Proxy Support

INPUTS AND OUTPUTS	HDMI In x 1 3.5-mm Audio Jack x 1 Ethernet LAN (RJ45) x 1
POWER	100 to 240 VAC, 50 to 60 Hz
VESA	400 x 300 mm
PRODUCT DIMENSIONS	49 x 30.5 x 2.13 in (124.49 x 77.38 x 5.42 cm)
PRODUCT WEIGHT	50.7 lb (23 kg)
PACKAGE DIMENSIONS	56 x 36 x 8.5 in (142 x 92 x 21.5 cm) * With an outer box
PACKAGE WEIGHT	77 lb (35 kg)
OPERATING TEMPERATURE AND HUMIDITY	Operating Temperature 0°C to 40°C Storage Temperature -10°C to 60°C Operating Humidity 20% to 80% RH Storage Humidity 10% to 60% RH
LANGUAGE SUPPORT	English * Additional languages to be supported in future software release

*Specifications are subject to change without prior notice.

Zoom Rooms Simplified

DTEN.COM SALES@DTEN.COM 1.866.936.3836