ThinkSmart Core for Microsoft Team Rooms 11S3000EUS

PSREF
Product Specifications Reference

PERFORMANCE

Processor
Intel® Core™ i5-1145G7E (4C / 8T, 1.5 / 4.1GHz, 8MB)

Graphics
Integrated Intel Iris® Xe Graphics

Chipset
Intel SoC Platform

Memory
1x 8GB Soldered DDR4-3200

Memory Slots
Memory soldered to systemboard, no slots, dual-channel

Max Memory
16GB soldered memory, not upgradable

Storage
256GB SSD M.2 2280 PCIe® 3.0x4 NVMe®

Storage Support
One drive, 256GB M.2 2280 SSD

Power Supply
90W 89% Adapter

DESIGN

Touchscreen
10-point Multi-touch

Case Color
Black (ThinkSmart™ Core + ThinkSmart Controller Full Room Kit)

Mounting
Integrated VESA Mount

Component Options
ThinkSmart Core + ThinkSmart Controller Full Room Kit|1x ThinkSmart Core|1x ThinkSmart Controller|1x ThinkSmart Bar|2x Satellite Microphone|1x ThinkSmart Cam

Controller
ThinkSmart Controller, 10.1" Display, 10-point Multi-touch

Camera Component
ThinkSmart Cam

Microphone Component
2x Mic on ThinkSmart Cam + 4x Mic on ThinkSmart Bar + 2x Satellite Mic

Audio Bar
ThinkSmart Bar (4 Speakers)

Dimensions (WxDxH)[1]
- ThinkSmart controller|265.5 x 13 x 168.1 mm (10.5 x 0.5 x 6.6 inches)
- ThinkSmart controller with stand|265.5 x 83.3 x 168.1 mm (10.5 x 3.3 x 6.6 inches)
- Compute System|226 x 200 x 37.5 mm (8.9 x 7.9 x 1.5 inches)
- Compute System with clamp unfold|226 x 200 x 51.7 mm (8.9x 7.9 x 2 inches)

Weight[2]
- Compute System|1.1 kg (2.4 lbs)
- ThinkSmart controller|753.8 g (1.7 lbs)

CONNECTIVITY

Ethernet
Integrated 100/1000M

WLAN + Bluetooth®
Intel Wi-Fi® 6 AX201, 11ax 2x2 + BT5.0, vPro®

Rear Ports
- 1x Thunderbolt™ 4
- 1x USB-C® 3.2 Gen 1
- 1x USB 3.2 Gen 1
- 2x USB 3.2 Gen 2
- 1x HDMI®-in
- 2x HDMI-out 1.4
- 1x Ethernet (RJ-45)
- 1x power connector

SECURITY & PRIVACY

Security Chip
Discrete TPM 2.0, TCG certified

Physical Locks
Kensington® Security Slot™

MANAGEABILITY

System Management
Intel vPro

SERVICE

Base Warranty
3-year, Onsite

Included Upgrade
First Year Maintenance, 3Y Premier Support Upgrade from 3Y Onsite

SOFTWARE

Operating System
Windows® 10 IoT Enterprise SAC 64, English

Bundled Software
Microsoft® Teams Rooms

MODEL

TopSeller	: Yes	**Announce Date**	: 2022-08-09
EAN / UPC / JAN	: 196802728171	**End of Support**	: N/A



Product image is a sample, it may not match the real color of this model

Note:
[1] The system dimensions may vary depending on configurations.
[2] The system weight is approximate and based on results in Lenovo lab, which varies depending on the source of component, variance of the distribution of each component, and manufacturing process. It may not be the exact weight for each specific model.
· Lenovo reserves the right to change specifications without notice.
To see more note information, please link to
https://psref.lenovo.com/Detail/1746?M=11S3000EUS

Premier Support - **A direct 24x7x365 line to our most elite technicians.**

- Advanced technical support, 24x7x365, in more than 100 markets
- Technical Account Managers for proactive relationship and escalation management
- Comprehensive hardware & OEM software support
- Priority on service delivery and repair parts
- Single point of contact for simplified end-to-end case management
- Lenovo Service Connect Portal for customized reporting and product support

Accidental Damage Protection - **Protection of your PC from the unexpected.**

Experience shows that a significant portion of devices may be damaged (and not covered under warranty) in the first three years. Lenovo's Accidental Damage Protection service covers accidents beyond the system warranty such as drops, spills, bumps and even electrical surges. Make sure your new device has maximum protection, avoid unplanned costs and get peace of mind.

Base Warranty - **Included with the systems you purchase, default 1- or 3-year coverage window.**

Warranty Extensions & Upgrades - **Service and protection that's right for your circumstances.**

- Pick Up & Return Courier
- Onsite Support
- Technician Installed Customer
- Replaceable Unit Service
- International Warranty Upgrade

Lenovo may not offer the products, services or features discussed in this document in all regions. Lenovo may withdraw an offering at any time. Information is subject to change without notice. Consult your local representative for information on offerings available in your area. Lenovo reserves the right to change specifications or other product information without notice. Lenovo is not responsible for photographic or typographical errors. Lenovo provides this publication "as is" without warranty of any kind, either express or implied, including the implied warranties of merchantability or fitness for a particular purpose.

Recommended Accessories



Lenovo 500 FHD Webcam

4XC0V13599

A USB Video Class (UVC) compliant video camera designed for teleconferencing applications on desktop or laptop. It's a reliable digital video device to transfer video data with HD quality through a high-speed USB inte...



Lenovo Universal USB 3.0 to VGA/HDMI Adapter

4X90H20061

The Lenovo Universal USB 3.0 to VGA/HDMI Adapter turns an available USB 3.0 port into a display port offering either VGA or HDMI output with support for high-definition 1080p and with audio (from HDMI port only). The ...

For a full list of accessories and services, please visit:
https://smartfind.Lenovo.com

Lenovo **PSREF**
Product Specifications Reference