

VGA Monitor Extension Cable, 640x480 (HD15 M/F), 10 ft. (3.05 m)

MODEL NUMBER: P510-010



Highlights

 Superior molded cables with foilshielding for maximum EMI/RFI protection

System Requirements

 Monitor with HD15 cable and resolutions up to 640x480.

Package Includes

 10-ft. VGA Monitor Extension HD15F to HD15M Gold Connectors

Features

- Superior molded cables with foil-shielding for maximum EMI/RFI protection
- Gold plated connectors and gold plated copper contacts ensure excellent conductivity
- HD15 male to HD15 female molded connectors

Specifications

OVERVIEW	
UPC Code	037332012340
Product Type	Passive Cable
Technology	VGA/SVGA
Cable Type	Passive
PHYSICAL	
Color	Black
Cable Jacket Color	Black
Cable Length (ft.)	10
Cable Length (m)	3.05
Cable Length (in.)	120
Shipping Dimensions (hwd / in.)	8.50 x 6.90 x 0.50
Shipping Dimensions (hwd / cm)	21.59 x 17.53 x 1.27



Shipping Weight (lbs.)	0.44	
Shipping Weight (kg)	0.20	
CONNECTIONS		
Side A - Connector 1	HD15 (MALE)	
Side B - Connector 1	HD15 (FEMALE)	
Latching or Gripping Connector	No	
FEATURES & SPECIFICATIONS		
IP68 Rated	No	
STANDARDS & COMPLIANCE		
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	



© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.