HAVIS DOCKING STATIONS FOR DELL 10" LATITUDE 7030 RUGGED EXTREME TABLET

PKG-DELL-1200 SERIES



REDEFINING RUGGED RESILIENCE IN WAREHOUSE APPLICATIONS

- Two-piece design provides IP65 rating & device mobility
- Port replication for seamless integration of multiple peripherals
- LED power indicator
- IP65 sealed I/O panel accommodates a variety of cable diameters
- One-handed docking & undocking
- Spring-loaded connector head
- Internal, non-isolated (9-36VDC) or external, isolated power supply
- Access to all tablet buttons & ports when docked
- Compatible with accessories, including hard & soft handles & shoulder strap
- Compact & lightweight
- Integrated cable management system
- Integrated VESA 75 mounting pattern

HAVIS DOCKING STATIONS FOR DELL 10" LATITUDE 7030 RUGGED EXTREME TABLET

PKG-DELL-1200 SERIES

DELL 7030 TABLET SOLUTION

- Two-piece design provides IP65 rating & device mobility
- One-handed docking & undocking
- Port replication for seamless integration of multiple peripherals
- Internal, non-isolated (9-36VDC) or external, isolated power supply
- LED power indicator



PART NUMBER	TABLET ADAPTER	DOCKING STATION	ETHERNET	USB 3.0	SERIAL	POWER INPUT	EXTERNAL POWER	INTERNAL POWER
PKG-DELL-1201-1232	TA-102	DS-TAB-301	1	3	1 @ 5V	12-32 V	LPS-186	
PKG-DELL-1201-2060	TA-102	DS-TAB-301	1	3	1 @ 5V	20-60 V	LPS-187	
PKG-DELL-1202	TA-102	DS-TAB-302	1	3	1 @ 5V	9-36 V		YES

SPECIFICATIONS:

Height: 9.64” (24.47cm)
Width: 9.35” (23.75cm)
Depth: 3.20” (8.13cm)
Weight: 2.77 lbs (1.26 kg)

CERTIFICATIONS & TESTING:

Vibration Testing: MIL-STD 810H 514.8
Crash Testing: SAE J1455 30mph
Cycle Test: Latch handle & docking connectors 30K cycles
Environmental Testing: Hot/Cold Operational -29° C to 63° C (-20° F to 145° F); Hot/Cold storage -40° C to 85° C (-40° F to 185° F)