Ortronics

TRACJACK RECESSED F-CONN 75 OHM WHITE

Part No. 63700087-88



The TracJack, recessed 75 ohm, F-Type, female to female connector, Fog White Adapter Plate, has a single Recessed F-Type, 75Ω, feedthrough connector, mounted at a 180° exit angle. F-connectors are often used with RG-6 and RG-59 75 ohm coaxial cable to connect equipment supporting cable TV(CATV), satellite TV, close circuit TV(CCTV), and security cameras. This adapter panel is 1 unit high. TracJack modules offer flexabilty with structured cabling at the workstation or in furniture with a modular design and a wide variety of connectivity options. Inteligent engineering simplifies and speeds up moves, adds, and changes with a front removeable design. Compatible With: All TracJack faceplates

Features & Benefits

Meets Category 5e standard: Ensures standards compliance.

Designed for multiple coax cable styles: Accepts both push-style and screw-style.

Standard TracJack footprint: Fits in all TracJack faceplates and housings.

Integrates with Legrand Wiremold : Can be used in raceway, floor boxes, Poke-Thru, and work surface portals.

Low profile connector: Allows furniture to be placed closer to the wall.

75 Ohm F-connector: Ideal for cable/satellite TV, cable modems, and security cameras.

Front removable module: Less intrusive access for adds, moves, changes.

Specifications

General Info

Product Line	Ortronics	Color	Cloud White
UPC Number	662875834779	Country Of Origin	Taiwan, Province Of China
Application Sector	Commercial	Standard	UL Standard
Warranty Type	5-Year	Type	Workstation

Dimensions

Product Width US	0.73 in	Product Depth US	0.875 in
Product Height US	0.92 in		

Technical Information

Connector 2	F-Type Female	Connector 1	F-Type Female
Connectivity Footprint	TracJack		