Poly EduCart System G7500 with EagleEyeIV 12x and Speakers with Cart (ABA) (9P7Y7AA)



Overview

Customize rooms with confidence

Boost productivity and collaboration using the Poly G7500 video conferencing system with the Poly Studio E70 and TC10, designed to bring teams closer with crystal-clear communication, seamless interaction, flexible setup, and immersive meeting experiences.

Create your ideal space

This modular video conferencing system makes it easy to outfit conference rooms to meet your organization's unique needs. Loaded with flexible features, the Poly G7500 bundle leverages your design to power your meetings and wow your teams [1].

Smart technology, focused meetings

Experience clear, distraction-free meetings with smart audio and video technologies from Poly. Easy touch controls keep calls, camera, and content on track, ensuring efficient, focused discussions.

---

[1] The Poly G7500 Video Conferencing System with Poly Studio E70 and the Poly TC10 touch controller.

Additional specifications

Audio	Poly NoiseBlockAI technology; Poly Acoustic Fence technology
Audio standards	22 kHz with Polycom Siren 22 technology; 20 kHz with G.719 (M- Mode) and Polycom Siren 22 technology; 14 kHz with Polycom Siren 14 technology, G.722.1 Annex C; 7 kHz with G.722, G.722.1; 3.4 kHz with G.711, G.728, G.729A
Certified collaboration software	Zoom; Microsoft Teams
Color	Black
Content video resolution (input)	UHD (3840 x 2160); HD (1920 x 1080); WSXGA+ (1680 x 1050); UXGA (1600 x 1200); SXGA (1280 x 1024); WXGA (1280 x 768); HD (1280 x 720); XGA (1024 x 768); SVGA (800 x 600)
Content video resolution (output)	UHD (3840 x 2160); WUXGA (1920 x 1200); HD (1920 x 1080); WSXGA+ (1680 x 1050); SXGA+ (1400 x 1050); SXGA (1280 x 1024); HD (1280 x 720); XGA (1024 x 768)
Country of origin	Product of Laos
Digital signage	Appspace; Raydiant
Interoperability	Zoom Certified; Microsoft Teams Certified; All cloud service providers through Poly Video App mode; USB Device mode; Support for native 3rd party applications including Zoom, Microsoft Teams, BlueJeans, Dialpad, GoToRoom, RingCentral and StarLeaf
Management Software	Poly Lens
Manufacturer Warranty	Poly standard one-year limited warranty
Minimum dimensions (W x D x H)	13.75 x 1.5 x 5.5 in
Minimum dimensions (W x D x H)	349.2 x 38.1 x 139.7 mm
Minimum order quantity	1
Network capabilities	IPv4; IPv6; 1x 10/100/1G Ethernet; Auto-MDIX; H.323 and/or SIP up to 6 Mbps in Poly App video mode; Polycom Lost Packet Recovery (LPR) technology; Dynamic bandwidth allocation; Reconfigurable MTU size; Web proxy support: basic, digest, and NTLM; 3x 10/100/1G LLN supporting POE+/PSE; RS232 with REST and CLI API support
Non-Operating Humidity Range	5 to 95%
Non-operating temperature - Celsius	-40 to 70 °C
Non-operating temperature - fahrenheit	-40 to 158 °F
Operating altitude	3,048 m
Operating altitude	10,000 ft
Operating humidity range	15 to 80%
Operating temperature range	0 to 40 °C
Operating temperature range	32 to 104 °F

People video resolution	4K, 30 fps (TX and RX) from 2048 Kbps; 1080p, 60 fps from 1740 Kbps; 1080p, 30 fps from 1024 Kbps; 720p, 60 fps from 832 Kbps; 720p, 30 fps from 512 Kbps; 4SIF/4CIF, 60 fps from 512 Kbps; 4SIF/4CIF, 30 fps from 128 Kbps; QCIF (176 x 144) from 64 kbps; SIF (352 x 240) from 64 Kbps; CIF (352 x 288) from 64 Kbps; w288p from 128 Kbps; w448 from 384 Kbps; w576p from 512 Kbps
Physical security	Standard Kensington lock slot
Ports	1 USB Type-C® 5Gbps signaling rate; 3 USB Type-A 5Gbps signaling rate; 1 audio-in; 1 audio-out; 1 RS-232; 1 HDMI-in 1.4 (video and audio); 2 HDMI-out 1.4 (video); 1 HDCI; 1 HDMI-out 1.4 (audio)
Power	65 BTU h
Power supply type	External
Special features	Auto sensing power supply
UNSPSC code	45111902
Video frame rate	5–60 fps (up to 4K resolution at 15 fps in call)
Video standards	H.264 AVC; H.264 High Profile; H.265
Weight	2.1 lb
Weight	952.5 g

Disclaimer — Copyright

© Copyright 2024 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (us-en) – Mar 07, 2024 4:43 PM UTC+0000