TRIPP-LITE

1000 Eaton Boulevard Cleveland, OH 44122 United States

Protect It! 6-Outlet Low-Profile Surge Protector, Direct Plug-In, 540 Joules, Diagnostic LED

MODEL NUMBER: SK6-0







Highlights

- 6 outlets/direct plug-in
- 540 joule rating

Package Includes

- SK6-0 Surge Suppressor
- Warranty information
- Instruction manual

Description

The SK6-0 Surge Suppressor is ideal for protecting audio/video devices and printers. This direct plug-in surge suppressor features six outlets and 540 joules of surge energy absorption.

Features

- 6 outlets; direct plug-in
- Surge energy absorption: 540 joules; 27,000 amps
- \$10,000 Ultimate Lifetime Insurance (USA and Canada Only)
- Automatic shutoff cuts power to outlets when the protection circuit has been compromised

Specifications

OVERVIEW		
UPC Code	037332010261	
INPUT		
Nominal Input Voltage(s) Supported	120V AC	
Recommended Electrical Service	120V (110-125V)	
Input Cord Length Details	Direct Plug-In	
Voltage Compatibility (VAC)	120	
Maximum Surge Amps	36000	
Input Plug Type	NEMA 5-15P	
Input Cord Length (ft.)	0	

TRIPP-LITE

Right-Angle Plug	No	
Input Cord Length (m)	0.00	
Integrated Cord Clip	No	
OUTPUT		
Frequency Compatibility	50 / 60 Hz	
Output Receptacles	(6) 5-15R	
Circuit Breaker (amps)	15	
Transformer Accommodation	(2) Yes	
Right-Angle Outlets	No	
USER INTERFACE, ALERTS & CON	TROLS	
Diagnostic LED(s)	Yes	
SURGE / NOISE SUPPRESSION		
AC Suppression Joule Rating	540	
AC Suppression Response Time	< 1 ns	
Protection Modes	Includes full normal mode (H-N) and common mode (N-G / H-G) line suppression	
AC Suppression Surge Current Rating	27,000 amps	
UL1449 Let Through Rating	400, 500, 500	
Immunity	Conforms to IEE 587 / ANSI C62.41	
Automatic Shut-Off	Yes	
DATALINE SURGE SUPPRESSION		
Cable (Coax) Protection	No	
Network (Ethernet) Protection	No	
Telephone/DSL Protection	No	
PHYSICAL		
Material of Construction	Plastic	
Housing Color	Light Gray	
Mounting Holes or Slots	No	
Outlets Measurement (Center to Center)	Distance between horizontal outlets = 25.2mm; Distance between vertical outlets = 39mm	
Receptacle Color	Gray	
Shipping Dimensions (hwd / in.)	6.30 x 8.70 x 1.50	
Shipping Dimensions (hwd / cm)	16.00 x 22.10 x 3.81	

TRIPP-LITE

[
Shipping Weight (lbs.)	0.61	
Shipping Weight (kg)	0.28	
Unit Dimensions (hwd / in.)	4.800 x 4.350 x 1.420	
Unit Dimensions (hwd / cm)	12.19 x 11.05 x 3.6	
Unit Weight (lbs.)	.406	
Unit Weight (kg)	0.18	
FEATURES & SPECIFICATIONS		
Rotatable Outlets	No	
Antimicrobial	No	
STANDARDS & COMPLIANCE		
Product Certifications	cUL Listed; UL 1449; UL Listed	
Product Compliance	RoHS	
WARRANTY & SUPPORT		
Product Warranty Period (Worldwide)	Lifetime limited warranty	
Connected Equipment Insurance (U.S., Canada & Puerto Rico)	\$10,000 Ultimate Lifetime Insurance	



© 2023 Eaton. All Rights Reserved. Eaton is a registered trademark. All other trademarks are the property of their respective owners.