Ortronics

TechChoice 6 Keystone jack, Orange, 25pack

Part No. KS6-43



Category 6 Keystone jack, 8-position, 180 degree exit, icon compatible, T568A/B wiring. TechChoice keystone jacks and modules feature an easy-to-follow universal wiring label and support standard termination using a 110-impact tool. The keystone footprint allows for the greatest flexibility in installation scheduling because its rear insertion into the faceplate allows the technician to complete the termination before and during the construction process.

Features & Benefits

- Icon compatible, supports 606 designation requirements
- Easy to follow universal wiring label
- Rear loading, preferred mounting for panels

Specifications

General Info

Product Line	Ortronics	Color	Orange
UPC Number	662875526902	Country Of Origin	China
Application Sector	Commercial, Industrial	Standard	ANSI/TIA-568.E-2;ISO/IEC 11801-1;UL 1863
Warranty Type	5-Year	Type	Jack

Dimensions

Product Width US	0.55 in	Product Depth US	1.13 in
Product Height US	0.63 in		

Additional Information

Product Environmental Profile	Yes

Technical Information

Wire Gauge	22-24 AWG	Termination Style	110
Connector Type	RJ-45	Impedance	100 Ohm