ELITE SCREENS

VMAX 3 Series Dimensions Table

Model Number	Nominal Diagonal & Aspect Ratio	Screen Material	Gain	Case Color	Case Length (A)	Viewable Width (A1)	Screen Width (A2)	A3	Weight Bar Length (A4)	Overall Height (B)	Viewable Height (B1)	B2	B3	End cap Height (B4)	Top Leader (B5)	C1	End cap Width (C2)	Power Cord Length (D)	Packing Dimensions (LxWxH)			Net Weight	Gross Weight
Unit: inch																						***Lbs***	***Lbs***
VMAX125UWH3	125" (16:9)	MaxWhite® Fiberglass	1.1	Black	120.8	109.0	112.9	118.7	116.3	76.6	61.3	72.4	3.1	4.1	8.0	0.7	3.5	98.4	Coming Soon			*	*
VMAX135UWH3	135" (16:9)	MaxWhite® Fiberglass	1.1	Black	129.5	117.7	121.6	127	124.8	80.69	66.2	76.6	2.4	4.1	8.0	0.7	3.5	98.4	134.7	6.5	5.9	41.3	50.2
VMAX150XWV3	150"(4:3)	MaxWhite® Fiberglass	1.1	White	131.9	120.0	123.9	129.7	127.1	100.5	90.0	96.4	2.4	4.1	4.0	0.7	3.5	98.4	137.1	6.7	6.2	41.3	49.9
VMAX150XWH3	150"(16:9)	MaxWhite® Fiberglass	1.1	White	142.6	130.7	134.7	140.4	137.8	84.0	73.5	79.9	2.4	4.1	4.0	0.7	3.5	98.4	147.9	6.8	6.5	44.1	52.6
VMAX150UWH3	150"(16:9)	MaxWhite® Fiberglass	1.1	Black	142.6	130.7	134.7	140.4	137.8	84.0	73.5	79.9	2.4	4.1	4.0	0.7	3.5	98.4	147.9	6.8	6.5	44.1	52.6
VMAX150UWH3-E24	150"(16:9)	MaxWhite® Fiberglass	1.1	Black	142.6	130.7	134.7	140.4	137.8	104.0	73.5	99.9	2.4	4.1	24.0	0.7	3.5	98.4	147.6	6.9	6.1	44.3	53.0
VMAX166XWH3	166" (16:9)	MaxWhite® Fiberglass	1.1	White	156.5	144.7	148.6	154.3	151.8	91.9	81.4	87.8	2.4	4.1	4.0	0.7	3.5	98.4	161.7	6.5	6.1	49.6	60.6
Unit: mm																						***Kgs***	***Kgs***
VMAX125UWH3	125" (16:9)	MaxWhite® Fiberglass	1.1	Black	3069	2767	2867	3014	2953	1945	1557	1840	80	105	203	17	90	2500	Coming Soon			*	*
VMAX135UWH3	135" (16:9)	MaxWhite® Fiberglass	1.1	Black	3289	2989	3089	3234	3169	2049	1681	1944	60	105	203	17	88	2500	3421	165	150	18.8	22.8
VMAX150XWV3	150"(4:3)	MaxWhite® Fiberglass	1.1	White	3349	3048	3148	3294	3228	2553	2286	2448	60	105	102	17	88	2500	3481	170	157	18.8	22.7
VMAX150XWH3	150"(16:9)	MaxWhite® Fiberglass	1.1	White	3622	3321	3421	3567	3501	2135	1868	2030	60	105	102	17	88	2500	3757	173	165	20.2	25.8
VMAX150UWH3	150"(16:9)	MaxWhite® Fiberglass	1.1	Black	3622	3321	3421	3567	3501	2135	1868	2030	60	105	102	17	88	2500	3757	173	165	20.2	25.8
VMAX150UWH3-E24	150"(16:9)	MaxWhite® Fiberglass	1.1	Black	3622	3321	3421	3567	3501	2643	1868	2538	60	105	610	17	88	2500	3750	175	155	20.1	24.1
VMAX166XWH3	166" (16:9)	MaxWhite® Fiberglass	1.1	White	3975	3675	3775	3920	3855	2334	2067	2229	60	105	102	17	88	2500	4107	165	155	22.5	27.5

Note: Data Error may be ±1"

The listed measurements are for general reference only. Please contact Elite Screens to verify product design and dimensions before attempting to integrate its products with any structural or furniture modification. Although a manufacturer may offer product advice, it may be taken or disregarded at the integrator's discretion. Elite Screens will not be held responsible or be otherwise liable for faulty installations.





