



# Fast & Versatile Production Scanning at 120\* IPM



## PATRIOT™ 780

Scans directly to searchable  
PDF!

- GSA & TAA Compliant
- 60 pages per minute in simplex and 120 images per minute\* in duplex
- A3 (11" x 17") Flatbed and ADF
- 120 pages ADF capacity\*\*
- Superior image quality and OCR accuracy with Kofax VRS software
- Convert documents into PDF files that can be scanned to network drives for sharing
- Compatible with hundreds of document capture applications
- Hi-Speed USB 2.0 interface (USB 1.1 compatible)
- TWAIN and ISIS drivers

\*Up to 120 ipm at 200 dpi, black & white

\*\*16# paper

### The Visioneer Patriot™ 780 Document Scanner

The Visioneer Patriot 780 is a production flatbed scanner with 120-page capacity ADF, scans documents at 60 ppm and 120 ipm through Hi-Speed USB 2.0. The Visioneer Patriot 780 brings, production scanning to any organization at the right price with high quality. Software bundle includes Kofax VRS, and ScanSoft OmniPage. The use of production scanners for regulatory compliance is sharply on the rise, the Visioneer Patriot makes compliance easy for any scanning operator. With its A3 (11" x 17") size flatbed, documents which previously were too large are no longer a problem. The ADF allows scanning of documents landscape or portrait.

### Government Solutions

The U.S. Government is one of the largest organizations in the world that manages paper for information flow, data collection, archiving, and records management. GPO (Government Printing Office) is the largest printer in the world. The U.S. District Courts have six-hundred offices throughout the U.S. that manually processes hundred of thousands of court records and other types of data. Millions of medical documents for the Army, Navy, Air Force and Marine personnel are stored at various bases, ships and countries, and paper is at times the only media available. In recent years the U.S. Government has recognized the need to have all these various government documents digitized and accessible through their infrastructure.

The Patriot 780 has the ability to power these paper-to-digital workflows and processes through best-in-class performance, compatibility and productivity. Fast, reliable and cost-efficient document imaging solutions that include the Patriot 780 provide near-term ROI.

New regulatory compliance requirements have dramatically increased the need for companies to implement secure and reliable records management and document capture solutions. Production scanners are ideal for document management in small to mid-volume applications and may also be used to complement higher volume needs in centralized scanning settings.





# PATRIOT™ 780



## Robust Features & Connectivity

The Patriot 780's powerful software, robust functionality and hardware specifications delivers the speed and quality for production scanning. And document size is not an issue for the Patriot 780. The ADF handles everything from 4" x 4.5" documents up to A3 (11" x 17"). The flatbed of course can accommodate all sizes up to A3 including books, delicate originals and multiple pieces of paper.

## Scan to Text-Searchable PDF

The Patriot 780 transforms volumes of documents and illustrations into organized digital files that you can quickly find, use, and share. In PDF format, you can instantly search documents for keywords or phrases. This gives them additional archival benefits beyond traditional storage, and the widely accepted PDF format lets everyone view and print documents – on any computer.

## Superior Image Quality and OCR Accuracy

Get superior results with Kofax VirtualReScan (VRS), the award-winning, patented technology that automatically produces the best possible image quality and OCR results for scanned document images. As pages pass through the scanner, VRS performs a multipoint inspection of each document, instantly checking and adjusting alignment (skew), brightness, contrast, and image clarity.

## Software That Gets the Job Done

The Patriot 780's robust software suite includes comprehensive ISIS and TWAIN support:

- Kofax VRS
- ScanSoft OmniPage Pro
- Visioneer OneTouch™ Technology
- TWAIN, Certified ISIS and WIA drivers

### Patriot 780 Product Specifications Model # P7801D-WU

Scan Speed	
Black & White, 200 dpi	Up to 60 ppm simplex / 120 ipm duplex
Optical Resolution	600 dpi
Scanner Bit Depth (color)	48-bit internal (16-bit A/D converter recognizes over 281 trillion colors)
Scanner Bit Depth (grayscale)	16-bit internal (65,536 shades of gray)
Output Bit Depth	24-bit color, 8-bit grayscale, 1-bit black & white
Scan Method	Fast Duplex Scanner
Interface	Hi-Speed USB 2.0 (USB 1.1 compatible)
Dimensions	26.37"(w) x 20.23"(d) x 9.8"(h)
Weight	43.4 lbs.
ADF Maximum Document Size	11.7" x 17"
ADF Minimum Document Size	4" x 4.5"
ADF Capacity	120 sheets (16 lb. paper)
Duty Cycle	8,500 pages/day

### Minimum System Requirements

- Pentium® III or equivalent processor
- Windows® XP\*/2000\*\*
- 512MB RAM (Recommended 1GB)
- 200MB available hard disk space
- CD-ROM drive
- USB port

\*Service Pack 1 and 2 \*\*Service Pack 4

### Support Contracts

Visit [www.visioneer.com](http://www.visioneer.com) to learn more about the many warranty and service options available to you.

### Contents

- Patriot 780 Scanner
- Power Supply
- USB 2.0 Cable
- Quick Install Card
- Technical Support Card
- User's Manual
- CD-ROM including:
  - Kofax VRS
  - ScanSoft OmniPage Pro
  - Visioneer OneTouch™ Technology
  - Scanner Drivers
  - (TWAIN, Certified ISIS and WIA)

