CUSTOM
EMPOWERING BUSINESS TRANSACTIONS

2-LINE LCM CUSTOMER DISPLAY

ATTACH, CONFIGURE, TRANSACT

With its family of Micro USB-attached accessories, TREK can be instantly transformed for any customer touchpoint. Three strategically positioned ports along the display bezel allow for secure attachment of accessories to create a multitude of solutions that empower transactions.

The TREK 2-Line LCM Customer Display is a 2-line x 20-character LED backlit display that is purpose-built for the point-of-sale. Capable of displaying any downloadable codepage of single byte characters, the TREK 2-Line LCM Customer Display seamlessly adds functionality and interactivity to the TREK.



AT A GLANCE

- Three-Year Warranty
- Android and Windows OS Support
- Multiple Mounting Options

AVAILABLE MODELS

Description	Part Number
LCM 2-LINE CUSTOMER DISPLAY FOR TREK	932PW010500M33

Specifications	Details
Color	Black
Input Connector Type	USB Type C
Input Voltage	USB +5 V Power Supply
Power Consumption (Typical)	0.5 W
Display Type	FSTN Negative Transmissive LCD
Display Color	Blue Ground - White Character
Brightness (typical)	260 cd/m2
Number of Characters	40 (20 columns x 2 lines)
Characters Available	96 alphanumeric
Dot Size (X x Y)	0.92 mm x 1.1 mm
Font Size (W x H)	4.84 mm x 9.22 mm
Viewing Angle	30 ~ 60 degress (Vertical) | -45 ~ 45 degrees (Horizontal)
Panel Dimension	134 (W) x 36 (H) x 13.7 (D) mm
Supported Command Sets	POS7300, EPSON ESC/POS, DSP800, ADM787/ADM788, AEDEX/EMAX, UTC, and CD5220
Language Support	Belarusian, Bulgarian, Croatian, Czech, Danish, Dutch, English, Estonian, French, French Canadian, German, Greek, Hebrew, Hungarian, Italian, Japanese, Latvian, Lithuanian, Macedonian, Norwegian, Polish, Portuguese, Romanian, Russian, Serbian, Slovak, Slovene, Spanish, Swedish, Turkish, Ukrainian
SDK / Drivers	USB Virtual COM
Supported Operating Systems	Windows 10, Windows 11, Android, ChromeOS Flex
MTBF	10,000 hours (Power on time)
Dimensions	160 mm x 74 mm x 90 mm
Shipping Box Dimensions	200 mm x 148 mm x 82 mm
Weight (Unpackaged)	300 g
Weight (Packaged)	400 g
Operating Temperature	-20° C to 70° C
Storage Temperature	-30° C to 80° C
Humidity	30% ~ 85%
Warranty	3 years
What's in the Box	2-Line LCM Display, 2x mounting screws, mounting bracket

Explore our full product lineup at custom.biz, or connect with our team to configure the right setup for your business by emailing info@custom.biz.