Poly TC10 White Touch Controller GSA/TAA (973G1AA)



Overview

Meet. Schedule. Join

The Poly TC10 touch control panel makes meetings more productive and allows users to easily schedule workspaces and conference rooms.

Easier room scheduling

Meeting spaces are a breeze to schedule with a Zoom-certified scheduling panel. Multi-color LED lights let you know the vacancy status before you approach the door. And the touch screen lets you schedule your next meeting space in seconds.

Clean and simple installation

Our versatile touch panel is sleek and professional. Mount it on walls or glass or place it on a table with its flexible stand. Adjust the angle for visibility. With a single cable for power and connectivity, it maintains a clean profile.

Complete call control

Instantly take charge of calls and enjoy seamless access to your favorite cloud video apps on your room's video system. Control of your video calls with ease and share content with a tap.

Features

Useful inside or outside any room

The incredible versatility enables it to be used outside the room for scheduling, or inside the room as a video and room controller.

Large, clear display

The TC10 offers a clear, high-resolution 10” touch display that makes its intuitive controls easy to find and use.

Sleek design

The TC10 offers a uniquely tidy, professional-looking setup, thanks to its sleek design and convenient single cable for both power and connectivity.

Certified for Zoom

Schedule and conduct Zoom meetings with ease via seamless, Zoom-certified integration with the app.

Certified for Microsoft Teams

Deploy as a controller for Microsoft Teams on Android when paired to a Poly video system or install outside the room as a Microsoft Teams Panel for scheduling.

Specifications

Display size (diagonal)	25.7 cm (10.1")
Display size (diagonal)	10.1"
Panel technology	IPS
Dimensions (W x D x H)	260 x 184 x 64 mm
Dimensions (W x D x H)	10.25 x 7.25 x 2.5 in
Weight	1.27 kg
Weight	2.79 lb
Ports	1 RJ-45
Package dimensions (W x D x H)	190 x 210 x 55 mm
Package weight	300 g
Special features	Air Quality Sensor; Proximity sensor; Scheduler; Wall mountable; Standalone mode
UPC number	(ABA) 197961052206; (AC3) 198122634231
Manufacturer Warranty	Poly standard one-year limited warranty
What's in the box	Poly TC10; Wall mount kit; Table stand; Mounting hardware; RJ-45 cable; Quick start QR code; Warranty card; Poly Lens coaster

Additional specifications

Aspect ratio	16:10
Brightness	300 nits
Cartons per layer	5
Cartons per pallet	35
Certified collaboration software	Zoom
Contrast ratio	1000:1
Horizontal viewing angle	75°
Interoperability	Support for native 3rd party applications includes: Zoom Rooms, 8x8, BlueJeans, GoToRoom, Tencent, RingCentral, DialPad and others (when paired to a Poly Video OS system); Integration with Extron (environmental controls)
Management Software	Poly Lens; Device Management Service[1]
Master carton dimension (imperial)	5.02 lb
Master carton dimension (metric)	40 x 60 x 28.8 cm
Master carton weight (metric)	2.28 kg
Multiple order quantity	4
Native resolution	WXGA (1280 x 800)
Non-Operating Humidity Range	5 to 95%
Non-operating temperature - Celsius	-20 to 60 °C
Non-operating temperature - fahrenheit	-4 to 158 °F
Operating altitude	3,048 m
Operating altitude	10,000 ft
Operating humidity range	15 to 80%
Operating temperature range	0 to 40 °C
Operating temperature range	32 to 104 °F
Pallet (layers)	7
Pallet dimensions	47.24 x 39.37 x 84.68 in
Pallet dimensions (W x D x H)	120 x 100 x 215.1 cm
Pallet weight	787.05 lb
Pallet weight	357 kg
Physical security	Standard Kensington lock slot
Power	Power over Ethernet (PoE), compatible with IEEE 802.3at class 0
Products per pallet	140

Products per pallet layer	20
UNSPSC code	45111902
Vertical viewing angle	75°

---

[1] Requires downloadable software on Poly.com/lens. Host PC requires Windows 10 or higher.

Services

Communication & Collaboration

★ : Recommended

Poly Support Services

3 Year Poly+ TC10	**P37760312 ★**
1 Year Partner Poly+ Onsite TC10	P37760158
1 Year Partner Poly+ TC10	P37760160
1 Year Poly Elite Custom TC10 for Citi use only	E37760650
1 Year Poly Elite FRURAD TC10 For Commercial use	U99P0PV
1 Year Poly Elite FRURAD TC10 Government Agency Use only	U99NTPV
1 Year Poly Elite Onsite FRURAD TC10 For Commercial use	U99P1PV
1 Year Poly Elite Onsite FRURAD TC10 Government Agency Use only	U99NVPV
1 Year Poly Elite Onsite TC10	E37760114
1 Year Poly Elite TC10	E37760112
1 Year Poly+ FRURAD TC10 For Commercial use	U99NWPV
1 Year Poly+ FRURAD TC10 Government Agency Use only	U99NNPV
1 Year Poly+ Onsite FRURAD TC10 For Commercial use	U99NXPV
1 Year Poly+ Onsite FRURAD TC10 Government Agency Use only	U99NQPV
1 Year Poly+ Onsite TC10	P37760114
1 Year Poly+ TC10	P37760112
1 Year extension of 5yr HW Replacement TC10 with advanced part replacement HSP Only	D37760DS1
3 Year Partner Poly+ Onsite TC10	P37760358
3 Year Partner Poly+ TC10	P37760362
3 Year Poly Elite Onsite TC10 Service	U86S5PV
3 Year Poly Elite TC10	E37760312
3 Year Poly+ FRURAD TC10 For Commercial use	U99NYPV
3 Year Poly+ FRURAD TC10 Government Agency Use only	U99NRPV
3 Year Poly+ Onsite FRURAD TC10 For Commercial use	U99NZPV
3 Year Poly+ Onsite FRURAD TC10 Government Agency Use only	U99NSPV
3 Year Poly+ Onsite TC10	P37760314
4 Year Poly+ TC10	UJ8Y4PV
5 Year Next Business Day HW Replacement TC10 HSP Only	D37760DS5
5 Year Poly+ TC10	UF4W1PV

Service Reactivtion Fee TC10 for product less than one year out of support coverage	R37760801
Service Reactivtion Fee TC10 for product more than one year out of support coverage	R37760802
Upgrade embedded 1yr Poly+ to 1yr Poly Elite TC10	E37760912
Upgrade embedded 1yr Poly+ to 1yr Poly+ Onsite TC10	P37760102
Upgrade embedded 1yr Poly+ to 3yr Partner Poly+ Onsite TC10	P37760788
Upgrade embedded 1yr Poly+ to 3yr Partner Poly+ TC10	P37760351
Upgrade embedded 1yr Poly+ to 3yr Poly+ Onsite TC10	P37760309
Upgrade embedded 1yr Poly+ to 3yr Poly+ TC10	P37760103
Upgrade embedded 3yr Partner Poly+ to 3yr Partner Poly+ Onsite TC10	P37760555
Upgrade embedded 3yr Partner Poly+ to 3yr Poly+ Onsite TC10	P37760444
Upgrade embedded 3yr Partner Poly+ to 3yr Poly+ TC10	P37760333

Disclaimer — Copyright

© Copyright 2025 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

Generated by Dynamic Collateral Tool – (ww-en) – Nov 28, 2025 4:00 AM UTC+0000