

Power It! 10-Outlet Power Strip, 15 ft. (4.57 m) Cord

MODEL NUMBER: TLM1015NC



Highlights

- 10 outlets spaced to accommodate transformers
- Illuminated on/off switch with cover
- 15-amp circuit breaker
- 15-ft. (4.57 m) power cord
- Heavy-duty metal case
- Keyhole slots on removable mounting brackets

Package Includes

- TLM1015NC power strip
- Warranty information
- Instruction manual

Description

Tripp Lite's Power It! TLM1015NC power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment. Includes 10 NEMA 5-15R outlets spaced to accommodate transformers, 15-ft. (4.57 m) AC power cord and keyhole slots on removable mounting brackets. Multi-outlet strip reduces cable clutter and enables the connection of multiple electrical devices to a single AC wall socket. Features heavy-duty metal case to stand up to the most demanding environments, illuminated power switch with transparent cover to prevent accidental shutoff and 15A integrated circuit breaker to prevent dangerous overloads.

INPUT/OUTPUT: Input: NEMA 5-15P/Output: 10 NEMA 5-15R

ELECTRICAL: 120V AC, 50/60Hz, 15A

FORMAT: Corded power distribution strip

Features

- Multi-outlet power strip offers reliable, convenient and cost-effective power distribution for appliances, power tools, lighting and other electrical equipment
- Includes 10 NEMA 5-15R outlets spaced to accommodate transformers
- Illuminated on/off switch provides one-touch power control for connected equipment
- Transparent switch cover snaps tight to prevent accidental shutoff
- Convenient keyhole slots on removable brackets provide secure mounting options for a wide variety of surfaces and applications
- 15A power handling capacity with integrated circuit breaker
- 120V AC, 50/60Hz electrical compatibility
- 15-ft. (4.57 m) AC power cord
- Heavy-duty metal case provides maximum safety and durability
- UL certification

Specifications



| OVERVIEW | |
|--|--|
| UPC Code | 037332136107 |
| INPUT | |
| Nominal Input Voltage(s) Supported | 120V AC |
| Recommended Electrical Service | 15A 120V |
| Input Cord Gauge Type | 14 gauge; SJT |
| Voltage Compatibility (VAC) | 120 |
| Input Plug Type | NEMA 5-15P |
| Input Cord Length (ft.) | 15 |
| Input Cord Length (m) | 4.57 |
| Integrated Cord Clip | No |
| OUTPUT | |
| Frequency Compatibility | 50 / 60 Hz |
| Output (Watts) | 1800 |
| Output Receptacles | (10) 5-15R |
| Circuit Breaker (amps) | 15 |
| Overload Protection | 15A circuit breaker |
| Transformer Accommodation | (5) Yes |
| Outlet Orientation | 10 outlets arranged in 2 rows and spaced to accommodate transformers |
| Right-Angle Outlets | No |
| USER INTERFACE, ALERTS & CONTROLS | |
| Switches | Illuminated on/off switch controls power to all outlets |
| Locking Switch Cover | Transparent switch cover snaps tight to prevent accidental shutoff |
| PHYSICAL | |
| Color | Light Gray |
| Antimicrobial Coating | No |
| Color (AC Line Cord) | Light Gray |
| Included Mounting Accessories | Keyhole slots on removable mounting brackets |
| Integrated Keyhole Mounting Slots | Yes (Includes flanges) |
| Keyhole Slot Mounting Measurement (Center to Center) | Distance between end tabs = 462.30mm |
| Material of Construction | Metal |



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

| | |
|--|--|
| Outlets Measurement (Center to Center) | Distance between horizontal outlets = 71.45mm; Distance between vertical outlets = 38.90mm |
| Receptacle Color | Light gray |
| Shipping Dimensions (hwd / cm) | 6.60 x 23.11 x 51.31 |
| Shipping Dimensions (hwd / in.) | 2.60 x 9.10 x 20.20 |
| Shipping Weight (kg) | 2.31 |
| Shipping Weight (lbs.) | 5.10 |
| Unit Dimensions (hwd / cm) | 44.5 x 10.2 x 5.7 |
| Unit Dimensions (hwd / in.) | 17.5 x 4 x 2.25 |
| Unit Weight (kg) | 2.09 |
| Unit Weight (lbs.) | 4.6 |
| STANDARDS & COMPLIANCE | |
| Canada | cUL |
| Additional International Approvals | Complies with RoHS (Restriction of Hazardous Substances Directive) |
| UL1363 (Power Tap) | UL1363 |
| WARRANTY | |
| Product Warranty Period (Worldwide) | Lifetime limited warranty |

© 2021 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice. Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies: <https://www.tripplite.com/products/product-certification-agencies>