

1ft (30cm) Short Extension Cord, NEMA 5-15R to NEMA 5-15P Black Extension Cord, 13A 125V, 16AWG, Outlet Extension Power Cable, NEMA 5-15R to NEMA 5-15P AC Computer Power Cord - UL Listed

**Product ID:** PAC101



This 12in Computer Power Cord Extension Cable instantly turns a large, awkward power connector into a smaller, streamlined connector.

The power adapter will fit into any socket, maximizing the space on your power strip, surge protector, or wall outlet.

The power adapter also doubles as a power cord extender, giving you an extra 12in of reach for your monitor, computer case, or any other powered device.

## Certifications, Reports and Compatibility



## Applications

- Allows you to attach bulky power adapter to a power strip or a wall outlet without blocking other outlets
- StarTech.com's power extender cable saves space and conveniently connects big sized adapters so you can maximize all your power/surge strip outlets

## Features

- **POWER EXTENSION CORD:** This 1ft (0.3m) 16AWG AC power extension cable with NEMA 5-15R and NEMA

5-15P connectors is suitable for workstations/home office Indoor use Rated to carry 125V at 13A

- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief on connectors for durability  
Fire Rating: VW-1 3 Conductor extension cord with 100% copper wire This cable is available in other lengths
- **SPECS:** 1ft (0.3m) AC Power Cord NEMA 5-15R to NEMA 5-15P 16AWG 125V 13A (Max) Jacket Type: SJT  
Jacket Material: PVC Black Temperature Range: 37F to 140F (3C to 60C) Cable Outer Diameter: 0.33in (8.5mm)
- **COMPATIBILITY:** PC Power Extension Cord NEMA 5-15P works with North American outlets Extend a 3-prong power connection from your desktop computer, server, or printer Replacement power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this extension cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

---

#### Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

---

#### Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
Connector B	1 - NEMA 5-15 Power (North America)

---

#### Power

Input Voltage	125 AC
Input Current	13 A

---

#### Environmental

Operating Temperature	-20C to 60C (-4F to 140F)
-----------------------	---------------------------

---

#### Physical Characteristics

Color	Black
Wire Gauge	16 AWG
Cable Length	12.0 in [304.8 mm]
Product Length	12.0 in [304.8 mm]
Weight of Product	3.0 oz [86 g]

---

**Packaging  
Information**

Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	1.1 in [27 mm]
Shipping (Package) Weight	3.4 oz [95 g]

---

***\*Product appearance and specifications are subject to change without notice.***

